ZOTAC GAMING GeForce RTX 5070 AMP White Edition

SKU: ZT-B50700FQ-10A | EAN: 8886307703392 | UPC: 810012086769

The ZOTAC GAMING GeForce RTX 5070 AMP White Edition is a high performance, NVIDIA SFF-Ready graphics card that packs a huge punch in a compact form factor. Using NVIDIA's cutting-edge Blackwell architecture, and features like DLSS4, a strong factory OC and impressive cooling, the AMP White Edition is built tough and hard-hitting in video games and professional workloads.









KEY FEATURES

- NVIDIA Blackwell Architecture
- 5th Generation Tensor cores
- 4th Generation RT cores
- NVIDIA DLSS 4
- Game Ready and NVIDIA Studio Drivers
- NVIDIA® App
- NVIDIA Broadcast, NVIDIA G-SYNC®
- NVIDIA SFF-Ready Enthusiast GeForce Card
- 12GB GDDR7 graphics memory
- IceStorm 2.0 advanced cooling
- FREEZE fan stop
- Triple 90mm BladeLink Fans
- Metal backplate
- SPECTRA RGB lighting
- ZOTAC GAMING FireStorm Utility
- Side Retention Mount for secure transport

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

- NVIDIA GeForce RTX 5070 GPU
- 6144 CUDA cores
- 12GB GDDR7 memory
- 192-bit memory bus
- Engine boost clock: 2587 MHz
- Memory clock: 28 Gbps
- PCI Express 5.0 x16

SOFTWARE COMPATIBILITY

- Game Ready and NVIDIA Studio Drivers
- PCI Express® Gen 5
- Microsoft DirectX® 12 Ultimate
- Vulkan RT APIs, Vulkan 1.4
- OpenGL 4.6
- Windows 11 / Windows 10 64-bit (v1809 November 2018 or later)

CONNECTIONS

- 3 x DisplayPort 2.1b with UHBR20 (up to 4K 480Hz or 8K 165Hz with DSC)
- 1 x HDMI® Connector (Supports 4K 480Hz HDR or 8K 120Hz HDR with DSC, and Gaming VRR as specified in the HDMI 2.1b Specification)
- HDCP 2.3 support
- Up to 4 displays simultaneously

POWER REQUIREMENTS

- 650-watt power supply recommended
- 250-watt max power consumption
- 1 x 12v-2x6 power input

INSIDE THE BOX

- ZOTAC GAMING GeForce RTX 5070 AMP White Edition
- User Manual
- 2 x 8-pin-to-16-pin cable
- GPU Support Stand

DIMENSIONS

Product:

- Length: 304.4 mm (12 in)
- Height: 115.8 mm (4.6 in)
- Width: 2 slot (41.6 mm) (1.6 in)

Box:

- Height: 424mm (16.7 in)
- Width: 207mm (8.1 in)
- Depth: 99mm (3.9 in)

©2026 ZOTAC Technology Pte. Ltd. All rights reserved. All company and/or product names may be trade names, trademarks and/or registered trademarks of the respective owners with which they are associated. Features, pricing, availability and specifications are subject to change without notice. ZOTAC Technology Pte. Limited does not warrant the accuracy, completeness or reliability of information, materials and other items contained on this website or server. No liability is assumed with respect to the use of the information contained herein. When accessing this website, users acknowledge that ZOTAC Technology Pte. Limited will not be liable in any event for any damages arising out of the use of this site or any websites linked to it.

©2026 NVIDIA Corporation. NVIDIA, the NVIDIA logo, and GeForce are registered trademarks of NVIDIA Corporation in the U.S. and other countries. All rights reserved.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

For more information please visit:

ZOTAC.COM