Rugged Mobile Computing Solutions

ZX80
ACCESSORY SPEC BROCHURE



GETAC TECHNOLOGY CORPORATION
5F, Building A, No. 209, Section 1, Nangang Rd., Nangang Dist., Taipei City,
115018, Taiwan, R.O.C. Tel : +886 2 2785 7888 globalmarketing@getac.com |
www.getac.com

Copyright © 2026 Getac Technology Corporation and/or any of its affiliates. All Rights Reserved.

CARRY BAG

Features & Benefits

Constructed of durable Nylon/air mesh fabric, and featuring an adjustable padded shoulder strap, this compact carry bag provides sturdy protection for your tablet while giving maximum comfort. The zippered compartments with multi-functional pockets inside offer the optimal solution to transport the tablet and all of its accessories together in one case, delivering extra convenience and go-anywhere productivity to mobile professionals.

Product Information

Dimensions : L 255 x W 230 x H 123mm
Weight : 560g
Main Materials : Nylon, air mesh fabric

SKU ID

GMBCX3



EXTERNAL DUAL BAY MAIN BATTERY CHARGER

Features & Benefits

This external dual-bay main battery charger is designed to charge up to two batteries at the same time. It provides you the benefit of charging and storing the 2 main batteries together when there are limited space and power socket.

Product Information

AC Input : 100V~240V
DC Output : 13.05V, 2.4A Max.
Number of charge bay : 2 Bay
Dimensions : L 160 x W 180 x H 72.5mm
Weight : 1.2kg
Support main batteries and high-capacity batteries.



SKU ID

GCMCEM (EU Power Cord)
GCMCUM (US Power Cord)
GCMCKM (UK Power Cord)
GCMCAM (AU Power Cord)
GCMCCM (CHN Power Cord)
GCMCTM (TW Power Cord)
GCMCIM (IN Power Cord)

MULTI-BAY BATTERY CHARGER EIGHT BAY

Features & Benefits

The 8-bay multi-battery charger is designed to charge multiple battery packs simultaneously and provide users an efficient charging solution.

Product Information

AC Input : 100V~240V AC, 4.2A 50~60Hz
DC Output : 19.5V, 16.9A
* w / 330W AC Adapter Number of charge bays : 8 bays
Dimensions : L 465 x W 245 x H 95.3~111.3mm
Weight : 4.7 kg, not including battery packs
Support main batteries and high-capacity batteries.



SKU ID

GCECEP (EU Power Cord)
GCECUP (US Power Cord)
GCECKP (UK Power Cord)
GCECAP (AU Power Cord)
GCECCP (CHN Power Cord)
GCECTP (TW Power Cord)
GCECIP (IN Power Cord)

DIGITIZER PEN WITH TETHER

Features & Benefits

The digitizer pen provides a more accurate and easy way for data entry and handwritten signature.

Product Information

Dimensions : 110.8 x Ø9.0mm
Tip size : 2.0 mm ; Ø1.65mm
Tether Length : 304mm

SKU ID

GMPDX7



CAPACITIVE HARD TIP STYLUS & TETHER

Features & Benefits

This capacitive stylus is lightweight and easy to control, allowing smooth and comfortable interaction with the touch screen without worrying about scratching the screen or leaving fingerprints on it. The stylus comes with a tether to keep it attached to the tablet, so it doesn't get lost or misplaced.

Product Information

Stylus dimension : 109.1 mm: Ø 8.9 mm
Tip size : 4 mm; Ø 5.5 mm
Tether Length : 304 mm

SKU ID

GMPSXV
* MOQ : 5pcs



SHOULDER STRAP 2-POINT

Features & Benefits

The 2-point shoulder strap provides a quick and comfortable handsfree carrying option. The strap length is adjustable by using the slide adjusters for height. Also, it fits most body sizes for both cross-body and shoulder carry.

Product Information

Length : 1740mm
Main Material : Nylon

SKU ID

GMS2X2





OFFICE DOCK

Features & Benefits

The Getac office dock brings out multiple I/O ports for connecting essential peripheral devices in the office environment. Through the integrated ethernet or USB connections, users can quickly collect and synchronize field data with central offices for real-time reporting and analytics. The HDMI port also provides a convenient solution for sharing presentations or worksheets from a larger screen.

Product Information

Dimensions : L 148.2 x W 152.6 x H 176.8mm
Weight : 580g
Docking Connector : POGO
* without 65W USB-C AC Adapter
I/O Interfaces :
USB 3.2 Type-C (power delivery only) x 1
Audio In/Output x 1
USB 2.0 Type-A x 2
LAN x 1
HDMI x 1
Kensington lock x 1

SKU ID

GDODXC



65W USB-C AC ADAPTER

Features & Benefits

This adapter is designed to power the device and charge its internal battery from an AC power source.

Product Information

Input : 100V-240V, 50~60Hz, 1.6A
Output : 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3.25A
Dimensions : L 90 x W 51 x H 28.5mm
Weight : 220g ±15g
Input cable length : 1830mm
Output cable length. : 1500mm

SKU ID

GAT6U1 (US Power Cord)
GAT6E1 (EU Power Cord)
GAT6K1 (UK Power Cord)
GAT6A1 (AU Power Cord)
GAT6C1 (CHN Power Cord)
GAT6T1 (TW Power Cord)
GAT6G1 (AG Power Cord)



HAND STRAP WITH STYLUS HOLDER

Features & Benefits

The adjustable strap is designed to keep the tablet secured to user's hand and easier to carry.

Product Information

Dimensions : L 155 x W 54 x H 18mm
Weight : 25g
Main Material : PU

SKU ID

GMHSXE



HIGH-CAPACITY BATTERY 9980MAH

Features & Benefits

The high-capacity battery pack extends the system run time up to two times compared to the standard battery pack, providing a great solution for mobile professionals who require extra battery life for operation longer than one day.

Product Information

Battery Type : Lithium-ion Polymer
Voltage : 3.84V
Capacity : Typical 9980mAh ; Min. 9470mAh
Dimensions : L 119.5 x W 60.6 x H 16.6mm
Weight : 170g

SKU ID

GBM2XA



ROTATING HAND STRAP & KICKSTAND

Features & Benefits

The Rotating Hand Strap is designed to make using the tablet easier and more convenient to carry. The hand strap is adjustable to fit most hand sizes and can be rotated 360 degrees to find the ideal viewing angle while on-the-go. It also includes a built-in kickstand that allows for handsfree usage on flat surfaces, providing more on-the-job flexibility.

Product Information

Dimensions : L 155 x W 80 x H 30mm
Weight :132g
Main Material : PU

SKU ID

GMHRXL



SCREEN PROTECTION FILM (AG)

Features & Benefits

This screen protection film is cut precisely to fit the tablet and is easy to install and remove without leaving a sticky residue. With anti-glare coating, it not only protects the screen from the rigors of daily use but also helps to diffuse light on the screen and reduces glare, providing effortless readability for displayed information under common ambient lighting conditions.

Product Information

Dimensions : L 184 x W 114 x D 0.15 mm
Main Material: PET

SKU ID

GMPFXV
* MOQ : 10pcs



STANDARD BATTERY 4990MAH

Features & Benefits

The hot-swappable battery can support full-shift computing with no downtime. It is a great solution for mobile professionals who require long battery life for all-day operation.

Product Information

Battery Type : Lithium-ion Polymer
Voltage : 3.84V
Capacity : Typical 4990mAh ; Min. 4870mAh
Dimensions : L 119.5 x W 60.6 x H 8.95mm
Weight : 98g

SKU ID

GBM1XA



65W DC-DC VEHICLE ADAPTER

Features & Benefits

The 65W Vehicle Adapter connects to the vehicle dock to charge the tablet. It comes with a choice of two types of connections: a bare wire with individual wire ends already stripped, and a cigarette lighter plug for easy connection to the cigarette lighter socket in the vehicle interior, providing a convenient way to charge and power your tablet while you are on the road.

Product Information

Input Voltage : 12VDC~ 32VDC
Output Voltage : 19.5VDC
Output Current : 3.33A Max.
Case Dimensions : L 70 x W 37.6 x H 26mm
Weight : Cigarette lighter plug version 130g / Bare wire version 105g
Input Cable Length : 1200mm
Output Cable Length : 250mm

SKU ID

GAD6X1 (Cigarette Lighter Plug Version)
GAD6X2 (Bare Wire Version)



65W USB-C VEHICLE ADAPTER

Features & Benefits

The 65W Vehicle Adapter connects to the vehicle dock to charge the tablet. It comes with a choice of two types of connections: a bare wire with individual wire ends already stripped, and a cigarette lighter plug for easy connection to the cigarette lighter socket in the vehicle interior, providing a convenient way to charge and power your tablet while you are on the road.

Product Information

Input Voltage : 12VDC~ 32VDC
Output Voltage : 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3.25A
Case Dimensions : L 70 x W 37.6 x H 26mm
Weight : Cigarette lighter plug version 180g / Bare wire version 145g
Input Cable Length : 1200mm
Output Cable Length : 1000mm

SKU ID

GAD6X3 (Cigarette Lighter Plug Version)
GAD6X4 (Bare Wire Version)

