

#### Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

# Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC), 25M (82 ft.)

### MODEL NUMBER: N320-25M



### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 25 meters ( 80ft ) Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## **Specifications**

OVERVIEW	
UPC Code	037332134912
Technology	Multimode
Optical Mode	OM1
PHYSICAL	
Color	Orange
Cable Jacket Rating	LSZH
Clad Diameter	125 micron

### Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber
- Insertion loss testing performed on every connector (0.2dB typical)

### **System Requirements**

 Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

### **Package Includes**

 25 Meter (80ft) Duplex MMF Cable LC/LC 62.5/125 Micron Fiber



2	
82	
25	
984.3	
30.48 x 26.67 x 1.27	
12.00 x 10.50 x 0.50	
0.20	
0.43	
COMMUNICATIONS	
1Gbps	
CONNECTIONS	
LC DUPLEX (MALE)	
LC DUPLEX (MALE)	
LC DUPLEX (MALE)	
SPECIAL FEATURES	
No	
STANDARDS & COMPLIANCE	
FDDI and OFNR rated	
Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies