

AQUOS®
THERE'S MORE TO SEE



The AQUOS GP1U Series in 37" and 32"*1 screen sizes is a dream come true for game players. This is the first LCD-TV series designed from the ground up to be optimized for today's state-of-the-art video games. The newly developed Vyper Drive game mode eliminates any perceptible lag between the video game and the TV. Side-mounted terminals provide easy connections to games. A custom remote control includes an innovative "Game" button that quickly jumps into Vyper Drive and activates the side terminals. Six 1080p-compatible terminals (3 HDMI, 2 component, 1 DVI-I) ensure the images from your new game console's 1080p outputs will be as clear as possible. Finally, the GP1U's incredible 6ms response time and 10,000:1 (32") / 8500:1 (37") Dynamic Contrast Ratio, combined with Full HD 1080p resolution, provide the best picture quality money can buy.

Features:

Full HD 1080p (1920 x 1080) Resolution for the sharpest picture possible.

Vyper Drive game mode eliminates perceptible lag between game console and display on the TV.

Side terminals enable easy access to game connections.

Custom remote control includes special Game button for quickly jumping to the side terminals and activating the Vyper Drive mode.

10,000:1 (32") / 8500:1 (37") Dynamic Contrast Ratio and 6ms response time produce spectacular picture quality.

Three HDMI™ Inputs and dual component for the ultimate in terminal flexibility. All are compatible with 1080p sources.

Wide Viewing Angles (176°H x 176°W) Sharp's AQUOS viewing angles are so wide, you can view the TV clearly from practically anywhere in the room.

OPC Function automatically alters brightness to adjust to changing room conditions.

Elegant New Design with glossy black cabinet.

High Brightness (450 cd/m²) AQUOS LCD Televisions are very bright. You can put them virtually anywhere – even near windows, doors or other light sources – and the picture is still vivid.

Built-in ATSC / QAM / NTSC Tuners provide access to DTV and analog TV channels.*2

Specifications

Models	LC-37GP1U	LC-32GP1U
Screen Size ^{*1}	37"	32"
Panel Type	Advanced Super View / Black TFT LCD Panel	
Pixel Resolution	1920 x 1080	
Brightness	450cd/m ²	
Viewing Angle	176°H / 176°V	
Lamp Life ^{*4}	60,000 hours	
Audio System	10 W + 10 W	
Tuning System	ATSC / QAM / NTSC	
Dynamic Contrast Ratio with Enhanced Picture Contrast Technology	8500:1	10,000:1
Native Contrast Ratio	1700:1	2000:1
Aspect Ratio	16:9	
Response Time	6ms	
HDMI™ Input	3 (1080p compatible) – 1 side, 2 rear	
HD Component Input	2 (1080p compatible) – 1 side, 1 rear	
DVI-I Input	1 (1080p compatible)	
S-Video Input	1	
Composite Video Input (A/V)	3 – 1 side, 2 rear	
Audio Inputs (L/R)	4 – 1 side, 3 rear	
Back-Light System	4-wavelength	
Limited Warranty ^{*4}	1 year parts and labor	
Cabinet Color	Black	
Table Stand	Included	
Optional Wall Mount Brackets	AN-LCGWF, AN-52AG1	
Power Consumption AC	203 W	165 W
Power Source	120V	
TV Dimensions (wxhxd) (inches) TV with Stand and Speakers TV only	36-3/16 x 25-3/4 x 11-1/2 36-3/16 x 23-5/8 x 3-53/64	31-25/64 x 23-9/32 x 10-3/4 31-25/64 x 20-59/64 x 3-53/64
Net Weight (in pounds) TV with Stand and Speakers TV only	51.8 43.0	45.2 36.4
UPC	074000363922	074000363939

*1 Actual screen size 37-1/64" measured diagonally (37) and 31-1/2" measured diagonally (32).

*2 Contact your local cable or satellite service provider for available HDTV.

*3 The typical period of time after which the lamp's power output will have decreased by about half, given that the AQUOS is used continuously in a 77°F room under standard lighting and brightness conditions.

*4 See warranty statement included in the product operation manual available as a PDF download at www.sharpusa.com.

Sharp and AQUOS are registered trademarks of Sharp Corporation.

HDMI, the HDMI logo and High Definition Multimedia Interface are trademarks or registered trademarks of HDMI Licensing, LLC.

Product specifications and design are subject to change without notice.



06L092