

1U 17" Rackmount LCD Console - USB + PS/2

Product ID: RACKCONS1701



The RACKCONS1701 1U 17" Rack Mount LCD Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet space - providing complete KVM control right from a server rack.

Offering a durable, compactable 1U design, when the rack console is not in use it's as simple as folding the display like a laptop computer, and sliding it back into the server rack on the sturdy mounting rails (included). The included key lock provides an added security layer, helping to reduce unauthorized access to connected computers.

Offering consolidated control from a convenient location, the KVM rack console can be connected to virtually any multiport KVM switch, for control of multiple servers/computers, providing a scalable KVM control solution that lets you determine the type of KVM switch to use based on function and budget.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Centralized control of dozens of PCs and servers if used with optional KVM
- Managing cabinet mounted servers
- Improving the internal space efficiency of existing cabinets

Features

- Bright Active Matrix TFT Display
- Durable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan
- Supports both USB and PS/2 connected servers or KVMs

Hardware	Warranty	2 Years	
	Audio	No	
	Display Size	17in	
	Key Lock	Yes	
	KVM Ports	1	
	Number of Monitors Supported	1	
	Panel Type	Active Matrix TFT LCD	
	PC Interface	USB and PS/2	
	PC Video Type	VGA	
	Rack-Mountable	Yes	
	U Height	1U	
Performance	Aspect Ratio	Standard (4:3)	
	Brightness	250 cd/m ²	
	Color Depth	24-bit, 16.7M colors (Truecolor)	
	Contrast Ratio	1000:1	
	IP Control	No	
	Maximum Analog Resolutions	1280x1024 @ 60Hz	
	MTBF	60,000 Hours	
	On-Screen Display	Yes	
	Pixel Pitch Support	0.264 x 0.264 mm	
	Port Selection Support	Hotkeys and OSD (On Screen Display)	
	Response Time	5ms	
	Viewing Angle	170° (H), 160° (V)	
Connector(s)	Host Connectors	1 - USB Type-A (4 pin) USB 2.0 Female 1 - VGA (15 pin, High Density D-Sub) Female 2 - PS/2 (6 pin, Mini-DIN) Female	
	Software	OS Compatibility	OS independent; No software or drivers required
	Power	Center Tip Polarity	Positive
Input Voltage		115V-230V AC	
Power Source		AC Adapter Included	
Environmental	Operating Temperature	0 ~ 50 °C / 32 ~ 122 °F	
	Storage Temperature	20 ~ 60 °C / -4 ~ 140 °F	

Physical Characteristics	Cable Length	6ft (1.83m) Console Cable Kit
	Color	Black
	Enclosure Type	Heavy Duty Steel
	Maximum Mounting Depth	31.5 in [800 mm]
	Minimum Mounting Depth	21.7 in [550 mm]
	Product Height	1.8 in [45 mm]
	Product Length	20.9 in [530 mm]
	Product Weight	26.5 lb [12 kg]
	Product Width	18.9 in [480.8 mm]
Packaging Information	Shipping (Package) Weight	38.1 lb [17.2 kg]
What's in the Box	Included in Package	1 - 1U LCD Rack Console Drawer
		1 - Mounting Rails - Set
		1 - Console Cable Kit
		1 - Power Cord

Product appearance and specifications are subject to change without notice.