Specifications







Eaton TLP88DBTEL

Protect It! 8-Outlet Surge Protector - 5-15R Outlets, 2400 Joules, Telephone/Modem Protection, 8 ft. (2.4 m) Braided Cord, Black

General specifications	
PRODUCT NAME	Eaton Tripp Lite series Protect It surge protector
CATALOG NUMBER	TLP88DBTEL
UPC	037332294463
PRODUCT LENGTH/DEPTH	1.4 in
PRODUCT HEIGHT	12.3 in
PRODUCT WIDTH	3.7 in
PRODUCT WEIGHT	1.7 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	CSA C22.2. CSA Std. C22.2 UL Listed UL 1449
GLOBAL CATALOG	TLP88DBTEL
PRODUCT TYPE	Surge protector

Powering Business Worldwide

Product specifications

OPERATING TEMPERATURE	0° to 40°C
STORAGE HUMIDITY RANGE	0% to 90% RH
SURGE STYLE	ST - STRIP
SWITCHES	Combination AC circuit breaker and 2 position red illuminated on/off power switch
VOLTAGE COMPATIBILITY (VAC)	120
OUTLETS	8
CIRCUIT BREAKER	15
FREQUENCY RATING	50/60 Hz
DIAGNOSTIC LED DETAILS	Built-in LED confirms suppressor "protection present" (green) status
EMI / RFI FILTERING	Yes
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
OVERLOAD PROTECTION	15A resettable illuminated combo switch / circuit breaker
PROTECTION MODES	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
RECEPTACLE COLOR	BLACK
RECOMMENDED ELECTRICAL SERVICE	120V (110-125V)
STORAGE TEMPERATURE RANGE	5° to 104°F (-15° to 40°C)
TRANSFORMER ACCOMMODATION	Transformer Accommodation
UL1449 LET THROUGH RATING	500V
INPUT CORD DETAILS	SJT
INPUT CORD GAUGE (AWG)	14
CORD LENGTH	8 Foot
POWER CORD COLOR	Black
HOUSING COLOR	Black
OUTLET ORIENTATION	Single row of 7 outlets
MATERIAL	Plastic
INPUT PLUG TYPE	NEMA 5-15P
PRODUCT CATEGORY	Surge Protector

Resources

DRAWINGS	Submittal Drawing for TLP88DBTEL
FLYERS	Eaton Tripp Lite series EMI/RFI surge protectors flyer

OUTPUT RECEPTACLES	5-15R
PACKAGE CONTENTS	TLP88DBTEL 8-Outlet Surge Protector Owner's manual
INPUT NOMINAL VOLTAGE	120 VAC
PRODUCT FEATURES	Automatic Shut-Off Telephone/DSL Protection Mounting Holes or Slots Diagnostic LED(s) UL Certified
PRODUCT HIGHLIGHTS	8 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment 2400 joules protect your valuable electronics against dangerous surges and spikes On/off switch with circuit breaker allows one-touch control over connected equipment 8 ft. braided cord with NEMA 5-15P plug connects to compatible AC wall outlet Built-in RJ11 jacks allow protection of connected telephone, fax or modem Lifetime limited warranty (Worldwide) $85,000 Ultimate Lifetime Insurance (U.S., Canada and Puerto Rico only)
CHARGING PORT TYPE	USB A (FEMALE) USB C (FEMALE)
PLUG COLOR	White
AC SUPPRESSION JOULE RATING	2400
AC SUPPRESSION RESPONSE TIME	< 1 ns
CORD GAUGE TYPE	• 14 gauge • SJT
OPERATING HUMIDITY RANGE	20% to 85% RH
TOTAL OUTLETS	8

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.