Product data sheet

Specifications

Rack Mount, Security and Environmental Appliance, NetBotz, 750

NBRK0750

Overview

Presentation	The NetBotz Rack Monitor 750 provides integrated surveillance,sensing, access control, and advanced alerting for IT environmentsof all sizes, from single-rack edge networks to large data centers.
Lead time	Usually in Stock

Main

Product or Component Type	Industrial rack PC
Range of Product	Netbotz
Number of rack unit	1U
Communication Port Protocol	A-Link DHCP HTTPS IPv4 SNMP v1 SNMP v3 SSH v2 TCP/IP
Provided Equipment	Rack Mounting brackets Temperature/Humidity Sensor USB cable
Product Compatibility	Rack Sensor Pod 150 Room Sensor Pod 155

General

Camera Frame Rate	Up to 30fps
display resolution	Up to 1280x1024
APC Universal Sensors Supported	0-5V Door contact Dry Contact Humidity Smoke Fluid Spot Leak Temperature Vibration
Number of Universal Sensor Ports	6
Number of Sensor Pods Supported	12
Number of Universal Sensors Supported	78
Number of Cameras Supported	4

Physical

Color	Black

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	1.7 in (4.3 cm)
Width	17.008 in (43.2 cm)
Depth	7.008 in (17.8 cm)
Net Weight	5.40 lb(US) (2.45 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted
Mounting position	Horizontal

Conformance

Standards	CSA C22.2 No. 60950-1-03 FCC Part 15 class A ICES-003 UL 60950-1
Product Certifications	2014/30/EU AS/NZS 3548 (C-Tick) Class A CE EMC Directive 2004/108/EC VCCI Class A

Environmental

Ambient Air Temperature for Operation	32.0000000000…104.0000000000 °F (0…40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0…95 %
Ambient Air Temperature for Storage	5.0000000000…149.0000000000 °F (-15…65 °C)
Storage altitude	0…50000 ft (0.0000000000…15240.0000000000 m)
Storage Relative Humidity	0…95 %

Communications & Management

Communication Network Type	RJ-45 10/100/1000 Base-T

Ordering and shipping details

GTIN	731304344407

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.8 in (12.1 cm)
Package 1 Width	12.5 in (31.8 cm)
Package 1 Length	21.0 in (53.3 cm)
Package 1 Weight	9.19 lb(US) (4.17 kg)

Contractual warranty

Warranty	2 years

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.