


# Lexmark X945e



**LEXMARK**  
TM

# Lexmark X945e MFP

The Lexmark X945e MFP departmental network color multifunction solution includes print, color copy, fax and scan capabilities. The easy-to-use e-Task touch screen lets you easily automate document workflow processes.



## In the Box

### Lexmark X945e

- High Capacity Feeder
- 80+GB Hard Disk
- 13,000-page Black Toner Cartridge<sup>1</sup>
- Photoconductor Kit
- 12,000-page Cyan, Magenta and Yellow Toner Cartridges<sup>1</sup>
- Setup Sheets
- Software / Documentation CD
- Warranty Sheet
- Supplies Use and Return Flyer
- Phone cord
- Power Cord

## Product Specifications

Part Number	21Z0221
Product Class	Departmental Color Laser MFP
Speed	Black: Up to 45 ppm; Color: Up to 40 ppm
Time to First Page	Black: As fast as 5.2 seconds; Color: As fast as 10 seconds
Resolution	2400 Image Quality
Processor	1.25GHz
Memory (std./max.)	512MB/1024MB
Connectivity	
Standard	Gigabit Ethernet, USB, USB Direct Interface, 1 Internal Solutions Port
Optional	Wireless, Fiber Optic, Parallel, Serial
Printer Languages	PostScript 3 and PCL 6 emulations, PPDS Migration Tool
Direct Print Formats	PDF v1.6 emulation, HTML Direct Image Space, .jpg, .tif, .gif, .bmp, .png, .pcx, .dcx
Fonts	<b>PCL 6:</b> 89 scalable, includes OCR-A, OCR-B and Code 3 of 9 bar codes; 2 bitmapped; <b>PostScript:</b> 158 scalable; <b>PPDS:</b> 39 scalable, 5 bitmapped
Operating Systems	Windows, Linux, UNIX, Mac, NetWare and OS/400
Copy	Reduce/enlarge (25-400%), paper saver (2-up and 4-up), collation, darkness adjustment, original size to output size selection, copy select 1-999, date/time stamp, single-pass duplex, message overlay, priority copy (job interrupt), copy countdown
Fax	Speed: 33.6 bps max.; transmission speed: approximately 3 seconds per page; resolution: 200 x 100 dpi, 200 x 200 dpi, 300 x 300 dpi, 400 x 400 dpi; fax redirect, group fax, manual fax, fax from PC, up to 512-character shortcuts, fax preservation, LDAP lookup, Caller ID, speed dials, block junk faxes
Scan	Output resolutions: up to 600 x 600 dpi black, up to 300 x 300 dpi color; scan destinations: Network TWAIN, USB Direct Interface, e-mail, FTP, LDSS, Scan-to-PC; File Formats: TIFF, JPG, PDF; legal-size from flatbed; duplex scanning
Acoustics	<b>Printing:</b> 52 dBA; <b>Copying:</b> 53 dBA; <b>Scanning:</b> 54 dBA; <b>Idle:</b> 34 dBA
Size (WxDxH)	26 in. x 31.9 in. x 45.4 in. (650 mm x 810 mm x 1,153 mm)
Weight	383 lb. (173.7 kg)
Duty Cycle	200,000 pages per month

## Media Specifications


Paper Capacity (sheets)	
Standard	<b>Input:</b> 3,140 (3,040 + 100 MPF); <b>Output:</b> 400
Maximum	<b>Input:</b> 3,140 (3,040 + 100 MPF); <b>Output:</b> 3,500 (500 + 3,000)
Paper Sources	
Standard	<b>Input:</b> 5; <b>Output:</b> 1
Maximum	<b>Input:</b> 5; <b>Output:</b> 3
Media Information	
Types	Plain paper, paper labels, card stock, transparencies, envelopes
Size	Letter, Legal, Tabloid, A4, A5, A3, JIS B5, JIS B4, Executive, Folio, Statement, Universal (3.9 in. x 17 in. to 5.5 in. x 11.7 in.), envelopes (7 3/4, 10, DL, C5)
Weight	<b>Plain paper:</b> 17 to 28 lb. (60 to 220 g/m <sup>2</sup> ); <b>Card stock:</b> up to 110 lb. (220 g/m <sup>2</sup> )

## Shipping Dimensions

**Lexmark X945e MFP**  
26.1 in. x 36.4 in. x 58.3 in.  
476 lb.

## Part Numbers

<b>Supplies</b>	36,000-page Black Toner Cartridge <sup>1</sup> 22,000-page Cyan Toner Cartridge <sup>1</sup> 22,000-page Magenta Toner Cartridge <sup>1</sup> 22,000-page Yellow Toner Cartridge <sup>1</sup> Black Photoconductor Kit 3-pack Color Photoconductor Kit 30,000-page Waste Toner Box Advanced Booklet Staples Staple Cartridge, 3 pack Routine Maintenance Items 100,000-page Maintenance Kit 600,000-page Maintenance Kit 150,000-page ADF Maintenance Kit	X945X2KG X945X2CG X945X2MG X945X2YG C930X72G C930X73G C930X76G 21Z0357 25A0013 40X4031 40X4032 40X4033
<b>Memory Options</b>	128MB SDRAM 256MB SDRAM 512MB SDRAM 32MB Flash Card 64MB Flash Card	13N1523 13N1524 13N1526 1021208 1021209
<b>Warranty</b>	1-year Next Business Day Onsite Repair 1-year Next Business Day Onsite Repair extended warranty 2-year Next Business Day Onsite Repair extended warranty 3-year Next Business Day Onsite Repair extended warranty	Base 2349452 2349453 2349454



<sup>1</sup> Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798.

## Additional Part Numbers

<b>Solutions</b>	Traditional Chinese Font Card Simplified Chinese Font Card Japanese Font Card Korean Font Card Bar Code Card and Forms Card PrintCrypton™ Card Card for IPDS and SCS/Tne	1021242 1021241 1021243 1021240 21Z0367 21Z0370 21Z0368
<b>Connectivity</b>	Internal Print Servers <sup>1</sup> MarkNet N8030 Fiber Ethernet MarkNet N8050 802.11g Wireless External Print Servers <sup>2</sup> N4050e 802.11g Wireless Local Connections RS-232C Serial Interface Card Parallel 1284-B Interface Card	14S0220 14S0165 14T0145 1021092 1021091
<b>Cables</b>	6-foot USB Cable 10-foot Parallel Cable	1021294 1021231
<b>Media</b>	Glossy Paper (letter, 200 sheets) Professional Color Laser Transparencies (letter, 50 sheets)	12A5950 12A8240

## Terms & Conditions

Lexmark, MarkNet and Lexmark with diamond design are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. PrintCrypton is a trademark of Lexmark International, Inc. PCL is a registered trademark of Hewlett Packard Company. All other trademarks are the property of their respective owners. © 2007 Lexmark International, Inc. All rights reserved.

**71K1210**

<sup>1</sup> Use of Internal Print Server disables network card resident in printer.  
<sup>2</sup> Requires USB Connection.