Product data sheet

Specifications



StruxureWare Data Center Expert Basic Management Pack

AP9482

Overview

Presentation	StruxureWare Data Center Expert Basic Management Pack provides a complete, surveillance, environmental, and physical infrastructure monitoring solution. Includes: 1 NetBotz Room Monitor 355 (with 120/240V PoE Injector), 1 NetBotz Door Switch Sensor for Rooms or 3rd Party Racks - 50 ft, 1 StruxureWare Data Center Expert Basic appliance with 25-Node License, 1 StruxureWare Data Center Expert Basic Software Support Contract
Lead time	Usually Ships within 2 Weeks

Main

Number of rack unit	1U
Number of cables	2
Communication Port Protocol	DHCP DNS HTTP HTTPS Modbus SMTP SMS SNMP v1 SNMP v3 SSL TCP/IP
Provided Equipment	1 Node Surveillance License Key 25-Node license key Documentation CD Installation guide

Physical

Color	Black
Height	1.7 in (4.4 cm)
Width	21.5 in (54.6 cm)
Depth	15.0000000000 in (38.1 cm)
Net Weight	21.05 lb(US) (9.55 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Standards	UL 60950

Environmental

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature for Operation	50…95 °F (10…35 °C)
Operating altitude	0...10000 ft
Relative Humidity	5…90 %
Ambient Air Temperature for Storage	-31…140 °F (-35…60 °C)
Storage altitude	0…30000 ft (0.0000000000…9144.0000000000 m)
Storage Relative Humidity	5…95 %

Ordering and shipping details

GTIN	731304272496

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.008 in (30.5 cm)
Package 1 Width	31.0 in (78.7 cm)
Package 1 Length	24.8 in (62.9 cm)
Package 1 Weight	42.09 lb(US) (19.09 kg)

Contractual warranty

Warranty	2 years repair or replace

Sustainability

Green Premium^{TM} label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Take-back

Resource performance

Take-Back Program Available

Well-being performance

Reach Free Of Svhc

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration