

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC) - Red, 10M (33 ft.)

MODEL NUMBER: N320-10M-RD



Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- Red PVC jacket
- Length: 10 meter Connectors: LC connector on each end
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI)and OFNR rated

Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber with Red jacket
- Length: 10 meter Connectors:
 LC connector on each end
- Insertion loss testing performed on every connector (0.2dB typical)

System Requirements

 Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

Package Includes

10M Duplex MMF Cable LC/LC
 62.5/125 Micron Fiber Red
 Jacket

Specifications

OVERVIEW		
UPC Code	037332130808	
Technology	Multimode	
Optical Mode	OM1	
PHYSICAL		
Color	Red	
Clad Diameter	125 micron	
Core Diameter	62.5 micron	
Number of Fibers	2	
Cable Length (ft.)	32.8	
Cable Length (m)	10	





Cable Length (in.)	393.7
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.90
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.75
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.12
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side A - Connector 2	LC DUPLEX (MALE)
Side B - Connector 1	LC DUPLEX (MALE)
SPECIAL FEATURES	
Push/Pull Tabs	No
STANDARDS & COMPLIANCE	
Approvals	FDDI and OFNR rated
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies