Ortronics

Clarity Cat6a TracJack,T568A/B,8 pos, Orange 180 degree

Part No. TJ6A-43



Clarity 6A TracJack, ETL verified to TIA Category 6a component specification. Front-loading and front removable. Universal T568A/B wiring label and tapered wiring towers simplify termination. Tuned to Cat6a Clarity patch cords for optimum performance

Features & Benefits

ETL Verified to Category 6A component standard: Ensures standards compliance.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Center tuned design: Transparent interface with Clarity 6A/10G cords

Easy lace IDC housing: Reduces wiring time

Standard TracJack footprint: Fits in all TracJack faceplates and housings

Icon compatible, C6A marking on jack face: Supports 606 designation requirements

Specifications

General Info

Product Line	Ortronics	Color	Orange
UPC Number	662875855606	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	IEC-603-7 compliant, UL 1863, FCC part 68 Subpart F, 802.3bt Type 3 and Type 4, IEEE 802.3af / 802.3at, TIA-568.2-D
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes

Technical Information

Wire Gauge	22-24 AWG	Termination Style	110
Connector Type	RJ-45	Impedance	100 Ohm