

Dell™ Laser Printer 1710 & 1710n



DELL MAKES IT EASY TO BUY, USE AND OWN PRINTERS

Easy to Buy

- Dell Direct Advantage: Order online or through our professional sales team
- Exceptional performance for price
- Low total cost to purchase, operate and maintain

Easy to Use

- Pre-loaded drivers for quick plug-and-play setup (when ordered with a Dell system)
- Dell Toner Management System™ provides early warning of low toner level
- Dell Printer Web Tool (1710n only) for easy installation, configuration and management. See back for more details.

Easy to Own

- Convenient ink/toner ordering and delivery with Dell Toner Management System™
- Dell service & support staff
- 24x7 toll-free technical phone support



Dell Printer Web Tool for 1710n

Designed for easy installation, configuration and management of Dell network printers and consumables, this web-based tool can be set up to provide automatic e-mail notifications of printer, consumables and paper-handling alerts.

- Can be accessed using a standard web browser
- Doesn't require additional software installation
- Resides on printer hardware



The Dell Laser Printer 1710 series offers fast, affordable printing in a compact design. Choose the 1710 for direct attach printing from your computer or select the 1710n to share over your office network. Fast, up to 27 page per minute print speed (actual speed will vary with use) and up to 15,000 page monthly duty cycle make it ideal for a busy office environment.

The 1710 and 1710n offer a low total cost of printing, which includes initial purchase price, management and operation costs for the life of your printer. Dell allows you to save money with a low acquisition cost on hardware as well as a low toner cost per page. We also make it easy to manage and order supplies with the Dell Toner Management System™. In addition, both of these printers include peace of mind with a 1-year Next Business Day Advanced Exchange Service² and 24x7 toll free technical phone support.

The Dell Laser Printer 1710 & 1710n deliver:

Outstanding Performance

- Fast printing - up to 27 pages per minute (actual speed will vary with use)
- Sharp print quality - 1200 x 1200 dpi
- Ships with a Standard Capacity Toner Cartridge, up-to-3,000 page yield¹ and the optional High Capacity Toner Cartridge with an up-to-6,000 page yield¹ is available
- Durable, up to 15,000 page monthly duty cycle
- 1710n model adds networking, PostScript and an additional 16MB of memory

Easy Management

- Dell Toner Management System™ tells you when toner is low
- Dell Printer Web Tool for the 1710n

Quality Dell Service & Support

- 24x7 toll-free technical phone support
- One-year Next-Business-Day Advanced Exchange Service²
- Two-, three- and four-year Extended Service options
- Options include Next Business Day Onsite Service⁴, Printer Gold Technical Phone Support, Installation and Asset Tagging

Easy to Use

- Includes setup placemat for quick and easy installation
- Easy toner installation using drop-in cartridge design

Convenience - Easy to Buy Toner

- Dell Toner Management System™ Allows for easy toner level detection and ordering. There are many ways to check printer status and toner level:
 - 1. Printer:** Printer LED notifies you when toner is low
 - 2. PC:** Directly attached PC displays status alerts
 - 3. Network (1710n only):** Check printer status and toner level over the network with the Dell Printer Web Tool™
 - 4. E-mail (1710n only):** Alerts can be e-mailed to specified recipients notifying them of printer status and toner levels
- Direct link to website from Low Toner alert
- Or, order toner at www.dell.com/supplies
- 3-5 day shipping included at no additional charge⁵, overnight shipping available
- Environmentally friendly: Dell pays postage to return toner cartridges to Dell for recycling
- Lifetime limited toner cartridge warranty³

Dell Laser Printer 1710 & 1710n

FEATURES DESCRIPTION

Printer Type:	Monochrome laser
Printer Speed¹:	Up to 27 pages per minute (Actual print speed will vary with use)
Processor:	366 MHz
Memory:	16MB standard / 144MB max for 1710 32MB standard / 160MB max for 1710n
Monthly Duty Cycle:	Up to 15,000 pages per month
Max. Resolution:	1200x1200 dpi
Media Types:	Auto Feed: A4, A5, JIS B5, Letter, Legal, Executive, Folio, Statement, Universal Manual Feed: A4, A5, JIS B5, Letter, Legal, Executive, Folio, Statement, Universal, Envelopes
Paper Weight:	Auto Feeding Tray 1 / 2nd Drawer: 60-90 g/m2 (16-24 lb) Manual Feeding: 60-163 g/m2 (16-43 lb)
Media Sizes:	Max: 216 x 356 mm (8.5" x 14") Min: 76 x 127 mm (3" x 5")
Standard Input Tray:	Standard 250-sheet covered paper input drawer
Optional Input:	Optional 550-sheet paper drawer (15.59" x 14.75" x 5.06" (WxDxH))
Print Cartridges¹:	Ships with Standard Capacity Toner Cartridge, 3,000 pages. High Capacity Toner Cartridge 6,000 pages available
Print Languages:	PCL5e, PCL6, add PS3 for 1710n
Fonts Support:	1710 - 17 Scalable PCL fonts, 2 Bitmap, (17 PS Fonts - Mac only) 1710n - 89 Scalable PCL fonts, 89 Scalable PS fonts, 2 Bitmap
Connectivity:	USB & Parallel, add 10/100 Ethernet for 1710n
Minimum OS:	Microsoft® Windows® (Server 2000 & 2003, NT 4.0, XP, 2000, Me, 98, 98SE, XP 64 bit) MS Longhorn OS, RedHat® Linux® Enterprise 3.0, Suse Linux (7.x, 8.x), Novell NetWare (3.x, 5.x, 6.x TCP/IP only), Macintosh OS X, Citrix support (NT4.0, Win 2K & 2003 Server running Terminal Services w/ Citrix MF 1.8 or XP 1.0), SAP certification
Dimensions:	15.59" x 13.9" x 9.72" (WxDxH)
Weight:	22.4 lbs (including consumables); 19.95 lbs (excluding consumables); 26.5 lbs (with packaging)
Printer Management:	Dell Toner Management System™ intelligent toner monitoring proactively notifies you before you run out of toner, add Dell Printer Web Tool for 1710n
Power:	Printing Operation: 600w; Sleep Mode: 20W; Power cord included
Standard Service:	1 year, Next Business Day Advanced Exchange Service ² standard; 1 year 24x7 toll-free tech support
Humidity Range Operating:	Operating: 8 to 80% Relative Humidity; Non Operating: 8 to 95% Relative Humidity
Max/Min Operating Temperature:	Operating: 16 to 32°C (60 to 90°F); Non Operating: -20 to -40°C (-4 to 104°F)
Sound Emission:	Printing: Bystander Sound Pressure = 51dBA; Sound Power = 6.5 Bels Standby: Bystander Sound Pressure = 25dBA; Sound Power = 4.1 Bels
Certifications:	TAA compliance (1710n only), Section 508, Energy Star; RoHS compliant (lead-free) ⁷

RECYCLING MADE SIMPLE

Recycling printers and toner with Dell is easy and at no charge to the customer. Visit www.dell.com/recycling for details.



- Each Dell printer and toner cartridge includes instructions for returning products to recycle
- Dell "Use & Return" cartridges offer more savings per equivalent yield than our "Regular" toner cartridges⁶
- Dell provides packaging and postage for returning used cartridges at no charge to the customer



GET MORE OUT OF NOW. 

For more information visit www.dell.com

Dell cannot be responsible for pricing or other errors, and reserves the right to cancel orders arising from such errors. ¹ Toner yield based on printing pages with 5% page coverage in accordance with ISO/IEC 19752 testing methodology. Yields vary with usage and environmental conditions. ² Replacement part or unit will be dispatched if necessary following phone-based troubleshooting in advance of receipt of returned defective unit. Subject to parts availability, geographical restrictions and terms of service contract. Service timing dependent upon time of day call placed to Dell. Defective unit must be returned. Replacements may be refurbished. U.S. only. ³ For a copy of our guarantees or limited warranties, please write Dell USA L.P., Attn: Warranties, One Dell Way, Round Rock, TX 78682. For more information, visit http://www.dell.com/us/en/gen/misc/policy_010_policy.htm. ⁴ Service may be provided by third-party. Technician will be dispatched if necessary following phone-based troubleshooting. Subject to parts availability, geographical restrictions and terms of service contract. Service timing dependent upon time of day call placed to Dell. U.S. only. ⁵ Valid for Continental (except Alaska) U.S. only. ⁶ Use & Return cartridges are available for Dell's laser printers. Dell's Use & Return program is a printer toner cartridge discount program that avoids the hassle of traditional rebates. If you choose Use & Return, in exchange for the up-front discount you agree to use the cartridge only once, and to return the empty cartridge only to Dell for recycling. You don't have to choose Use & Return products if you want other recycling options. Use & Return saves you money on a new, top-quality product while helping keep materials out of landfills. Dell provides packaging and postage for returning empty cartridges for recycling. ⁷ Per the EU Restriction on certain Hazardous Substances directive, this product or configuration contains less than 0.1% lead by weight. Dell and the Dell logo are registered trademarks of Dell Inc. Microsoft and Windows are registered trademarks of Microsoft Corporation in the U.S. and other countries. Other trademarks and trade names are used to identify the entities claiming the marks and names of their products. Dell Inc. disclaims any proprietary interest in trademarks and trade names other than its own. © Copyright 2005 Dell Inc. All rights reserved.