


EPSON PERFECTION™ V200 PHOTO

Weight = Approx. 2.6kg



BASIC

SCANNER TYPE
OPTICAL RESOLUTION

Flatbed colour image scanner
Main 4800 dpi x Sub 9600 dpi

DOCUMENT SIZE

REFLECTIVE
TRANSPARENCY

216 x 297mm (A4 + Letter)
32.9 x 244.4mm
(35mm Strip film 6 frames, 35mm Slides 4 frames)

INTERFACE

USB2.0 Hi-speed

CONFIGURATION

PHOTOELECTRIC DEVICE

Alternate 12 lines colour CCD with Micro Lens
122,400 pixels (10,200 x 4 Line x 3 colours)

LIGHT SOURCE

White cold cathode fluorescent lamp

SUB-SCANNING METHOD

Fixed document and moving carriage

PERFORMANCE

OUTPUT RESOLUTION
COLOURS

50 - 6400, 9600, 12800 dpi
Internal 48 bit (281.5 trillion colours)
Output 48 bit (281.5 trillion colours)
24 bit (16.7 million colours)
16 bit (65,536 grayscale levels)
8 bit (256 grayscale levels)
1 bit Monochrome

SCANNING SPEED

REFLECTIVE SCANNING

MONOCHROME* 1

A4 600dpi	2.9 msec/line
A4 1200dpi	5.6 msec/line

24bit COLOUR* 2

A4 600dpi	2.9 msec/line
A4 1200dpi	11.0 msec/line

FILM SCANNING

35mm Positive film
35mm Negative film

	Draft Mode	Best Mode
4800dpi	84 sec	108 sec
4800dpi	103 sec	145 sec

FUNCTIONS

IMAGE QUALITY ENHANCER

PRINT Image Matching II
Image Enhancement function
Dust Removal for film, Color Restoration, Grain Reduction
Selectable tone of Auto Exposure
Unsharp Mask with Noise Reduction
De-Screening with Document Type Optimizer
Tone Curve Adjustment with Histogram

4 Easy Push Buttons
Multiple page scan to PDF with scanner buttons
Stand-Alone Application and Scan to File Feature
Multi Purpose User Interface
Multi Document Auto Detection
Multi Document Auto Cropping
Auto Skew Correction
Auto Photo Orientation
Multi Marquee
Film Scanning Thumbnail Preview

EASY SCANNING

SUPPORTED PLATFORMS

USB1.1 & 2.0

Microsoft® Windows® 2000 Professional/XP Home Edition/XP Professional
XP Professional x64 Edition/ Windows Vista™*
(Pre-installed model or upgrade of Windows® 2000 Professional pre-installed model)
Mac OS® X 10.2.8 or later

*USB2.0 Host Driver by Microsoft is required

ENVIRONMENTAL CONDITIONS

TEMPERATURE

10°C to 35°C (Operating)

HUMIDITY

10% to 80% without condensation (Operating)

ELECTRICAL SPECIFICATIONS

VOLTAGE

AC220-240V 50-60Hz

POWER CONSUMPTION

Approx. 0.5W (Power Off)
Approx. 16.5W (Operation)
Approx. 14.0W (Ready Mode)
Approx. 3.6W (Sleep Mode)

^To use the USB port, consult the documentation provided with your PC for further information about USB connectivity. Please note that errors may occur if non-standard cables or multiple hub connections are used.

Scanning Speed Data Pattern
The thumbnail images below show the scanning patterns used to determine scanning speed specifications.

System Configuration of Scanning Speed

CPU: Pentium 4, 3.2GHz

RAM: 1GB

I/F: USB2.0 Hi-Speed

OS: Windows XP Home Edition

Soft: Adobe Photoshop 7.0E



*1

Line Art (Memo)

*2

Photo (Photo courtesy of ISO/JIS-SCID, Reprinted by permission.)

Scanning speed test results vary according to system configuration, dpi setting, and scan mode setting. However, documents and photos other than those pictured above can be substituted without significantly affecting test results.

When scanning resolution is high, scanning size may be restricted.



EPSON is the registered trademark of Seiko Epson Corporation.


All other product names and other company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners.

EPSON disclaims any and all rights in those marks. Scan/Print samples shown herein are simulations. Specifications are subject to change without notice.



INDIA - (91) 80-305-15000, CALCUTTA - 228 31589/90,
CHENNAI - 302 77500, MUMBAI - 282 61515/16/17,
NEW DELHI - 306 15000
INDONESIA - (62) 21-572-3161
MALAYSIA - (60) 3-562-88288
PHILIPPINES - (632) 813-6567
SINGAPORE - (65) 6586-5500, (65) 6586-3111
THAILAND / INDOCHINA - (662) 685-9888

Dealer's Stamp



Printed in May 2007

SHEER, SIMPLE, SLEEK PERFECTION



- Sheer Performance - Improved photo enhancement features with EPSON Easy Photo Fix™
- Simple Execution - Multi-page PDF scanning for effortless digitisation of documents at a stunning resolution of 4800dpi
- Sleek Lines - Stylish Black ID with functional extendable lid for convenient and easy scanning

AN ENTICING COMBINATION OF FORM AND FUNCTION FOR THE HOME



EPSON PERFECTION™ V200 PHOTO

The EPSON Perfection™ V200 Photo packs sleek design with high tech scanning functionality for the home user.

Simply Remarkable

Accurately reproduce images and documents at high resolutions of up to 4800dpi and 3.2 optical density. Preserve your memories with film and photo scanning, capturing every detail with amazing clarity.




Effortless Film Scanning

User friendly film holder with a capacity of 6 frames of 35mm filmstrips or 4 frames of 35mm mounted slides comes in handy for the home user to digitise and back-up their collection of films/negatives.



Easy One-Touch Scanning

Start, Copy, Scan-to-Email and Scan-to-PDF with the 4 push buttons on the control panel.



Smooth Design

Designed to impress, this sleek and stylish scanner features a slim black casing standing at only 57mm.



The outstanding black and silver scheme makes it an exceptional addition to any home study.

Innovative Functionality

The extendable hinge, which opens fully at 180°, allows easy scanning of thick documents and 3D objects. With the lid closed, you can scan books/magazines of up to 25mm thickness effortlessly.



EPSON Easy Photo Fix™

True perfection comes from this powerful software that includes advanced Color Restoration feature that brings your old photos to life. Improved Dust Removal tool detects and removes image defects like dust and scratches, while the new Backlight Correction tool analyses and makes necessary adjustments to the brightness, sharpness and colour balance of each image.


Color Restoration



Dust Removal



Backlight Correction



Tools for Photo Perfection

Achieve more from your scans with the following bundled software:

EPSON Creativity Suite

Epson's photo software solution allows you to easily manage all your digital images for storing, viewing & sharing.



EPSON Scan Version 3.1

Intuitive scan interface with EPSON Easy Photo Fix™ that includes dust removal, color restoration & backlight correction features.



ArcSoft PhotoImpression™ 6

A creative photo editing software that includes automatic photo-enhancing features, text effects and a clip-art library.



ABBYY FineReader 6 Sprint Plus*

A powerful Optical Character Recognition software that recognises and converts the image of a text document to text format for easy editing through MS Word or MS Excel.



*Version 5 for Macintosh

Partners in Perfection



Unbeatable photos from EPSON Stylus™ Photo Inkjets & Photo AiOs at 5760 optimised dpi and Variable Sized Droplet Technology.



Epson specialty media is developed to complement Epson genuine inks to produce exceptionally high quality prints.



Epson inks are the highest quality inks you can use with an Epson printer. Years of research and development have gone into its formulation. The results are inks designed specifically to work with your printer to deliver stable, long-lasting, photographic quality.