Rugged Mobile Computing Solutions

K120
ACCESSORY SPEC BROCHURE



Getac (UK) Ltd.
Getac House, Stafford Park 12, Telford, Shropshire TF3 3BJ, United Kingdom
Tel : +44 (0) 1952 207 222 Sales-Getac-UK@getac.com | www.getac.com/en/

Copyright © 2026 Getac Technology Corporation and/or any of its affiliates. All Rights Reserved.

CARRY BAG

Features & Benefits

Constructed of durable Nylon/air mesh fabric and featuring an adjustable padded shoulder strap, this compact carry bag provides sturdy protection for your device while giving maximum comfort. The functional pockets inside offer the optimal solution to transport the laptop and needed accessories together in one case, delivering extra convenience and go-anywhere productivity to mobile professionals.

Product Information

Dimensions : L 405 x W 330 x D 100mm
Weight : 1.335kg
Main Material : Nylon, air mesh fabric

SKU ID

GMBCX7



DUAL BAY BATTERY CHARGER

Features & Benefits

This external dual-bay main battery charger is designed to charge up to 2 batteries at the same time. It provides you the benefit of charging and storing the 2 main batteries together when there is limited space and power sockets.

Product Information

AC Input : 100V~240V
DC Output : 13.05V, 2.4A Max.
Number of charge bays : 2 bays
Dimensions : L 160 x W 180 x H 72.5mm
Weight : 1.2kg
Support main batteries and high-capacity batteries.





SKU ID

GCMCEF (EU Power Cord)
GCMCUF (US Power Cord)
GCMCKF (UK Power Cord)
GCMCAF (AU Power Cord)
GCMCCF (CHN Power Cord)
GCMCTF (TW Power Cord)
GCMCIF (IN Power Cord)

MULTI-BAY BATTERY CHARGER EIGHT BAY

Features & Benefits

The 8-bay multi-battery charger is designed to charge multiple battery packs simultaneously and provide users an efficient charging solution.

Product Information

AC Input : 100V~240V AC, 4.2A 50~60Hz
DC Output : 19.5V, 16.9A
* w / 330W AC Adapter
Number of charge bays : 8 bays
Dimensions : L 465 x W 245 x H 95.3~111.3mm
Weight : 4.7 kg ,not including battery packs
Support main batteries and high-capacity batteries.

SKU ID

GCECEA (EU Power Cord)
GCECUA (US Power Cord)
GCECKA (UK Power Cord)
GCECAA (AU Power Cord)
GCECCA (CHN Power Cord)
GCECTA (TW Power Cord)
GCECIA (IN Power Cord)



STANDARD BATTERY 2100 MAH (1-PACK)

Features & Benefits

This battery pack is specifically designed for the K120, and can be hot-swapped for quick and simple battery replacement in the field without powering the unit down.

Product Information

Battery Type : Lithium-ion
Number of cell : 3S1P
Voltage : 11.1V
Capacity : Typical 2100mAh; min. 2040mAh
Dimensions : L 123.9 x W 91.2 x H 12.3mm
Weight : 160g

SKU ID

GBM3X4





OFFICE DOCK WITH AC ADAPTER (LAPTOP MODE)

Features & Benefits

The Getac office dock brings out multiple I/O ports for connecting essential peripheral devices in office environment. Through the integrated ethernet, RS232, or USB connections, users can quickly collect and synchronize field data with central offices for real-time reporting and analytics. The HDMI and VGA ports also provide a convenient solution for sharing presentations or worksheets from a larger screen.

Product Information

Dimensions :408 x 225.7 x 67.5 mm
Weight : 1.90 kg
Docking Connector : POGO
* w / 120W AC Adapter
I/O Interfaces : DC in Jack x 1, Audio Output x 1, Microphone x1, USB 2.0 x 2, USB 3.0 x3, LAN x 2, HDMI x 1, VGA x 1, Serial Port x 1, Kensington Lock x 1





SKU ID

GDODE6 (EU Power Cord)
GDODU6 (US Power Cord)
GDODK6 (UK Power Cord)
GDODA6 (AU Power Cord)
GDODC6 (CHN Power Cord)
GDODT6 (TW Power Cord)

OFFICE DOCK WITH AC ADAPTER (TABLET MODE)

Features & Benefits

The Getac office dock brings out multiple I/O ports for connecting essential peripheral devices in office environment. Through the integrated ethernet, RS232, or USB connections, users can quickly collect and synchronize field data with central offices for real-time reporting and analytics. The HDMI and VGA ports also provide a convenient solution for sharing presentations or worksheets from a larger screen.

Product Information

Dimensions : L 313.3 x W 203.3 x H 265.7mm
Weight : 1.45kg
Docking Connector : POGO * w / 120W AC Adapter
I/O Interfaces : DC in Jack x 1, Audio Output x 1, Microphone x1, USB 2.0 x 2, USB 3.0 x3, LAN x 2, HDMI x 1, VGA x 1, Serial Port x 1, Kensington Lock x 1





SKU ID

GDODE5 (EU Power Cord)
GDODU5 (US Power Cord)
GDODK5 (UK Power Cord)
GDODA5 (AU Power Cord)
GDODC5 (CHN Power Cord)
GDODT5 (TW Power Cord)

CAPACITIVE STYLUS & TETHER

Features & Benefits

This capacitive stylus is lightweight and easy to control, spring-loaded nib increasing the durability also allowing smooth and comfortable interaction with the touch screen without worrying about scratching the screen or leaving fingerprints on it. The stylus comes with a tether to keep it attached to the tablet to get lost or misplaced.

Product Information

Nib Material : Conductive PET Fiber
Stylus Dimensions : 108.7 mm ; Ø9 mm
Tip size : 2.7 mm ; Ø2.8 mm
Color : Black
Tether Length : 304 mm

SKU ID

GMPSXN
* MOQ : 5pcs



DIGITIZER PEN WITH TETHER

Features & Benefits

The digitizer pen provides a more accurate and easy way for data entry and handwritten signature. A shortcut button allows the right mouse button functionality when using the pen.

Product Information

Stylus Dimensions : 109mm ; Ø9mm
Tip size : 2.0mm ; Ø1.65mm
Tether Length : 292mm

SKU ID

GMPDX6



GETAC DS100 USB-C DOCKING STATION WITH AC ADAPTER

Features & Benefits

The Getac DS100 USB-C Docking Station, featuring a slim and compact design, seamlessly consolidates cables on the workstation. This allows users to swiftly create a personalized workspace and organize their daily office environment. Compatible with various Getac laptop and tablet models, it provides extra connectivity and multiple I/O ports for additional peripherals and data sources.With support for MAC Address Pass-Through, Wake-on-LAN (WoL), and PXE Boot, the DS100 aids IT administrators in maintaining a secure, efficient, and well-managed network infrastructure.

Product Information

Dimensions: L 207 x W 90 x H 34.1mm
Weight (without 135W AC Adapter): 372.4g (0.82lbs)
Power Cable Length: 1.8m
USB-C Upstream Cable Length: 1m
I/O Ports: DC in Jack x 1, USB 3.2 Gen 1 Type-A x 3,
USB 3.2 Gen 2 Type-C x 2, LAN x 1, HDMI 2.0 x 1, DisplayPort 1.4 x 2,
Kensington lock, Kensington nano slot
(For use in non-hazardous areas only)



SKU ID

GDDSE2 (EU Power Cord)
GDDSU2 (US Power Cord)
GDDSK2 (UK Power Cord)
GDDSA2 (AU Power Cord)
GDDSC2 (CHN Power Cord)
GDDST2 (TW Power Cord)
GDDSI2 (IN Power Cord)

SHOULDER HARNESS 4-POINT

Features & Benefits

This shoulder harness has four snap hooks which attach to the corner rings on the tablet, and can be easily detached as well. The harness is worn in a backpack style, allowing the tablet to be carried hands-free in front of the user at a belt level for easy accessibility. It also delivers optimal support and a comfortable fit during movement, thanks to its wide soft padding and adjustable straps.

Product Information

Dimensions : 1380 x 372mm
Main Material : Polyester

SKU ID

GMS4X4





KEYBOARD DOCK WITH RF PASS-THROUGH

Features & Benefits

Featuring 4-level red backlighting, 83 full-size keys and an integrated touchpad, the keyboard dock with a built-in rear handle allows for a user-friendly, laptop-like operation to minimize mistakes and increase the efficiency as you perform data-intensive tasks. It also carries a variety of I/O ports for connections to peripherals and other devices. Its Double-locking mechanism strengthens the tablet-keyboard connection and prevents the keyboard from accidentally falling off.

Product Information

Dimension : L 340.5 x W 327.5 x H 21mm
Weight : 1.43Kg
Structure : IP66; membrane
Drop : 4ft Layout : 83 keys
I/O Interfaces : USB-C charging port x 1, DC in Jack x 1,
USB 3.2 Type-A x 3, Giga Lan (RJ-45) x 1, HDMI x 1, Serial Port x 1,
Display Port X 1, RF antenna pass-through for GPS, WLAN and WWAN
Docking Compatibility : Compatible with K120 vehicle /office docks (laptop mode).



SKU ID

GDKBUN (US) GDKBFN (Canadian French) GDKBVN (Canadian French Government) GDKBBN (DE) GDKBCN (UK) GDKBDN (FR) GDKBEN (IT) GDKBGN (Traditional Chinese)	GDKBHN (RU) GDKBIN (AR) GDKBKN (KR) GDKBLN (PL) GDKBMN (Spanish) GDKBNN (FDNS) GDKBTN (TR) GDKBWN (International US)

GETAC RUGGED KEYBOARD

Features & Benefits

The Getac Rugged Keyboard is designed with VESA and AMPS mounting capability that allow it to be placed firmly in the vehicle. It has gone through vigorous test that comply with MIL-STD 810G and IP65. It also features with 88 full sized keys, red LED backlight with five levels of brightness and impressive key response that will truly enhance user experience.

Product Information

Dimension : 307.7 x 194 x 32 mm
Weight : 870g
Compatibility : Windows 10 Pro, Windows 11 Pro
Backlit : Red LED. five levels of brightness
Coiled Cable Length : USB 2.0 interface, 1.83m



SKU ID

Getac Rugged Keyboard	Getac Rugged Keyboard with Smart card and USB 2.0	Getac Rugged Keyboard with Smart card and LF/HF RFID
GDKBU9 (US) GDKBC9 (UK) GDKBB9 (DE) GDKBD9 (FR)	GDKBU6 (US) GDKBC6 (UK) GDKBB6 (DE) GDKBD6 (FR)	GDKBU7 (US) GDKBC7 (UK) GDKBB7 (DE) GDKBD7 (FR)

HARD HANDLE

Features & Benefits

The multi-functional hard handle offers extra mobility to field workers to grab-and-go when the situation requires.

Product Information

Dimensions: L 358 x W 34.6 x H 64 mm
Weight: 220g
Main Material: TPU & PC

SKU ID

GMHDX4





DETACHABLE KEYBOARD

Features & Benefits

Featuring 4-level red backlighting, 88 full-size keys and a Precision Touchpad (PTP), the detachable keyboard allows a more accurate and reliable pointer and gesture functionality. Specifically designed for highly mobile professionals who need to perform data-intensive tasks in their daily workflows. The double-locking mechanism strengthens the tablet-keyboard connection and prevents the keyboard from accidentally falling off.

Product Information

Dimension : L 340.5 x W 327.5 x H 21mm
Weight :1.25Kg
Structure : IP66, membrane
Drop : 4ft
Layout : 88 keys
I/O Interfaces : DC in Jack x 1
Docking Compatibility : NOT compatible with K120 vehicle /office docks (laptop mode).



SKU ID

GDKBUM (US)
GDKBFM (Canadian French)
GDKBVM (Canadian French Government)
GDKBBM (DE)
GDKBCM (UK)
GDKBDM (FR)
GDKBEM (IT)
GDKBGM (Traditional Chinese)
GDKBHM (RU)
GDKBIM (AR)
GDKBKM (KR)
GDKBLM (PL)
GDKBMM (Spanish)
GDKBNM (FDNS)
GDKBTM (TR)
GDKBWM (International US)

SPARE MAIN STORAGE WITH CANISTER

Features & Benefits

Getac Spare Main Storage with canister is designed to provide you the ease of installation and allow you to remove your confidential data when your device is sent for service.

Product Information

Capacity : PCIe NVMe 256GB/512GB/1TB/2TB
Dimension : L 110.1 x W 28.2 x H 5.7mm
Weight : 40g

SKU ID

GSSEX6 (256GB PCIe NVMe SSD)
GSSFX6 (512GB PCIe NVMe SSD)
GSSGX6 (1TB PCIe NVMe SSD)
GSSHX4 (2TB PCIe NVMe SSD)



65W USB-C AC ADAPTER

Features & Benefits

This adapter is designed to power the device and charge its internal battery from an AC power source.

Product Information

Input : 100V-240V, 50~60Hz, 1.6A
Output : 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3.25A
Dimensions : L 90 x W 51 x H 28.5mm
Weight : 220g ±15g
Input cable length : 1830mm
Output cable length. : 1500mm

SKU ID

GAT6U1 (US Power Cord)
GAT6E1 (EU Power Cord)
GAT6K1 (UK Power Cord)
GAT6A1 (AU Power Cord)
GAT6C1 (CHN Power Cord)
GAT6T1 (TW Power Cord)
GAT6G1 (AG Power Cord)



HIGH CAPACITY BATTERY 3450 MAH (1-PACK)

Features & Benefits

The high capacity battery pack extends the system run time up to two times compared to the standard battery pack, providing a great solution for mobile professionals who require extra battery life for all-day computing. It's also hot-swappable for quick replacement without interrupting the tablet's performance.

Product Information

Battery Type : Lithium-ion
Number of cell : 4S1P
Voltage : 14.4V
Capacity : Typical 3450mAh; min. 3300mAh
Dimensions : L 123.9 x W 115.4 x H 22.3mm
Weight : 260g

SKU ID

GBM4X4





ROTATING HAND STRAP WITH KICKSTAND

Features & Benefits

The rotating hand strap is designed to make using the tablet easier and more convenient to carry. The hand strap is adjustable to fit the majority of hand sizes and can be rotated 360 degrees to find the ideal viewing angle while on-the-go. It also includes a built-in kickstand that allows for handsfree usage on flat surfaces, providing more on-the-job flexibility.

Product Information

Hand Strap Dimension : 242 x 115mm
Main Material : PU

SKU ID

GMHRXN



SCREEN PROTECTION FILM MATTE FINISH

Features & Benefits

This screen protection film is cut precisely to fit the K120 tablet and is easy to install and remove without leaving sticky residue. With anti-glare coating, it not only protects the screen from the rigors of daily use, and helps to diffuse light on the screen and reduces glare, providing effortless readability for displayed information under common ambient lighting conditions.

Product Information

Dimensions : L 301.08 x W 191.32 x D 0.14mm
Main Material : PET

SKU ID

GMPFXJ



SHOULDER STRAP 2-POINT

Features & Benefits

This shoulder strap attaches via two holders at the back of the tablet and is adjustable to fit most body sizes for both cross-body and shoulder carry. With its durable, sturdy design, the strap not only provides a comfortable, grip-free carrying option of the tablet but also helps in avoiding accidental drops while on the move. The shoulder strap can also attach to the detachable keyboard (sold separately) via two D-rings on the built-in handle.

Product Information

Dimensions : 38 x 1530mm
Main Material : Polyester

SKU ID

GMS2X8



GETAC RUGGED KEYBOARD

Features & Benefits

The Getac Rugged Keyboard is designed with VESA and AMPS mounting capability that allow it to be placed firmly in the vehicle. It has gone through vigorous test that comply with MIL-STD 810G and IP65. It also features with 88 full sized keys, red LED backlight with five levels of brightness and impressive key response that will truly enhance user experience.

Product Information

Dimension : 307.7 x 194 x 32 mm
Weight : 870g
Compatibility : Windows 11 Pro
Backlit : Red LED. five levels of brightness
Coiled Cable Length : USB 2.0 interface, 1.83m



SKU ID

Getac Rugged Keyboard	Getac Rugged Keyboard with Smart card and USB 2.0	Getac Rugged Keyboard with Smart card and LF/HF RFID
GDKBU9 (US) GDKBC9 (UK) GDKBB9 (DE) GDKBD9 (FR) GDKBM9 (ES) GDKBF9 (Canadian French)	GDKBU6 (US) GDKBC6 (UK) GDKBB6 (DE) GDKBD6 (FR) GDKBM6 (ES) GDKBF6 (Canadian French)	GDKBU7 (US) GDKBC7 (UK) GDKBB7 (DE) GDKBD7 (FR) GDKBM7 (ES) GDKBF7 (Canadian French)

GETAC RUGGED KEYBOARD V2.0

Features & Benefits

The Getac Rugged Keyboard V2.0 features VESA and AMPS mounting for secure vehicle placement and complies with MIL-STD 810G and IP65 standards for extreme durability. The newly optimized 83-key layout integrates navigation keys to save space, while maintaining a five-level red LED backlight and impressive key response. It also introduces a dedicated Copilot key for instant AI access, empowering modern productivity.

Product Information

Dimension : 307.7 x 194 x 32 mm
Weight : 870g
Compatibility : Windows 11 Pro
Backlit : Red LED. five levels of brightness
Coiled Cable Length : USB 2.0 interface, 1.83m



SKU ID

Getac Rugged Keyboard V2.0	Getac Rugged Keyboard V2.0 with Smart card and USB 2.0	Getac Rugged Keyboard V2.0 with Smart card and LF/HF RFID
GDKBUT (US) GDKBCT (UK) GDKBBT (DE) GDKBDT (FR) GDKBMT (ES) GDKBFT (Canadian French)	GDKBUU (US) GDKBCU (UK) GDKBBU (DE) GDKBDU (FR) GDKBMU (ES) GDKBFU (Canadian French)	GDKBUV (US) GDKBCV (UK) GDKBBV (DE) GDKBDV (FR) GDKBMV (ES) GDKBFV (Canadian French)