Wallaby Self-Service Stands

Specifications			
Model	Wallaby Pro countertop stand - E989127 Wallaby Pro floor stand - E989314 + E989512 Wallaby Pro double-sided floor stand - E989314 + E989314 + E990151 Wallaby Pro wall-mounted atand - E989127 + E990079		
Color	Black / Silver		
Display Compatibility	22" Android I-Series 4* 22" Windows I-Series 2* 24" 2402L Touchscreen Monitor* 24" 2403LM Touchscreen Monitor* 27" 2702L Touchscreen Monitor* 27" 2703LM Touchscreen Monitor* *portrait orientations only		
Compute Compatibility	Backpack 4 (Android) ECMG4 (Windows 10) Intel NUC (max dimensions of 127 x 127 x 51mm with 94mm mounting hole pattern) 3rd Party PC's (max dimensions of 127 x 127 x 51mm with 75mm or 100mm VESA pattern)		
Printer Compatibility	Epson - TM-T88, M30, EU-m30, L90; Star - TSP654, TSP100, mC-Print3; Bixolon - SRP-350		
EMV Compatibility	Verifone - MX915 and M400 - E458992*, MX925 - E352169*, P400 - E990282 Ingenico RP457C (Bluetooth) – E710930*, RP457C (Audio Jack) – E586981*, LANE3000 - E990468, LANE5000 - E996512, LANE7000 - E990654, iSC250 - E458992*, RP757 – E920661*, iPP350/iPP320/iPP315 - E458797* MagTek eDynamo – E375343* Square Terminal - E458992* *not compatible with the ECMG4		
Dimensions	Countertop stand (E989127): 31.10" x 15.75" x 13.78" / 790 mm x 400 mm x 350 mm Floor stand w/o wheels (E989314 + E989512): 57.01" x 18.90" x 17.72" / 1448 mm x 480 mm x 450 mm Double-sided floor stand (E989314 + E989314 + E990151): 57.01" x 20.08" x 22.52" / 1448 mm x 510 mm x 572 mm Wall mount kit for countertop stand (E990079): 27.95" x 7.87" x 4.72" / 710 mm x 200 mm x 120 mm		
Shipping Dimensions	Countertop stand (E989127): 31.69" x 16.34" x 14.57" / 805 mm x 415 mm x 370 mm Floor stand base (E989512): 22.64" x 20.67" x 7.09" / 575 mm x 525 mm x 180 mm Floor stand top (E989314): 59.06" x 12.8" x 11.81" / 1500 mm x 325 mm x 300 mm Double-sided base for floor stand (E989705): 27.76" x 21.06" x 7.09" / 705 mm x 535 mm x 180 mm Wall mount kit for countertop stand (E990079): 28.54" x 8.46" x 5.51" / 725 mm x 215 mm x 140 mm		
Weight	Countertop stand (E989127): 40.79 lbs / 18.50 kg Floor stand (E989314 + E989512): 94.58 lbs / 42.90 kg Double-sided base for floor stand (E989705): 42.99 lbs / 19.50 kg Wall mount kit for countertop stand (E990079): 4.63 lbs / 2.10 kg		
Shipping Weight	Countertop stand (E989127): 47.40 lbs / 21.50 kg Floor stand base (E989512): 35.71 lbs / 16.20 kg Floor stand top (E989314): 69.45 lbs / 31.50 kg Floor stand for double-sided base (E989705): 46.05 lbs / 20.89 kg Wall mount kit for countertop stand (E990079): 5.95 lbs / 2.70 kg		
Temperature	Operating: 0°C to 40°C / 32°F to 104°F, when using the ECMG4 - 0°C to 35°C OR 32°F to 95°F; Storage: -20° C to 60° C (-4° F to 140° F)		
Humidity (non-condensing)	Operating: 20% - 80%; Storage: 10% - 90%		
ADA Compliant	Yes		
Warranty	2-year		
What's in the Box	Countertop stand (E989127): 1x countertop stand 1x assembly instructions power cables 2x Wi-Fi extension cables 4x printer paper chutes 1x filler plate 1x ADA plate (ADA keypad sold separately) (refer to MS drawing for full details)	Floor stand top (E989314) 1x floor stand top 1x assembly instructions power cables 2x Wi-Fi extension cables 4x printer paper chutes 1x filler plate 1x ADA plate (ADA keypad sold separately) (refer to MS drawing for full details)	Floor stand base (E989512) 1x base plate 2x wheel assemblies 6x M5x6 wheel mounting screws 8x M5x10 socket head mounting screws 4x M5x10 flat head mounting screws (refer to MS drawing for full details)

Ordering Information

Part Number	
E989127	Wallaby Pro countertop stand
E989314	Wallaby Pro floor top (requires floor base E989512 for complete Wallaby Pro floor stand)
E989512	Wallaby Pro floor base (requires floor top E989314 for complete Wallaby Pro floor stand)
E989705	Wallaby Pro double-sided base for floor stand (requires 2x floor tops E989314 and 1x floor base E990151 for complete Wallaby Pro double-sided floor stand)
E990079	Wallaby wall-mount kit (requires countertop stand E989127 for complete Wallaby Pro wall-mounted stand)
E989893	Wallaby Pro ceiling pole kit for floor stand
E991255	Wallaby Pro signage kit for floor stand with ceiling pole
E990854	Wallaby Pro backer board kit for floor stand or countertop stand
E990151	Wallaby Pro backer board kit for double-sided floor stand
E284334	Wallaby Pro assist button kit

Learn more about Elo at **EloTouch.com**.

Americas
Tel +1 408 597 8000
elosales.na@elotouch.com

Europe (EMEA)
Tel +32 16 930 136
EMEA.Sales@elotouch.com

Asia Pacific
Tel +86 (21) 3329 1385
EloAsia@elotouch.com

Elo reserves the right to change or update, without notice, any information contained herein; to change, without notice, the design, construction, materials, processing or specifications of any products; and to discontinue or limit production or distribution of any products. Elo, the Elo logo and Wallaby are either trademarks or registered trademarks of Elo Touch Solutions, Inc. All other trademarks are the property of their respective owners. © 2024 Elo Touch Solutions, Inc. All rights reserved. 24071AES00167