C2G

C2G
USB-C® to HDMI® Dongle Adapter Converter
Part No. CG-C2G30035



This USB-C to HDMI Dongle Adapter Converter is an easy and convenient solution for connecting an HDMI monitor to a USB-C computer in your home or office. This adapter converter carries a digital video signal, supports up to a 4K resolution and meets the requirements of high performance applications.

Avoid frustration by simply plugging the adapter into your computer, then attach to the existing HDMI cable from your monitor or projector. The portable, compact design also makes it easy to carry in a laptop bag when traveling or on the go.

This adapter converter automatically converts the digital USB-C signal to HDMI, supporting full HD up to a 4K resolution at 60Hz.

Additional Technical Specifications

SIGNAL SPECIFICATIONS

- Testing: 100% Functional Test at 4K/60Hz/4:4:4 Resolution with Standard AV Test Equipment

ELECTRICAL SPECIFICATIONS

- USB-C to HDMI Adapter Power Consumption: 396mW (120mA/3.3V)

PHYSICAL SPECIFICATIONS

- Operating Temperature: 0°C - 40°C (0% - 90%RH)
- Storage Temperature: -10°C - 60°C (0% - 90%RH)

PHYSICAL CHARACTERISTICS

- HDMI 19pin Female Connector: Solder Type, Contacts: Brass, Gold Flash, Housing: LCP, Black, Shell: Nickel Plated
- USB Type-C Male Connector: Solder Type, Contacts: Brass, Gold Flash, Housing: LCP Black, Shell: Nickel Plated
- Adapter Hood: Molded Black (Pantone/#Black 6C) PVC
- Color Band: Black (Pantone#Black 6C) 12 x 1.5mm
- 360º Solder to Connector Shell
- Product is CE Marked and Conforms to 2011/65/EU ROHS 2

Features & Benefits

Adapts a USB-C output to HDMI, so no need to purchase a new monitor	Dongle style adapter reduces strain, prolonging the life of the port
Plug-and-play, so no additional software or drivers needed	Adapter supports up to a 4K video resolution, so meeting attendees will be able to see the displayed content for improved comprehension and detailed decision making

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120300359	Country Of Origin	China
Application Sector	Residential, Commercial	Warranty Type	5-Year
Type	Active Device, Adapter, Converter		

Listing Agencies / 3rd Party Agencies

FCC Compliant	Yes

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	4K 60Hz, 4K
Data Transfer Rate	18 Gbps	Adapter Rear	HDMI Female
Adapter Front	USB-C Male	Operating Temperature	0 C, 40 C
Storage Temperature	-10 C, 60 C		