


Versatile All-in-One for superior home office convenience with High-Speed ADF and Ethernet connectivity. Print, copy, scan, fax and direct photo printing.

Office Range



The PIXMA MX700 is the solution for superior home office convenience to print, copy, scan and fax with High-Speed ADF and Ethernet connectivity. Fast printing with 30ppm black and 20ppm colour. Effortless copying, scanning and faxing with the auto document feeder for continuous reading of the originals. High resolution, microscopic ink dots and 4 efficient individual ink tanks ensure you produce quality documents and photos. Scan at up to 2400 x 4800 dpi. The PIXMA MX700 is the versatile All-in-One solution for superior home office convenience.



Key Features

As a Printer

- High quality photos and documents with 2 picolitre FINE print head technology and 4800 x 1200 dpi¹
- Fast document printing up to 30ppm in black and 20ppm in colour³
- Photo lab quality prints delivered in high speeds of approx 46 seconds³
- Direct photo printing using PictBridge or directly from compatible memory cards and mobile phones⁴
- Borderless printing up to A4⁵

As a Copier

- Faithfully reproduce copies as they are seen with the naked eye with Dual Colour Gamut Processing Technology
- Standalone copying without a computer
- Copy up to 30cpm black and 20cpm colour³

As a Scanner

- Scan high-quality photos and documents at up to 2400 x 4800 dpi

As a Fax

- Supports the Super G3 standards up to 33.6kpbs to enable plain paper colour faxes and PC faxes to be transmitted
- No need to worry if the ink or paper runs out while receiving a fax, high-capacity memory can store data for up to 100 pages
- Speed dialling allowing up to 40 numbers to be registered

Easy to use Software – Just 3 easy steps

- Easy-Photo Print EX produces optimised prints of both portraits and sceneries with Auto Image Fix technology

4800^{Maximum} dpi
2^{Minimum} pl



Quality images

4800 x 1200 dpi resolution and 2 picolitre FINE print-head technology for high quality photos and documents¹

Long Lasting Prints

Produce long lasting printed photos with a combination of Canon's genuine dye ink and genuine photo papers²

Automatic Document Feeder

Fast copying, scanning and faxing with the automatic document feeder for continuous reading of originals



ADF

30 20
Black Color
ppm

Fast Printing and Copying

Print and copy at up to 30ppm black and 20ppm in colour³

FAX



33.6Kbps

Professional Fax

Enables stand-alone plain paper colour faxes and PC faxes to be transmitted

SCAN



2400x4800dpi

Quality Scanning

Scan high-quality photos and documents at up to 2400 x 4800 dpi



Ethernet

Printer sharing – Ethernet

Supports wired LAN connections in addition to USB allowing the printer to be shared between multiple personal computers



4 Single Inks

Efficient Individual Ink Tanks

Individual ink tanks saving you time and money, also notifying you when the ink is running out



Quick Start

Quick Start

Quick Start feature allows operations virtually the moment the power is turned on



PIXMA – Print with Confidence

Canon's PIXMA range features FINE print-head technology which places microscopic ink droplets on the page with unparalleled accuracy and consistency. PIXMA delivers superior quality to photographic and document printing with unsurpassed speed and reliability.

PIXMA MX700


All-in-One Inkjet Printer

Canon
advanced simplicity®



PIXMA MX700 Technical Specifications	
Printer Functions	
Min. Ink Droplet Size ¹	2 picolitres
Printing Resolution ¹	4800 x 1200 dpi
Print Speed ³	Black Text : Up to 30ppm, Colour Text & Graphics : Up to 20ppm, 6"x4" Standard Borderless Photo : Approx. 46 secs
Ink Tanks	PGI-5BK, CLI-8C/CLI-8M/CLI-8Y
Ink Yield*	Borderless 6x4" photo
	Plain paper A4
Borderless Printing	6"x 4", 5"x 7", 8"x10", Letter, A4, Credit Card, Wide
Plain Paper Capacity	250 sheets
Supported Paper Sizes	A4, Letter, Legal, A5, B5, Envelopes(DL, COM10), 4"x6", 4"x8", 5"x7", 8"x10", Credit Card (54mm x 86mm)
Supported Paper Weights	Plain Paper: 64-105g/m ² . Canon specialty paper (max paper weight): approx 273g/m ² (Photo Paper Plus Double-sided)
Paper Types	Plain Paper
	Photo Paper
	Other
Camera Direct Printing ⁴	PictBridge
Memory Card Printing ⁴	Yes
Mobile Phone Printing ⁴	PictBridge
Copier Functions	
Speed	Black Text : Up to 30ppm, Colour Text & Graphics : Up to 20ppm
Multiple Copy	Up to 99 copies
Reduction/Enlargement	25% to 400%
Special Copy Functions	Fit-to-page
Scanner Functions	
Scanner Type	CIS
Scanning Resolution	2400 x 4800 dpi
Special Scanning Functions	Push Scan
Fax Features	
Transmission Speed (Mono)	Approx. 3 sec. (33.6kbps)
Modem Speed	Super G3 standards up to 33.6kbps
Fax Memory	Approx. 100 pages
Speed Dials	40 locations
PC Faxing (Windows only)	Available
General Features	
Colour LCD Screen	1.8 inch
Automatic Document Feeder	Available
Dual Paper Path	Available
PC Interface Type ⁶	USB 2.0 Hi-Speed
Operating System	PC: Windows Vista/XP/2000, Mac: OS.X (10.2.8 or later)
Included as Standard	PIXMA MX700 All-in-One printer, Setup CD-ROM and printed documents, 4 Canon genuine ink tanks, print head, sample photo paper, telephone line cable, power cord and 12 month warranty card
Software Included	Easy-PhotoPrint EX, MP Navigator EX, ScanSoft OmniPage SE and Presto! Page Manager
Power Source	AC 100-240V, 50/60Hz
Power Consumption	Max: 17W (copying), Standby: 2.4W
Min. Dimensions (W x D x H)	480 x 463 x 239 mm
Weight	Approx. 10.4kg

Consumables



* Ink yield calculation is based on printing Canon 24 standard digital images on Photo Paper Plus Glossy (6" x 4" borderless print) with default settings in Windows XP driver and printing on Plain Paper (A4-ISO/IEC 24712). The figure above is an average value, measured when printing continuously using the ink immediately after it is unsealed, until the ink is out. Ink yield may vary depending on photos/documents printed, applications software used, print mode and type of paper used. This should be used as a guide only and does not take into account ink that might be used for head cleaning or head refreshing to maintain printer performance. Please visit our website for further details.

Subject to change without notice

Disclaimers

- Ink droplets can be placed with a pitch of 1/4800 inch at minimum.
- Up to 100 Years' Life in a Photo Album when printed with ChromaLife100 ink on selected Canon photo papers. Kept in a photo album, shut out light and air (gas), temperature 23 degrees and 50% humidity. Predicted value from the accelerated test. Result may vary based on individual environmental factors. For more information, please visit canon.com.au/ChromaLife100
- Print and copy speed dependent on system configuration, image/document complexity, type of paper used, software, print mode and does not take into account data processing time on host computer.
- PictBridge camera direct and mobile phone printing requires PictBridge compatible digital cameras and phones in order to function. Check with your digital camera manufacturer or users guide to determine PictBridge compatibility. Compatible memory cards include CompactFlash®, Microdrive, SmartMedia®, Memory Stick®, Memory Stick PRO™, SD Card™ and MultimediaCard® (v3.31). Note: xD-Picture Card™, Memory Stick Duo™, Memory Stick Pro Duo™, miniSD Card and RS-MMCTM (v3.31) can only be used with the addition of a special adaptor sold separately - ask your memory card supplier.
- Supported paper types for borderless printing: Photo Paper Pro, Photo Paper Plus Glossy, Photo Paper Plus Glossy II, Photo Paper Plus semi-gloss, Glossy Photo Paper, Matte Photo Paper, Photo Paper Plus Double-sided
- USB 2.0 Hi-Speed performance requires Windows Vista, Windows XP with Service Pack 1 or Windows 2000 with Service Pack 4 with pre-installed USB 2.0 Hi-Speed port.

canon.com.au