

## CHERRY G86-71400



Models may vary from the image shown

### Full-sized multifunctional keyboard with enhanced 131 position key layout

### Key benefits

- Full size keyboard with QWERTY layout
- Enhanced US 131 position key layout
- Robust product design with IP 54 spill and dust resistant key field for harsh environments
- Plug & Play configuration for all common POS features
- Unique function enhancement with "CHERRY Tools" virtual programming
- Fully programmable keyboard with 42 relegendable keys for easy layout configuration and quick function calls
- Option for unlimited programmability of all keys up to 3 layers provides convenient data access
- "Moving of Key" allows for easy key position exchange including modifier functions
- 131 programmable keys
- Powerful "CHERRY Tools" configuration software allows for quick product set up and configuration
- Easy configuration file transfer with Windows Explorer
- Comprehensive UPOS support for Windows and Linux client-server architectures
- Remote network installation with CHERRY Tools Activator
- Yellow status LEDs
- Accessory kit available to reconfigure key layout

### Technical Data:

#### Layout (country or language):

(possible country/layout versions, others available on request)  
US English

#### Housing color:

Product dependant, see table "Models"

#### Key color:

Product dependant, see table "Models"

#### Weight (product):

approx. 1500 g / approx 3.3 lb

#### Total weight (with packaging):

approx. 1700 g / approx. 3.7 lb

#### Cable Length:

approx. 1.85 m / approx. 6.07 ft

#### Storage Temperature:

-20°C to 60°C / -4° F to 140° F

#### Operating Temperature:

0°C to 50°C / 32° F to 122° F

#### Current Consumption:

typ. 35 mA

#### Interface:

- USB

#### Product approvals:

- cURus
- c-tick
- GOST-R
- VCCI
- CE
- FCC
- WHQL
- RoHS



#### Delivery Volume:

- CHERRY G86-71400
- Printed instructions
- Key removal device
- 2 pluggable feet

#### Dimensions (product):

442 x 183 x 33 mm / 17.4 x 7.2 x 1.3 in

#### Packaging dimensions:

496 x 248 x 45 mm / 19.4 x 9.8 x 1.8 in

#### Keyboard:

- Key technology: ATK
- Protection class: IP54
- Service life, standard key: 25 million key operations
- Inscription technology: Laser
- Number of Keys: 131
- Number of programmable keys: 131
- Number of relegendable keys: 42

#### Packaging Unit:

- Number of products in the master package: 22
- Number of master packages per pallet: 8

#### Warranty:

3-year limited manufacturer's guarantee

Errors, technical changes and delivery possibilities excepted.  
Technical information refers only to the specifications of the  
products. Features may differ from the information provided.

**Models:**

(possible country/layout versions, others available on request)

	<b>Product name</b>	<b>Order number</b>	<b>Housing color</b>	<b>Key color</b>
1	CHERRY G86-71400	G86-71400EUADAA	black	black
2	CHERRY G86-71400	G86-71400EUAEEAA	light grey	light grey