HAVIS DOCKING STATIONS FOR DELL 10" LATITUDE 7030 RUGGED EXTREME TABLET

DS-DELL-1100 SERIES



OPTIMIZING EFFICIENCY FOR PUBLIC SAFETY PROFESSIONALS

- Optional port replication with Advanced or Standard content
- Side-mounted USB 3.0 port
- LED power indicator
- One-handed docking & undocking
- Spring-loaded connector head
- Options for internal or external power supplies available
- Access to all tablet buttons & ports when docked
- Compatible with accessories, including all handles, magnetic mount, hand & shoulder strap
- Compact & lightweight
- Integrated cable management system
- Integrated VESA 75 mounting pattern

HAVIS DOCKING STATIONS FOR DELL 10" LATITUDE 7030 RUGGED EXTREME TABLET

DS-DELL-1100 SERIES

DELL 7030 TABLET SOLUTION

- Compact design with one-handed docking & undocking
- Advanced or basic port replication (optional)
- Non-isolated internal or external power supply (optional)
- LED power indicator



PART NUMBER	ETHERNET	USB-C	USB 3.0	HDMI	POWERED SERIAL	POWER INPUT	PASS-THRU ANT	ANT TYPE	EXT POWER	INT POWER
DS-DELL-1101	1	1 REAR	2 REAR 1 SIDE		1 @ 5V	9-36V				NON-ISO
DS-DELL-1102	1	1 REAR	2 REAR 1 SIDE	1	1 @ 5V	9-36V				NON-ISO
DS-DELL-1103										
DS-DELL-1104	1	1 REAR	2 REAR 1 SIDE		1 @ 5V	19.5V*				
DS-DELL-1105N	1	1 REAR	2 REAR 1 SIDE		1 @ 5V	19.5V			INCL.	
DS-DELL-1107	1	1 REAR	2 REAR 1 SIDE	1	1 @ 5V	19.5V*				
DS-DELL-1108N	1	1 REAR	2 REAR 1 SIDE	1	1 @ 5V	19.5V			INCL.	

* REQUIRES AN EXTERNAL HAVIS-APPROVED DC POWER SUPPLY

SPECIFICATIONS:

Height: 9.14-in (23.22 cm)
Width: 9.5-in (24.13 cm)
Depth: 3.45-in (8.7 cm)
Weight: 2.26 lbs (1.03 kg)

CERTIFICATIONS & TESTING:

UL Safety (pending)
CE Certified; RoHS Compliant
Vibration Testing: MIL-STD 810H 514.8
Impact Test: SAE J1455 30mph Crash Testing
Cycle Test: Latch Handle & Docking Connector Connectors Mechanism 30,000 cycles
Environmental Testing: Hot/Cold Operational & Storage