

PJ551D

LIGHT, BRIGHT AND PORTABLE PROJECTOR

with BrilliantColor™

Rich, vibrant digital images.

The ViewSonic® PJ551D is a DLP® projector that offers great value and performance in a portable six-pound package. Featuring 2,300 lumens, an ultra-high 2000:1 contrast ratio and BrilliantColor™ the PJ551D delivers RICH, VIBRANT IMAGE REPRODUCTION. Presenters will appreciate the VERTICAL KEYSTONE CORRECTION for easy image adjustment and the DIRECT OFF FEATURE that allows you to turn it off and go, no more waiting for a long cooling cycle. The Kensington® security port deters unauthorized projector removal from classrooms or media carts. The PJ551D is equally at home in the office or the classroom.



FULL-FEATURED, VALUE-PRICED PERFORMER

- > **Bright in virtually any setting with 2,300 lumens**
Packs 2,300 lumens in just 6 pounds. It's the bright choice for mobile presenters.
- > **BrilliantColor™ technology**
DLP® projectors with BrilliantColor™ feature multi-color processing to produce nearly 50% brighter colors for a vibrant image on the screen that won't fade over time.
- > **Supports HD signals including 720p and 1080i**
Capable of displaying HDTV signals as well as other video and data sources.*
- > **Multiple color correction modes**
Blackboard, greenboard and whiteboard modes give you the best possible picture regardless of the projection surface.
- > **OnView® controls for superior screen adjustability**
Screen geometry and color adjustments are precisely made via an easy-to-use on-screen menu.
- > **Eco-mode extends lamp life**
Extend the life of your lamp up to 4,000 hours** and reduce noise output.
- > **My Screen Startup**
Customize your startup with a company logo or favorite picture using the MyScreen function.



VIEWSONIC
PRODUCTS, PROGRAMS,
AND SERVICES

ViewSonic®
See the difference® 

PJ551D

LIGHT, BRIGHT AND PORTABLE PROJECTOR WITH BrilliantColor™



Optional Accessories

- Replacement lamp..... RLC-034
- Soft case with wheels..... CASE-006
- Extended Express Exchange® PRJ-EE-05-03
- Universal ceiling mount kit WMK-005
- VGA to component video adapter... ADPT-002
- Wireless G Presentation Gateway.... WPG-150



ViewSonic Corporation's QMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by the British Standards Institution.

Sales: (888) 881-8781 • SalesInfo@ViewSonic.com • ViewSonic.com

*Optional cables required. **Running eco-mode exclusively can extend lamp life. ***See ViewSonic.com for full details. †Adapter may be required. Analog adapter available from ViewSonic. DLP® and the DLP logo are registered trademarks of Texas Instruments and BrilliantColor™ is a trademark of Texas Instruments. Specifications subject to change without notice. Selection, offers and programs may vary by country; see your ViewSonic representative for complete details. Corporate names, trademarks stated herein are the property of their respective companies. Copyright © 2008 ViewSonic Corporation. All rights reserved. [13867-01B-03/08] PJ551D-1

PROJECTOR	Type	0.55 DDR DMD, DLP®
	Pixel Format	1024x768 XGA
	Lens	Manual zoom, manual focus
	Zoom Factor	1.1
	Keystone	Vertical ± 40°
DISPLAY	Size	27.2"–250" (diagonally)
	Throw Distance	47.2"–393.7"
	Throw Ratio	1.97–2.16:1
	Lamp	180W, 3,500 hrs. normal, up to 4,000 hrs. eco-mode**
	Brightness (max)	2,300 ANSI lumens
	Contrast Ratio	2,000:1
	Aspect Ratio	4:3 (native), 16:9
INPUT SIGNAL	Computer and Video	RGB analog, NTSC, NTSC 4.43, PAL, SECAM, HDTV (480p, 720p, 1080i)
	Frequency	F _H :31–79kHz; F _V :56–85Hz
COMPATIBILITY	PC	Analog: from VGA up to SXGA (scaled)
	Mac®†	Analog: up to SXGA
CONNECTOR	RGB (input)	15-pin HD, D-sub
	Composite Video (input)	RCA jack
	S-video (input)	Mini-Din 4-pin
	Component Video (input)	VGA DB-15 to HDTV/component cable*
POWER	Voltage	100–240VAC, 50–60Hz (universal)
	Consumption	250W (typ)
CONTROLS	Basic	Standby/on, input, menu
	OnView®	Display mode, brightness, contrast, keystone, aspect ratio, blank screen, gamma, white peaking, color temperature, user color, video (sharpness, saturation, tint), display (phase, tracking, H. position, V. position), advance (auto source, select, rear, ceiling, eco-mode, lamp hours, lamp reset, auto shutdown, OSD timeout, menu position, factory reset)
OPERATING CONDITIONS	Temperature	32–104°F (0–40°C)
	Humidity	10–90% (non-condensing)
	Altitude	0–10,000 ft.
NOISE LEVELS	Normal	34 dB (typ)
	Eco-mode	32 dB (typ)
DIMENSIONS	Physical (W x H x D)	10.8" x 4.3" x 8.8" (275mm x 109mm x 223mm)
WEIGHT	Net	6.0 lb. (2.7 kg)
	Gross	13.0 lb. (5.9 kg)
REGULATIONS		UL/cUL, FCC-B, CE, CB, CCC, NOM, C-TICK, ICES 003, TUV/GS, GOST-R, HYGIENIC, SASO, UKrSEPRO, RoHS
RECYCLE/DISPOSAL		The lamp in this product contains mercury. Please dispose of in accordance with local, state or federal laws.
PACKAGE CONTENTS		Projector, power cable, VGA cable, remote control with batteries, lens cap, Quick Start Guide, ViewSonic Wizard CD (with User Guide)
WARRANTY		3-year limited warranty on parts and labor, 1-year limited warranty on lamp, 1-year free Express Exchange® service.***

ViewSonic®
See the difference® 

For more product information, visit us on the web at ViewSonic.com