



DISPLAY

Size: 19" Widescreen Active Matrix TFT display
Resolution: 1440 x 900 WXGA+
Color: 16.2 Million
Pixel Pitch: 0.283(H)mm x 0.283(V)mm
Brightness: 300 cd/m²
Contrast: 700:1
Response Time: 5ms
Viewing Angle (H/V): 170°/160°
Panel Treatment: Anti-glare Hardcoating

INTERFACE

Analog Input: (1) D-Sub 15 Pin (VGA)
Audio Input: (1) 3.5mm Stereo

CONVENIENCE

Color: Black
Audio: 1W x 2 Channel Built-In Stereo Speakers
Tilt Stand: 0° - 20°
Mounting: VESA Standard Mounting Points
Kensington Lock
OSD in 11 languages

GO BEYOND

POWER

Input Voltage: 100VAC - 240VAC, 50/60Hz Autodetect
Power Consumption: 42W Maximum

WEIGHTS & DIMENSIONS

Net Dimensions: 17.8"W x 7.8"D x 14.6"H
Net Weight: 9.7 lbs
Shipping Dimensions: 20.5"W x 5.8"D x 17.7"H
Shipping Weight: 12.6 lbs
EAN Code: 4710859553669
UPC Code: 842651000561

WARRANTY

3 Year Limited Warranty

INCLUDED ACCESSORIES

(1) User Manual CD-ROM, (1) D-Sub 15 Cable(VGA)
(1) Power Cable, (1) Quick Start Guide, (1) Audio Cable

CERTIFICATIONS

FCC; UL; C-UL; CE; BSMI; CB; TUV; NOM
TCO'03; EPA Energy Star; WINDOWS VISTA



© 2007 HANN S·G Specifications and design are subject to change without notice. Non-metric weights and measurements are approximate. All brand, product, service names and logos are trademarks and/or registered trademarks of their respective manufacturers and companies. Screen shots are simulated.

See our entire product line up at
www.hannsg-usa.com
or email us at sales@hannsg-usa.com for more information

Always the best, always innovative and
Always going beyond- that is **HANN S·G**

Ref#: HMB070209-158