

Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), Black, 1 ft. (0.31 m)

MODEL NUMBER: N201-001-BK



Features

- Premium cabling for category 6, category 5e and category 5 applications
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- Length: 1-ft./Color: black/Connectors: RJ45 male
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- PVC 4-pair stranded UTP
- Deliver stable performance up to 550MHz/1 Gbps

Specifications

OVERVIEW		
UPC Code	037332141163	
Technology	Cat6	
PHYSICAL		
Color	Black	

Highlights

- Premium cabling for Category 6,
 Category 5e and Category 5
 applications, rated for 550
 MHz/1 Gbps communications
- Designed to meet Category 6 specifications; reduces crosstalk and return loss
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- Features boots with integral strain-relief and RJ45 (Male) connectors

System Requirements

For 1000 Base-T (1Gbps
 Ethernet), 10/100 Base-T
 (Ethernet), 100 Mbps TPDDI,
 155 Mbps ATM, ISDN, voice
 and Token Ring TYPE 3
 applications as well as EIA/TIA
 applications.

Package Includes

1-ft. Cat6 Gigabit Black
 Snagless Molded Patch Cable





Cable Shielding	UTP
Cable Jacket Material	PVC
Cable Jacket Rating	СМ
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	24 AWG
Cable Length (ft.)	1
Cable Length (m)	0.3
Cable Length (in.)	12
Cable Length (cm)	30.5
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.07
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
Maximum Data Rate	1Gbps
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Type	Molded; Snagless
Wiring Configuration	EIA/TIA 568B
FEATURES & SPECIFICATIONS	
Cable Style	Unshielded; Molded; Snagless
SPECIAL FEATURES	
IP68 Rated	No
Snagless Connector	Yes
Antibacterial	No
STANDARDS & COMPLIANCE	Davis
Certifications	ROHS



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies