2-Port Compact USB KVM Switch with Audio and Cable

MODEL NUMBER: **B004-VUA2-K-R**

Highlights

- Fast, easy switching via keyboard hot keys, push buttons or software (not required)
- PC and Mac compatible
- Allows sharing of audio components between systems; listen to music from one computer while switching to the other computer
- Compact design saves desk space
- No AC adapter required
- (x2) 6-ft. (1.83 m) USB KVM Cable kits and (x2) 6-ft. (1.83 m) 3.5mm Audio Cable kits included
- Compatible with all major operating systems

System Requirements

- Console: VGA, SVGA or Multisync Monitor, USB Keyboard and USB Mouse
- Computers: VGA, SVGA or Multisync Monitor Port and USB Port
- Audio (Optional): Speakers with standard 3.5 mm Connectors and a computer with 3.5mm ports
- Compatible with all major operating systems

Package Includes

- Compact 2-port USB KVM Switch with Audio
- (2) 6-ft. (1.83 m) USB KVM Cable Kits and (2) 6-ft. (1.83 m)

Features

- Fast, easy switching via keyboard hot keys, push buttons or software
- Plug-and-play setup - no software required
- Hot-swap capability allows easy addition or removal of computers without powering down the switch or other computers
- Speaker and microphone connections allow sharing of audio components between systems (standard 3.5 mm audio connections)
- Independent audio switching allows you to listen to audio from one computer while switching to the other computer
- Supports video resolutions up to 2048 x 1536 (standard 15-pin VGA connectors)
- Supports Microsoft® IntelliMouse® and the scrolling wheel on most mice]
- Compact design saves desk space
- Does not require an AC adapter
- Compatible with all major operating systems
- Includes two, 6-ft. (1.83 m) Cable Kits

3.5mm Audio Cable Kits

- CD-ROM with KVM Switcher Software
- Owner's Manual with Warranty Information

Specifications

OVERVIEW	
UPC Code	037332140043
Console	No
Max CPU	2
Technology	USB; VGA/SVGA; Stereo Audio

VIDEO	
Max Supported Video Resolution	2048 x 1536 @60Hz

AUDIO	
Audio Specification	Stereo Audio

INPUT	
Bus Powered	Yes

USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Selected PC)

PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	7.62 x 20.07 x 19.81
Shipping Dimensions (hwd / in.)	3.00 x 7.90 x 7.80
Shipping Weight (kg)	0.82
Shipping Weight (lbs.)	1.80
Unit Dimensions (hwd / in.)	1.3 x 4 x 2.6
Unit Packaging Type	Box
Unit Weight (kg)	0.10

Unit Weight (lbs.)	0.22

ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0%-90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
Power Consumption (Watts)	0.5

COMMUNICATIONS	
IP Remote Access	No

CONNECTIONS	
Ports	2
PC/Server Connections	USB; VGA
Side A - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	(2) USB A (FEMALE)
Side B - Connector 3	(2) 3.5MM (FEMALE)
Side B - Connector 4	(2) USB MINI-B 5-PIN (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	VGA
Connector Plating	Nickel

FEATURES & SPECIFICATIONS	
Autoscan (Y,N)	Y
Autoscan Duration	10 - 60 seconds
Number of Users	1
NIAP-Certified Secure	No
On-Screen Display (OSD)	Yes
Port Selection	Pushbutton; Hotkey; Software
USB Specification	USB 2.0 (up to 480 Mbps)
Cat5 KVM Switch	No

STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty