



Heavy-Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P005-010









Computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 10 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other EquipmentThis IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, servers and other network devices
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 10-ft. (3.05 m) away in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

 P005-010 Heavy-Duty C13 to C14 PDU-Style Power
 Extension Cable, 10-ft. (3.05 m), Black

Specifications

OVERVIEW	
UPC Code	037332140906





Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU	
Country/Region	North America	
INPUT		
Maximum Input Amps	15	
Voltage Compatibility (VAC)	100-250	
PHYSICAL		
Color	Black	
Number of Conductors	3	
Wire Gauge (AWG)	14	
Wire Gauge (OD - mm²)	2.08	
Cable Length (ft.)	10	
Cable Length (m)	3.1	
Power Cord Jacket Type	SJT	
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27	
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50	
Shipping Weight (kg)	0.48	
Shipping Weight (lbs.)	1.05	
ENVIRONMENTAL		
Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)	
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)	
Operating Humidity Range	10-85% RH	
Storage Humidity Range	10-85% RH	
CONNECTIONS		
Side A - Connector 1	IEC-320-C14	
Side B - Connector 1	IEC-320-C13	
SPECIAL FEATURES		
High Voltage	Yes	
Locking Plug	No	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies