



## 919Sw-1

<b>Cabinet Color</b>	Piano Black Finish
<b>Panel</b>	TFT Active Matrix LCD 19" Widescreen, Diagonal 482.6mm Viewable Image Size Hard Coating (3H), Anti-glare Treatment
<b>Pixel Pitch</b>	0.285mm x 0.285mm
<b>Display Area</b>	410mm x 256mm
<b>Brightness</b>	300 cd/m2 (typ)
<b>Contrast Ratio</b>	800:1 (typ)
<b>Response Time</b>	5ms (typ)
<b>Viewing Angle</b>	Horizontal: 170 Degrees (CR>10) Vertical: 160 Degrees (CR>10)
<b>Compatibility</b>	VESA, WXGA+, SXGA, XGA, SVGA, VGA Mac® Equipped With Analog VGA Dsub or DVI Port
<b>Scanning Frequency</b>	Horizontal: 30K~81KHz Vertical: 55~75 Hz
<b>Pixel Frequency</b>	135MHz
<b>Maximum Resolution</b> <b>Recommended Resolution</b> <b>Resolutions Supported</b>	1440x900x75Hz 1440x900@60Hz 720x400@70Hz, 640x480@60, 67, 75Hz 800x600@56, 60, 72, 75Hz, 1024x768@60, 70, 75Hz, 1152x864@60Hz, 1280x1024@60, 75Hz, 1440x900@60, 75Hz
<b>Color</b>	More than 16M
<b>Signal Input</b>	Video: 0.7Vp-p, RGB Analog Separate Sync: TTL Level H/V Sync: Positive / Negative
<b>Connectors</b>	Analog RGB Signal: 15-pin D-sub Male Power: (3-Pin Plug CEE22)
<b>ENERGY STAR®</b>	Yes
<b>Power Source</b>	Universal 100~240VAC, 50/60Hz
<b>ENERGY STAR® Power Consumption</b>	36 Watts (Max)
<b>Plug &amp; Play</b>	DDC2B
<b>User Control</b> <b>OSD Function</b>	Menu(1), Down/Brightness, Up/Contrast, Confirm(2), Power Auto Adjust, Contrast, Brightness, Input Select, Color Adjust (sRGB, 9300K, 6500K, 5400K, User Color), Information, Manual Image Adjust (H-Size, H/V Position, Fine Tune, Sharpness), Setup (Language, Resolution Notice, OSD Setup), Memory Recall
<b>OSD Languages</b>	English, French, Spanish
<b>Regulations</b>	cULus, FCC, CE, Works with Windows Vista, ROHS
<b>Other Features</b>	VESA 100mm Wall Mount Compliant*, Kensington Security Slot
<b>Dimensions (WxHxD mm)</b>	Monitor: 449x367x195, Carton: 500x428x122
<b>Dimensions (WxHxD inches)</b>	Monitor: 17.7x14.4x7.7, Carton: 19.7x16.9x4.8
<b>Dimensions w/o base (WxHxD inches)</b>	Monitor: 17.7x12.4x2.5
<b>Weight</b>	10.5 lbs (4.75 kgs) Net 12.3 lbs (5.6 kgs) Gross
<b>Loading Qty w/pallet</b>	20' = 920 pcs.; 40' Std = 1924 pcs.
<b>UPC Code</b>	685417018987