OVERVIEW



1. USB-B Touch	12. LAN Out (RJ45 Out)
2. HDMI 2.0	13. USB 2.0
3. USB 3.0	14. AV In
4. USB-C 3.0	15. PC Audio
5. TF Card Slot	16. USB-C 3.0
6. Line-in (3.5mm)	17. 2x USB 3.0
7. SPDIF Out	18. DP
8. Line-out (3.5mm)	19. 3x HDMI 2.0
9. HDMI 2.0 Out	20. USB-B Touch
10. Serial (RS232)	21. VGA
11. LAN In (RJ45 In)	22. USB 2.0

PERFORMANCE

Panel

Panel

In-Plane Switching (IPS)

Backlight

DLED

Display Size

65 inches

Max View Area

WxH: 1428.5 x 803.5 mm

Resolution

3840 x 2160

Aspect Ratio

16:9

Pixel Pitch

0.3720 x 0.3720 mm

Dot / Pixel Per Inch

67 dpi

Brightness

400 cd/m²

Contrast Ratio

- Contrast Ratio: 1200:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

8 ms

Refresh Rate

60Hz

Color Gamut

- 85% NTSC
- 99% sRGB

Color Support

1.07 Billion

Color Depth

10-bit

Screen Surface Treatment

Anti-glare

Smart System

Smart System

- Operating System: Android™ 9.0
- Quad Core™: ARM Cortex A73
- GPU: ARM Mali-G52 MC2
- Storage: 64 GB
- Memory: 4 GB

Operating System

Operating System

Android 9.0

Multi-Media

Camera

- Detachable 4K 8MP Camera, Support Voice Tracking AI Feature (Model 62F2KATCWW only)
- No camera

Microphone

8x microphone array

Speakers

Integrated Speakers, 2x 15W

Power Supply

Power Consumption

- Typical / Max: 199W / 251W
- Sleep / Off mode: 35W
- Switch-off Mode: ≤0.5W
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- HDR10 Compliance
- 1x Human Detection Sensor
- 1x Ambient Light Sensor

DESIGN

Display

Touchscreen

Infrared touch technology, supports 20-point touch, 1.0 mm touch accuracy, 3.2 mm touch glass, 8 Mohs glass hardness

Mechanical

Bezel Width

Side: 28.84mm

Case Color

Raven black

Dimensions (WxDxH)[1]

Models	Dimensions
Monitor Only	1527.5 x 87.8 x 952.0 mm (60.14 x 3.42 x 37.48 inches)

Packaging Dimensions (WxDxH)

1660 x 220 x 1045 mm (64.74 x 8.58 x 40.76 inches)

Weight[2]

Models	Weight
Monitor Only	40.5 kg (89.29 lbs)

Packaging Weight

52.5 kg (115.74 lbs)

Mounting

Supports VESA mount 600 x 400 mm

In the Box

- 1x HDMI® cable
- 1x Power cable
- 1x USB-A to USB-B Cable
- 2x Stylus
- Detachable Camera (Model 62F2KATCWW only)
- Display with Wall Mount Bracket

- Quick Setup Guide
- Remote Control with Battery
- Warranty Booklet
- Wireless Projection Dongle

Notes:

[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

Support 10M / 100M / 1000M

WLAN + Bluetooth®

802.11ac 2x2 Wi-Fi® + Bluetooth 5.0, MIMO (both 2.4GHz and 5GHz bands)

Ports[1]

Front Ports

- 1x USB-C® 3.0
- 1x USB 3.0
- 1x USB-B Touch
- 1x HDMI 2.0

Top Ports

1x USB 2.0

Bottom Ports

- 1x AV In
- 1x HDMI 2.0 out
- 1x LAN in (RJ45 in)
- 1x LAN out (RJ45 out)
- 1x PC Audio
- 1x SPDIF out
- 1x TF Card slot
- 1x USB 2.0
- 1x line-in (3.5mm)
- 1x line-out (3.5mm)
- 1x serial (RS232)

Left Ports

- 1x USB-C 3.0
- 1x USB-B Touch
- 2x USB 3.0
- 3x HDMI 2.0
- 1x DP
- 1x VGA

Right Ports

1x Power Connector

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
USB4 40Gbps (USB 40Gbps): 40 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s.

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications[1]

Green Certifications

RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland Low Blue Light

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.


Tuesday
2021/10/12
1:45
Whiteboard
File Manager
Meeting
Lenovo


Tuesday
2021/10/12
1:45
Whiteboard
File Manager
Meeting
Lenovo







