

ThinkBook 14 2-in-1 G4 IML



Designed to seamlessly fit into the dynamic lifestyle of mobile professionals, this lightweight design marvel is easy to carry around. Driven by the Intel® Core™ Ultra 7 processor, it empowers site engineers, sales representatives and field technicians for efficient multitasking. To complement the need for clarity and precision, its 14" multi-touch screen with an anti-fingerprint surface makes content editing or working outdoors a breeze. A versatile 360° hinge support grants users the flexibility to transition between four distinctive modes- laptop, tent, tablet and stand.

Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkBook combines the style and user experience of consumer devices with the security and business-class support of ThinkPad.

The ThinkBook packs a range of smart features dedicated to amplifying your collaborative endeavors. The Dolby Atmos stereo speakers create a more engaging and richer auditory experience, whereas the noise-cancelling dual-array mics capture clearer audio by reducing background noise during real-time web conferences.

Experience accelerated download speeds, reduced latency and peak performance with the onboard Intel Wi-Fi 6 feature. Plus, the dual USB-A, USB-C and HDMI 2.1 ports offer multifaceted peripheral connectivity, data expansion and seamless display support.

The ThinkBook features HD Realtek audio chip, dual Dolby Atmos stereo speakers, smart noise-cancelling mics and FHD 1080p camera with privacy shutter and fixed focus for seamless web conferencing experience.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Professional Wireless Rechargeable Combo Keyboard and Mouse



- Transform your workspace into a clutter-free, cable-free zone for ultimate productivity.
- The mouse's Optical IR Sensor ensures precise tracking, with 4-way scrolling for smooth, versatile navigation.
- Keyboard layouts are tailored to vary by language, ensuring accessibility and usability for all users.

PN: 4X31K03931 - 4X31K03978

ThinkPad USB-C Wireless Compact Mouse



- Seamless 4-way scrolling (left, right, up, and down) and on-the-fly adjustable DPI controls.
- Plug and play 2.4 GHz USB C wireless dongle
- Supports Lenovo USB A or USB C Unified Pairing Receiver

PN: With Battery : 4Y51D20848 Without Battery : 4Y51D20849

ThinkBook 14 2-in-1 G4 IML

Performance

Processor
Intel U Series Core Ultra 5 / 7 Processor (Series 1)

Operating System
Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language

NPU
Integrated Intel AI Boost, up to 11 TOPS

Graphics
Intel Graphics (integrated)

Memory [1]
Up to 32GB DDR5-5600, 2x SO-DIMM

[1]The max memory is based on the test results with current Lenovo memory offerings.

Storage [2] [3]
Up to two M.2 PCIe NVMe SSD
M.2 2280 SSD up to 2TB each

[2]The storage capacity supported is based on the test results with current Lenovo storage offerings.

[3]The system supports dual SSD via two M.2 slots, but Lenovo only offers one SSD configuration, another SSD slot for user self-extension. The max storage capacity is only technical readiness and may be different with current Lenovo storage offerings.

Audio
High Definition (HD) Audio
audio by HARMAN stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array with noise-cancelling

Camera*
FHD 1080p, with privacy shutter
FHD 1080p + IR hybrid, with privacy shutter

Battery [4]
60Wh (up to 10.78 hr) battery, Rapid Charge

[4]Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display [5]
14" WUXGA (1920x1200) IPS glossy AF 16:10
- 300nits, 100% sRGB, Corning Gorilla Glass, Eyesafe, Dolby Vision, touch

[5]IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Multimode
Laptop, tent, stand and tablet modes supported by 360° hinge

Pen*
Lenovo Slim Pen*

Keyboard
6-row, spill-resistant, Copilot key, backlight

Touchpad
Glass-like Mylar surface touchpad, 75 x 120 mm (2.95 x 4.72 inches)

Dimensions [6]
313 x 224 x 16.9-18.5 mm (12.32 x 8.82 x 0.67-0.73 inches)

[6]The system dimensions may vary depending on configurations.

Weight [7]
Starting at 1.64 kg (3.62 lbs)

[7]The system weight is approximate and may vary depending on configurations

Color
Luna grey, dual-tone design

Case material
Aluminium (top)
Aluminium (bottom)

Special Features
Modern Standby

Connectivity

WLAN + Bluetooth* [8]
802.11ax (Wi-Fi 6 or Wi-Fi 6E), Bluetooth 5.2 or 5.3
Up to Intel Wi-Fi 6E AX211, Bluetooth 5.3

[8]Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

WWAN*
No support

Ports
1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
1x USB-C (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 & DP 1.4
1x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 1.4
1x HDMI 2.1, up to 4K/60Hz
1x microSD card reader
1x Headphone / microphone combo jack (3.5mm)

Docking
Docking support via Thunderbolt or USB-C

Security & Privacy

Security
Discrete TPM 2.0
Kensington Nano Security Slot
Touch style fingerprint reader on side power button, match-on-chip
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*

Certifications

Green Certifications [9] [10] [11]
EPEAT Gold Registered
ENERGY STAR 8.0
ErP Lot 6/26
TCO Certified 9.0
RoHS compliant

[9]The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

[10]EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

[11]EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications
TÜV Rheinland Low Blue Light (Hardware Solution)
Eyesafe Certified 2.0
MIL-STD-810H

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2024 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.