

VP2650wb

26" (25.5" VIEWABLE) PROFESSIONAL LCD

WITH 110% NTSC
OPTICOLOR™ TECHNOLOGY

Professional-grade color and performance.

The 26" (25.5" viewable) VP2650wb widescreen LCD features OptiColor™ technology with 110% NTSC color capability for BETTER COLOR ACCURACY and more detailed images in any viewing environment. Creative and business professionals will enjoy the EXPANSIVE COLOR GAMUT available in the VP2650wb. Complementing the intense color range are 3ms video response, 4000:1 Dynamic Contrast Ratio, and 1920x1200 native resolution to display true HD content and full-motion images. This display also features PerfectSuite™ Plus software for hassle-free set up and maintenance. With ADVANCED ERGONOMIC ADJUSTMENTS and an ultra-thin bezel for multiple display configurations, the VP2650wb is the ideal choice for graphics professionals, movie production and serious gamers.



PRECISE, VIBRANT COLOR

- > **OptiColor™ technology**
Delivers 110% color saturation for richer, more precise colors. Enjoy more intense colors in your graphics, photos and documents.
- > **ClearMotiv® 3ms video response**
Ultra-fast video response enables digital, HD broadcast-quality video.
- > **4000:1 dynamic contrast ratio**
Provides for darker black levels and better overall front-of-screen performance.
- > **Pivot, height and wall-mount versatility**
VESA® wall-mount interface and detachable base for ergonomic flexibility with pivot,* height, tilt and 120° swivel adjustments.
- > **PerfectSuite™ Plus control software**
Professional-grade LCD control software featuring color calibration, asset management, theft deterrence, and auto screen rotation.*
- > **Full 25.5" viewable widescreen with 1920x1200 resolution**
- > **Multiple analog/digital inputs and integrated USB hub expand your connectivity**
- > **Certified for Windows Vista®**

1920x1200
SUPER HD

4000:1
Dynamic Contrast Ratio

4 USB
PORTS

OptiColor™



VIEWSONIC
PRODUCTS, PROGRAMS,
AND SERVICES

ViewSonic®
See the difference® 

VP2650wb

26" (25.5" VIEWABLE) PROFESSIONAL LCD
WITH 110% NTSC OPTICOLOR™ TECHNOLOGY



ViewSonic Corporation's QMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by the British Standards Institution.

Sales: (888) 881-8781 • SalesInfo@ViewSonic.com • ViewSonic.com

*PerfectSuite™ and pivot function not supported by ViewSonic on Apple computers. **Adapter may be required. Analog adapter available from ViewSonic. Specifications subject to change without notice. Selection, offers and programs may vary by country; see your ViewSonic representative for complete details. Windows Vista and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. Corporate names, trademarks stated herein are the property of their respective companies. Copyright © 2008 ViewSonic Corporation. All rights reserved. [13771-008-11/07] VP2650wb-1

LCD	Type	26" (25.5" viewable) Color TFT active matrix LCD
	Display Area	21.7" horizontal x 13.5" vertical; 25.5" diagonal
	Optimum Resolution	1920x1200
	Contrast Ratio	1000:1 static (typ), 4000:1 dynamic
	Viewing Angles	160° horizontal, 160° vertical @ contrast ratio > 10:1
	Response Time	3ms gray-to-gray (avg); 5ms black-white-black (typ)
	Light Source	Long life, 40,000 hrs. (typ)
VIDEO INPUT	Brightness	400 cd/m ² (typ)
	Panel Surface	Anti-glare
	Analog/Digital	RGB analog (75 ohms, 0.7/1.0 Vp-p) / DVI (HDCP)
COMPATIBILITY	Frequency	F _H : 24-92kHz, F _V : 50-85Hz
	Sync	H/V separated (TTL), composite, sync-on-green
	PC	VGA up to 1920x1200 non-interlaced
CONNECTOR	Mac®**	G3/G4/G5 up to 1920x1200; PerfectSuite™ Plus and pivot function not supported by ViewSonic.
	Analog/Digital	15-pin mini D-sub / DVI-D
	USB	V2.0, 1-up/4-down
POWER	Power	Internal power; 3-pin AC plug (CEE22)
	Voltage	AC 100-240V, 50-60Hz (auto switch)
CONTROLS	Consumption	110W (typ)
	Basic	Power, 2, up, down, 1
ERGONOMICS	OnView®	Auto image adjust, brightness, contrast, input select (analog, digital), ViewMatch® color adjust (sRGB, 9300K, 7500K, 6500K-default, 5000K, user color-RGB), information (resolution, H. frequency, V. frequency, pixel clock, model number, serial number), manual image adjust (H. size, H. position, V. position, fine tune, sharpness, dynamic contrast, aspect ratio, display mode), setup menu (language, resolution notice, OSD position, OSD timeout, OSD background, OSD pivot), memory recall
	Operating Conditions	Height adjustment range 4.7", tilt, swivel range 120°, pivot
OPERATING CONDITIONS	Temperature	32-104°F (0-40°C)
	Humidity	10-90% (non-condensing)
DIMENSIONS (W x H x D)	Physical with stand	23.4" x 18.4" x 15.3" (595mm x 468mm x 388mm)
	Physical without stand	23.4" x 15.3" x 3.9" (595mm x 389mm x 100mm)
WEIGHT	Net with stand	25.4 lb. (11.5 kg)
	Net without stand	20.0 lb. (9.1 kg)
	Gross with stand	31.7 lb. (14.4 kg)
REGULATIONS		UL, cUL, FCC-B (ICES), CB, CE, TCO'03, ICES-003B, ISO 13406-2, TUV/GS, TUV ERGO (covers ISO 13406-2 & MPR II), TUV-S, NOM, GOST-R, HYGIENIC, CCC, BSMI, PSB, C-TICK, KTL/MIC, SASO, WEEE, RoHS, EPEAT-Silver
RECYCLE/DISPOSAL		The lamp in this product contains mercury. Please dispose of in accordance with local, state or federal laws.
POWER MANAGEMENT		Meets TCO'03 standards
PACKAGE CONTENTS		LCD display, power cable, VGA cable, DVI cable, USB cable, Quick Start Guide, ViewSonic Wizard CD, PerfectSuite™ Plus CD
WARRANTY		Three-year limited warranty on parts, labor and backlight

ViewSonic®
See the difference® 

For more product information, visit us on the web at ViewSonic.com