ELITE SCREENS

Spectrum Series Dimensions Table (RC1 version)

Model Number	Nominal Diagonal	Aspect Ratio	Screen Material	Gain	Case Length (A)	Viewable Width (A1)	Screen Width (A2)	End Cap Screw Hole Distance (A3)	Weight Bar Length (A4)	L/R Masking Border (A5)	Bottom Edge Distance (B3)	Screen Material to Bottom Bar (B2)	Viewable Height (B1)	Overall Height (B)	End Cap Height (B4)	Top Black Masking Border (B5)	Screen Material to Wall Distance (C1)	End Cap Width (C2)	Power Cord Length (D)	Packing Dimensions (LxWxH)			Net Weight	Gross Weight
Unit: Inch																							***Lbs***	***Lbs***
Electric84H2	84"	16:9	MaxWhite 2®	1.1	85.0	73.2	77.2	82.9	80.6	2.0	3.1	53.2	41.2	57.4	4.1	8.0	0.7	3.5	98.4	90.2	6.7	6.3	18.5	24.9
Electric100H2	100"	16:9	MaxWhite 2®	1.1	99.0	87.2	91.1	96.8	94.5	2.0	3.1	61.0	49.0	65.2	4.1	8.0	0.7	3.5	98.4	102.0	6.7	5.9	21.0	25.4
Electric105H2	105"	16:9	MaxWhite 2®	1.1	103.1	91.5	94.5	100.9	99.5	1.5	2.6	61.0	51.5	64.7	3.7	6.0	0.5	3.1	98.4	106.3	6.7	5.9	21.8	26.7
Electric110H2	110"	16:9	MaxWhite 2®	1.1	109.2	95.9	99.8	107.0	103.0	2.0	2.4	64.3	53.9	68.0	3.7	8.0	0.7	3.1	98.4	114.2	6.3	5.5	24.0	29.5
Electric115H2	115"	16:9	MaxWhite 2®	1.1	111.8	100.2	103.2	109.6	108.3	1.5	2.6	65.9	56.4	69.6	3.7	6.0	0.5	3.1	98.4	*	*	*	*	*
Electric125H2	125"	16:9	MaxWhite 2®	1.1	122.2	109.0	113.0	120.0	116.4	2.0	2.4	69.0	61.3	72.7	3.7	5.4	0.7	3.1	98.4	126.0	6.7	6.3	29.0	36.7
Electric150H2	150"	16:9	MaxWhite 2®	1.1	142.6	130.7	134.7	140.4	137.8	2.0	2.4	79.9	73.5	84.0	4.1	4.0	0.7	3.5	98.4	147.6	6.7	6.3	43.0	51.3
Electric180H2	180"	16:9	MaxWhite 2®	1.1	168.3	156.9	160.8	166.2	164.0	2.0	2.4	96.6	88.3	100.8	4.1	6.0	0.7	3.5	98.4	170.9	6.7	6.3	53.4	65.9
Electric100V2	100"	4:3	MaxWhite 2®	1.1	93.1	80.0	83.9	91.0	87.1	2.0	2.4	67.4	60.0	71.0	3.7	5.0	0.7	3.1	98.4	93.1	6.2	5.5	21.0	26.7
Electric140V2	140"	4:3	MaxWhite 2®	1.1	123.6	112.0	115.0	121.4	119.9	1.5	2.6	93.5	84.0	97.2	3.7	6.0	0.5	3.1	98.4	128.4	6.7	5.9	27.3	33.1
Electric180V2	180"	4:3	MaxWhite 2®	1.1	155.4	144.0	147.9	153.2	151.1	2.0	2.4	114.4	108.0	118.5	4.1	4.0	0.7	3.5	98.4	159.0	6.9	6.5	55.0	66.8
Electric90X2	90"	16:10	MaxWhite 2®	1.1	88.2	76.3	80.3	86.0	83.7	2.0	3.1	55.8	47.8	60.0	4.1	4.0	0.7	3.5	98.4	93.4	6.7	6.4	19.8	26.0
Electric106X2	106"	16:10	MaxWhite 2®	1.1	103.1	89.9	93.8	100.9	97.0	2.0	2.4	62.6	56.2	66.2	3.7	4.0	0.7	3.1	98.4	108.4	6.3	5.5	23.0	29.4
Electric128X2	128"	16:10	MaxWhite 2®	1.1	121.7	108.5	112.5	119.5	115.6	2.0	2.4	74.2	67.8	77.9	3.7	4.0	0.7	3.1	98.4	126.8	6.3	5.5	29.7	37.0
Electric142X2	142"	16:10	MaxWhite 2®	1.1	132.7	120.4	124.4	130.6	127.7	2.0	3.1	83.5	75.4	87.6	4.1	4.0	0.7	3.5	98.4	137.9	6.5	6.1	29.1	36.9
Unit: mm																							***Kgs***	***Kgs***
Electric84H2	84"	16:9	MaxWhite 2®	1.1	2160	1860	1960	2105	2046	50	80	1352	1046	1457	105	203	17	90	2500	2292	170	160	8	11
Electric100H2	100"	16:9	MaxWhite 2®	1.1	2514	2214	2314	2459	2400	50	80	1551	1245	1656	105	203	17	90	2500	2590	170	150	10	11
Electric105H2	105"	16:9	MaxWhite 2®	1.1	2619	2325	2401	2564	2529	38	65	1550	1308	1643	93	152	12	80	2500	2700	170	150	10	12
Electric110H2	110"	16:9	MaxWhite 2®	1.1	2773	2435	2535	2718	2615	50	60	1633	1370	1726	93	203	17	80	2500	2900	160	140	11	13
Electric115H2	115"	16:9	MaxWhite 2®	1.1	2840	2546	2622	2785	2750	38	65	1675	1432	1768	93	152	12	80	2500	*	*	*	*	*
Electric125H2	125"	16:9	MaxWhite 2®	1.1	3103	2769	2869	3048	2956	50	60	1753	1557	1846	93	136	17	80	2500	3230	160	140	13	17
Electric150H2	150"	16:9	MaxWhite 2®	1.1	3622	3321	3421	3567	3501	50	60	2030	1868	2135	105	102	17	88	2500	3750	170	160	20	23
Electric180H2	180"	16:9	MaxWhite 2®	1.1	4276	3985	4085	4221	4165	50	60	2454	2242	2559	105	152	17	88	2500	4340	170	160	24	30
Electric100V2	100"	4:3	MaxWhite 2®	1.1	2366	2032	2132	2311	2212	50	60	1711	1524	1804	93	127	17	80	2500	2365	157	140	10	12
Electric140V2	140"	4:3	MaxWhite 2®	1.1	3139	2845	2921	3084	3046	38	65	2376	2134	2469	93	152	12	80	2500	3260	170	150	12	15
Electric180V2	180"	4:3	MaxWhite 2®	1.1	3947	3658	3758	3892	3838	50	60	2905	2743	3010	105	102	17	88	2500	4039	175	165	25	30
Electric90X2	90"	16:10	MaxWhite 2®	1.1	2240	1939	2039	2185	2126	50	80	1418	1214	1523	105	102	17	90	2500	2372	170	163	9	12
Electric106X2	106"	16:10	MaxWhite 2®	1.1	2618	2283	2383	2563	2463	50	60	1589	1427	1682	93	102	17	80	2500	2753	160	140	10	13
Electric128X2	128"	16:10	MaxWhite 2®	1.1	3091	2757	2857	3036	2937	50	60	1885	1723	1978	93	102	17	80	2500	3220	160	140	13	17
Electric142X2	142"	16:10	MaxWhite 2®	1.1	3371	3059	3159	3316	3244	50	80	2120	1915	2225	105	102	17	90	2500	3503	165	155	13	17

Note: Data Error may be ±1" ***DISCONTINUED**

The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.

