RUGGED DOCKING STATIONS FOR ZEBRA ET60, ET65, ET60W & ET65W TABLETS

DS-ZEB-500 SERIES



RUGGED VERSATILITY REDEFINED FOR WORK TRUCK APPLICATIONS

- Standard & advanced I/O options to support essential equipment.
- External isolated & non-isolated power options available
- LED power indicator
- One-handed docking & undocking
- Spring-loaded, floating connector head
- Provides access to critical buttons, ports & barcode scanner when docked
- Compact & lightweight design
- Compatible with the Zebra extended battery, kickstand with hand strap, carry handle, and CAC reader
- Intelligent cable management system
- Integrated VESA 75 mounting pattern
- Options equipped with triple pass-through antenna connection

RUGGED DOCKING STATIONS FOR ZEBRA ET60, ET65, ET60W & ET65W TABLETS

DS-ZEB-500 SERIES



ET6X TABLET SOLUTION

- Supports Zebra's ET60 & ET65 Tablets
- One-handed docking & undocking
- Standard & advanced port replication (optional)
- Compact & lightweight design
- LED power indicator
- Both Windows & Android versions are supported

PART NUMBER	ETHERNET	USB 2.0	POWERED SERIAL	POWER INPUT	PASS-THRU ANT	ANT TYPE
DS-ZEB-501		1 REAR		12VDC*		
DS-ZEB-501-3		1 REAR		12VDC*	TRIPLE	SMA
DS-ZEB-503				USB-C		
DS-ZEB-504	1	2 REAR	1 @ 5VDC	12VDC*		
DS-ZEB-504-3	1	2 REAR	1 @ 5VDC	12VDC*	TRIPLE	SMA

*Requires an external Havis-approved DC power supply

SPECIFICATIONS:

Height: 11.1-in (28.2 cm)
Width: 12-in (30.4 cm)
Depth: 3.3-in (8.3 cm)
Weight: 2.2 lbs. (1.0kg)
Mounting: Integrated VESA 75 - mounting pattern

CERTIFICATIONS & TESTING:

Vibration Testing: MIL-STD 810H 514.8
Crash Testing: SAE J1455 30mph
Cycle Testing: Latch handle and docking connectors 30K cycles
Environmental Testing: Hot/Cold operational -4° C to 50° C (24.8° F to 122° F); Hot/Cold storage -40° C to 70° C (-40° F to 158° F)