

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

300W Medical-Grade Mobile Power Retrofit Kit with 36 Amp-hour Battery and 3 Outlets

MODEL NUMBER: HCRK-36







Description

Tripp Lite's Medical-Grade Mobile Power Retrofit Kit provides UL 60601-1 compliance (a required patient shock-prevention measure) for all connected mobile electronic devices. The Mobile Power Retrofit Kit includes everything needed to add AC power to medical carts. The kit's power supply features an isolation transformer that reduces the cumulative shock potential of connected equipment, helping to ensure UL 60601-1 compliance. The included 36 amp-hour battery module provides long-lasting mobile power. The Mobile Power Retrofit Kit also includes a remote user interface (RUI), mounting hardware and standard cabling.

Tripp Lite's Medical-Grade Mobile Power Retrofit Kit is fully compatible with most popular carts by AFC, Anthro, Datalux, GCX, Hergo, Humanscale, Jaco, Knurr, Stinger and more.

Features

- Provides UL 60601-1 compliance for connected mobile equipment (used in every sector of healthcare
 - facilities, both inside and outside of patient-care areas)
- Adds reliable mobile AC power source for medical carts
- Medical-Grade Mobile Power Supply (included) features an isolation transformer, providing UL 60601-1
 - compliance for connected equipment
- The Power Supply's advanced 3-stage charger recharges batteries faster and safer than conventional chargers
- The Power Supply's internal Automatic Transfer Switch (ATS) allows the power supply to simultaneously run connected equipment while recharging the battery module
- The Power Supply also features 3 NEMA 5-15R AC outlets, a 10-ft. coiled AC input cord with a hospitalgrade NEMA 5-15PHG plug, a USB communication port and a compact, all-metal housing that stands up to the most demanding environments
- 36-amp hour user-replaceable Battery Module (included) provides long-lasting mobile power. Maintenance-free, spill-/leak-proof sealed lead-acid (SLA) AGM battery features simple, plug-in connection with included cable

Highlights

- Provides UL 60601-1 compliance for connected mobile equipment (used in every sector of healthcare facilities, both inside and outside of patient-care areas)
- Adds reliable mobile AC power source to medical carts
- Saves money by upgrading new or existing non-powered carts for a fraction of the cost of buying new powered models
- Simultaneously powers connected equipment while recharging batteries
- Includes everything needed to retrofit a cart: mobile power supply, 36-amp hour userreplaceable battery module, PowerAlert data-saving software, remote user interface (RUI) and mounting hardware kit

Package Includes

- Medical-Grade Mobile Power Supply
- 36-amp hour user-replaceable Battery Module and cabling
- PowerAlert Software CD and USB cable
- Remote User Interface (RUI) and cabling
- Mounting Hardware Kit and owner's manual with warranty information



- Remote User Interface (RUI) displays output and battery charge status at a glance. Includes on/off and alarm-mute switches. Mounts anywhere on the cart for easy access with included mounting material and cable
- Mounting Hardware Kit retrofits most standard medical carts from AFC, Anthro, Datalux, GCX, Hergo, Humanscale, Jaco, Knurr, Stinger and more

Specifications

OVERVIEW	
UPC Code	037332142801
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Connection Type	NEMA 5-15P-HG Hospital-Grade
Voltage Compatibility (VAC)	120
Voltage Compatibility (VDC)	12
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
ουτρυτ	
Frequency Compatibility	60 Hz
Pure Sine Wave Output	No
Output (Watts)	300
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(3) 5-15R
Continuous Output Capacity (Watts)	300
Peak Output Capacity (Watts)	750
BATTERY	
DC System Voltage (VDC)	12
Battery Charge	Equal to discharge time. Includes advanced 3-stage (10A) battery charger
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	On Remote User Interface (RUI): Output AC Power, Battery Charge Level and Battery Charging Status
Switches	On Remote User Interface (RUI): On/Off Switch and Alarm-Mute Switch



Audible Alarm	Low Battery Alarm
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Cooling Method	Fan
Form Factors Supported	Retrofits most standard medical cart configurations
Material of Construction	Metal (Power Supply and Battery Module)
Shipping Dimensions (hwd / cm)	47.24 x 45.97 x 37.59
Shipping Dimensions (hwd / in.)	18.60 x 18.10 x 14.80
Shipping Weight (kg)	32.21
Shipping Weight (lbs.)	71.00
COMMUNICATIONS	
Network Monitoring Port	USB
STANDARDS & COMPLIANCE	
Certifications	Tested, certified and compliant to UL 60601-1, CAN/CSA-C22.2 No. 601.1-M90 and UL 1778 by TUV
WARRANTY	
Product Warranty Period (Worldwide)	2-year power module and 6-month battery module limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies