



**Small in size, huge in performance.
Perfect for your small workgroup.**

Fast, affordable desktop colour printing for every small workgroup.

With one of the smallest footprints in its class, the C3600 brings fast, affordable, high quality colour to the busiest offices.

Based on our award winning single-pass digital LED technology this latest addition to the C3000 Series comes with the features and functionality that you might expect to find only in larger, more expensive machines.

Impressive performance

Capable of printing as many as 16 colour pages per minute (ppm) (20ppm in black and white), and with the first page appearing in just 12 seconds or even less, it's not just one of the smallest printers for the price, but one of the fastest.

Unique space saving design

Compact design and easy access output tray the C3600 is perfect when space is at a premium. A front-facing LCD display gives clear, easy to understand status information and the top lifts up for quick replacement of the toner cartridges and drums.

Developed for endurance and economy

With separate drums and toner cartridges, you only ever have to replace what needs replacing. And with drums that print up to an impressive 15,000 pages, you can print more, for longer, as well as saving money.

Built for reliability

With fewer moving parts there's less to go wrong. That's why OKI Printing Solutions pioneered the use of digital LEDs and it's why we continue to use them in all our colour printers. Combine that with single-pass printing technology and you'll see why our printers just keep going: just what you need for a small but busy workgroup.

Powerful productivity software

The C3600 comes with a whole suite of useful productivity and creative software, making it ideal for the office environment:

- Print Control - for tracking usage and controlling access for tighter cost control.
- PrintSuperVision - browser-based monitoring and management of all your network printers, regardless of make or model.
- Template Manager 3.0 - editable, easy to use templates for creating a wide range of office documents.
- Color Correct - for fine-tuning the standard palette of Microsoft Office applications.
- Color Swatch - for reproducing custom colours such as those in corporate logos.

THE C3600 FEATURES AT A GLANCE

	C3600
Colour speed (A4)	16ppm
Mono speed (A4)	20ppm
Paper size	A4, A5, A6, banner
Paper capacity	250
Dimensions	290mm x 376mm x 479mm
Duplex (for double-sided print)	Manual (Windows only)
Processor speed	400MHz
Standard RAM memory	128MB RAM
Printer languages	PCL and Postscript



The C3600 Colour and Mono Printer

		C3600
Order number		44004603
Speed & throughput	A4 Print speed	16ppm colour, 20ppm mono
	Time to first print	10 seconds mono, 12 seconds colour
	Warm up time	up to 80 seconds from power on and up to 40 seconds from power save
	Processor speed	400MHz
Print quality	Resolution	ProQ2400 Multi-level technology, 1200 x 600dpi
	Enhancements	Auto Colour Balance, Photo Enhance via driver (excludes Mac OS and all PostScript drivers)
Typefaces	Printer fonts	Scalable: 87 PCL fonts and 80 PostScript fonts; PCL Bitmap fonts. OCR-A/B; USPS ZIP Barcode
Compatibility	Printer languages	PCL 6 (XL3.0) and PCL5c, PostScript 3 (clone). SIDM (IBM-PPR, EPSON-FX)
	Connectivity	Hi-Speed USB & 10/100-TX Ethernet
	OS Compatibility	Windows 2000 / XP Home / XP Professional / XP Professional x64 / Server 2003 / Server 2003 for x64 / Vista (32-bit) / Vista (64-bit) / Mac OS X PowerPC 10.2.8 or greater / Mac OS X Intel 10.4.4 or greater ^{†1}
	Barcode support	Barcode with checksum support
Utility Suite		Color Correct, Color Swatch, OKI LPR (Windows only), PrintSuperVision.net (Windows only), Template Manager 3.0 (Windows only), Web Driver Installer (Windows only), Web Print (Windows only), Print Control Server (Windows only), Print Control Client, Storage Device Manager (Windows only), Gamma Utility
Memory	Std RAM	128MB
	Max RAM	640MB
Paper handling	Paper capacity tray 1	250 sheets. Paper sizes: A4, A5, B5, A6
	Paper capacity of multi-purpose tray	1 sheet. Paper sizes: A4, A5, B5, A6, Envelopes (Com-9, Com-10, DL, Monarch, C5), Labels (Avery 7162, 7664, 7666), Custom Size (up to 1220mm length including Banners ^{†2})
	Standard tray paper weight	64–120gsm
	Multi-purpose tray paper weight	75–203gsm
	Duplex	Manual (Windows Only)
	Duplex paper sizes	A4, A5, B5. Supports Custom Size: Width 148-215.9mm Length 210-355.6mm
	Duplex paper weight	75–105gsm
	Paper Output	150 sheets face down (80gsm), 1 sheet face up
Operating conditions	Temperature/humidity	10°C to 32°C (17°C to 27°C recommended) / 20% to 80% RH (50% to 70% RH recommended)
	Storage	-10°C to 43°C, 10% to 90% RH
Power requirements	Power supply	Single phase 220-240VAC, frequency 50/60Hz +/-2%
	Power consumption	Typical 400W, Peak 980W, Idle 100W (average), Power save <14W
Noise level		Operating: Up to 51.0 dB(A), Standby: 37 dB(A), Power Save: Background Level
Dimensions (HxWxD)		290mm x 376mm x 479mm
Weight ^{†3}		Approx 21kg
Duty cycle	Printer duty (max)	35,000 pages/month
	Printer duty (average)	500 - 2,000 pages/month
Warranty		Pan European 1 year on-site
Accessories		• 256MB (01182901) or 512MB (01182902)

• Optional (order number)

^{†1} Check local OKI Printing Solutions website for latest driver releases & OS Compatibility

^{†2} Installation of optional memory is recommended to enable full banner printing capabilities

^{†3} Includes all consumables

Consumables Information: For the protection of your printer, and in order to ensure that you benefit from its full functionality, this model has been designed to operate only with genuine OKI Printing Solutions toner cartridges. These can be identified by the OKI trademark. Any other toner cartridge may not operate at all, even if it is described as “compatible”, and if it does work, your printer’s performance and print quality may be degraded.

Description	Life* (pages)	Order number
Black toner	1,500	43459436
	2,500	43459332
Colour toners	1,500	Cyan: 43459435 / Magenta: 43459434 / Yellow: 43459433
	2,500	Cyan: 43459331 / Magenta: 43459330 / Yellow: 43459329
Image drum	15,000 A4 pages	Black: 43460208 / Cyan: 43460207 / Magenta: 4340206 / Yellow: 43460205
Transfer belt	50,000 A4 pages	43378002
Fuser unit	50,000 @ A4	43377003

*All toners: A4 pages @ 5%, Printer shipped with 500 pages @ 5%. All Drums: A4 pages average life.
Specification subject to change without notice. All trademarks acknowledged.

Colour Printers

Mono Printers

MFPs

Fax

Dot Matrix

OKI Europe Ltd.

Central House, Balfour Road
Hounslow, Middlesex TW3 1HY
United Kingdom

T +44(0) 20 8219 2190

F +44(0) 20 8219 2199

WWW.OKIPRINTINGSOLUTIONS.COM



High Definition Color

OKI
PRINTING SOLUTIONS