

Epson GT-1500Specification Sheet



Fast and cost effective scanning

Epson GT-1500	B11B190031
SCANNER TYPE	Sheetfed & Flatbed A4 colour image scanner
OPTICAL RESOLUTION	Flatbed: 1,200 x 2,400 dpi with Micro Step™ Drive
	ADF: 600 x 600 dpi
OUTPUT RESOLUTION	50 dpi to 4,800 dpi (50 ~ 2400dpi in 1dpi increment, 3200dpi, 3600dpi, 4800dpi)
SUB-SCANNING METHOD	Fixed document and carriage moving

MAXIMUM EFFECTIVE SCAN AREA		
REFLECTIVE	Flatbed: 216 x 297mm (8.5 x 11.7 inches) ADF: 216 x 356mm (8.5 x 14.0 inches)	
PHOTOELECTRIC DEVICE	3 lines colour CCD	
PIXEL DEPTH	In: 16 bit/pixel Out: 1, 8, 16 bit / pixel	
GRAYSCALE	16-bit (65,536 greyscale levels) external 16-bit (65,536 greyscale levels) internal	
COLOUR	48-bit (281,474 billion colours) external 48-bit (281,474 billion colours) internal	
INTERFACE	USB 2.0++	

++The functionality of the USB port(s) must be ensured by the vendor of the Host.v

CONFIGURATION	
LIGHT SOURCE	White LED
SUB-SCANNING METHOD	Fixed document and moving carriage

SCANNING SPEED			
REFLECTIVE SCANNING			
MONOCHROME*1	A4 200dpi (PDF)	18ppm	
COLOUR*2	A4 200dpi (PDF)	12ppm	

The thumbnail images below show the scanning patterns used to determine scanning speed specifications.





System Configuration of Scanning Speed

CPU: Pentium 4,3.2GHz

RAM: 1GB

I/F: USB2.0 Hi-Speed

OS: Windows XP Home Edition Soft: Adobe Photoshop 7.0E

*1 Line Art (MEM0) *2 Photo Photo courtesy of ISO&JIS-SCID. Reprinted by permission)

Scanning speed test results vary according to system configuration, dpi setting, and scan mode setting. However, documents and photos other than those pictured above can be substituted without significantly affecting test results.

g		
ADF		
TYPE	Sheet through, Simplex scanning	
PAPER SUPPLY	Paper Supply: Face up load Paper Out: Face down eject	
DOCUMENT SIZE	A4, Letter, Legal, B5, A5, A6 Max. size: 216 x 356 mm Min. size: 105 x 148.5 mm	
PAPER SETTING CAPACITY	40 pages (75g/m2)	
PAPER WEIGHT	50-120g/m2	

Ē	U	N	C	T	IO	N	S

EASY DOCUMENT SCANNING 4 Customisable push buttons

10 customisable job

Double sided scanning of PDF Searchable PDF (Windows only)

Scan to Mutli PDF Encrypted pdf Compression pdf

Stand-Alone Application and Scan to File

Feature

Multi Purpose User Interface Auto Skew Correction

Multi Marguee

DOCUMENT IMAGE ADJUSTMENT Text enhancement

Colour enhancement Dropout colour

Unsharp Mask
De-Screening with Document Type Opti-

miser

Tone Curve Adjustment with Histogram

SUPPORTED PLATFORMS

USB1.1 USB2.0 High-Speed

*Microsoft® Windows® 2000 Professional / XP (Home Edition / Professional / Professional X64) / Windows® Vista (Home Basic, Home Premium, Business, Enterprise, Ultimate)

Mac OS X v10.2.8 or later

*USB2.0 Host Driver by Microsoft is required

ENVIRONMENTAL CONDITIONS

TEMPERATURE 10°C to 35°C (Operating) -25°C to 60°C (Storage)

HUMIDITY 10% to 80% without condensation (Operating) 10% to 85% without condensation (Storage)

ELECTRICAL SPECIFICATIONS

RATED VOLTAGE (AC100V model) AC100-120V 50-60Hz (AC200V model) AC220-240V 50-60Hz

POWER CONSUMPTION Approx. 12.5W (Operating)

Approx. 12.3W (Operating)
Approx. 2.4W (Sleep Mode)
Approx. 5.5W (Ready Mode)
Approx. 0.6W (Power Off)

BUNDLED SOFTWARE*

Epson Scan
Epson Event Manager

ABBYY FineReader Sprint Plus 6 (for Windows)/ ABBYY FineReader Sprint Plus F (for Magistock)

Plus 5 (for Macintosh)

NewSoft Presto! Page Manager 8 Standard Online User Guide

* Microsoft® Windows® 2000 Professional/ XP Home edition/ XP Professional/ XP Professional x64 Edition/ Vista (Home Basic, Home Premium, Business, Enterprise, Ultimate)/ Mac® OS 10.2.8 or later

WARRANTY

12 months return to base Standard
Optional Additional 2 Year Warranty 3YWGT1500

DIMENSIONS

WIDTH	470mm
DEPTH	318mm
HEIGHT	121mm
WEIGHT	Approx. 3.9kg

For more information visit www.epson.com.au or www.epson.co.nz