

ThinkPad L14 Gen 5 (AMD)

Experience unparalleled efficiency and reliability wherever your work takes you. Weighing in at 1.41 kg (3.11 lbs), this portable laptop ensures professionals stay nimble on the go. Powered by the lightning-fast AMD Ryzen 7 Pro processor, multitasking becomes seamless, allowing you to tackle intensive workloads with ease. Elevate your productivity further with the inclusion of AMD Radeon 660M or 680M graphics, ensuring stunning visuals for presentations, design tasks, and entertainment alike. Plus, with up to 13.55 hours of battery life, you can power through your day without worrying about recharging.



Built for business with cutting-edge technology

The mid-range ThinkPad L Series offers enterprise docking, enhanced security features and optional remote management capabilities.

Security solutions include an optional Microsoft Pluton TPM 2.0 chipset that offers protection against advanced security threats such as hardware attacks and firmware vulnerabilities, ensuring the sensitive data stored on the laptop remains secure. Additionally, an optional touch-style fingerprint reader streamlines the authentication process by allowing business professionals to log in and access secure applications with just a touch.

The compact dimensions, measuring 313.7 x 226 x 18.92 mm (12.35 x 8.90 x 0.74 inches), make this laptop highly portable, enabling business professionals to easily carry it during travel or meetings.

With dimensions starting at 313.7 x 226 x 18.92 mm (12.35 x 8.90 x 0.74 inches), this laptop boasts a sleek and portable build, ensuring easy mobility without compromising on power.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Expedited Depot Repair Warranty

- Speeds up standard 7-10 business-day depot service
- Get the repaired system back in 3 to 4 business days
- Avoid unplanned expenses when you need a faster repair

Accessories

Lenovo Powered USB-C Travel Hub



- Connects to a PC through a single USB-C cable which also recharges the device
- Connect to an external display with HDMI or VGA, and other peripherals with 2x USB ports
- Compact 183x100mm (7.2x4") design with integrated cable management

PN: 4X90S92381

Lenovo Professional Wireless Keyboard & Mouse



- Wireless keyboard and mouse combo with reliable 2.4 GHz wireless connection
- Slim keyboard with number pad, noise-suppression design, dedicated media controls & adjustable tilt legs
- Contoured design of the mouse suits both left-handed & right-handed users

PN: 4X30H56796

ThinkPad L14 Gen 5 (AMD)

Performance

Processor
AMD Ryzen 3 / 5 / 7

Operating System
Windows 11 Pro
Windows 11 Home
Windows 11 DG Windows 10 Pro 64
Linux
Ubuntu Linux

Graphics
AMD Radeon 660M Graphics (integrated)
AMD Radeon 680M Graphics (integrated)

Memory [1]
Up to 64GB DDR5-4800, 2x SO-DIMM

[1]The max memory is based on the test results with current Lenovo memory offerings.

Storage [2]
Up to 1x 2TB M.2 2280 PCIe NVMe SSD

[2]The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio
High Definition (HD) Audio
Dolby Audio speakers
Dual-microphone array, far-field, Dolby Voice

Camera*
HD 720p, with privacy shutter
5.0MP + IR discrete, with privacy shutter

Battery [3]
46.5Wh or 57Wh battery, up to 13.55 hr
Rapid Charge

[3]Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*
45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display [4]
14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, 60Hz, DBEF5
- 400nits, 45% NTSC, 60Hz, DBEF5, Eyesafe, touch
- 400nits, 100% sRGB, 60Hz, low power, Eyesafe

[4]IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard
6-row, spill-resistant, optional backlight

Touchpad
TrackPoint and Mylar surface touchpad
60 x 115 mm (2.36 x 4.53 inches)

Dimensions [5]
Models with aluminium (top) and PC-CF (bottom)
Starting at 313.7 x 226 x 18.66 mm (12.35 x 8.90 x 0.73 inches)

Models with aluminium (top) and PC-ABS (bottom)
Starting at 313.7 x 226 x 18.76 mm (12.35 x 8.90 x 0.74 inches)

Models with PC-ABS (top) and PC-ABS (bottom)
Starting at 313.7 x 226 x 18.92 mm (12.35 x 8.90 x 0.74 inches)

[5]The system dimensions may vary depending on configurations.

Weight [6]
Models with aluminium (top) and PC-CF (bottom)
Starting at 1.36 kg (2.99 lbs)

Models with aluminium (top) and PC-ABS (bottom)
Starting at 1.38 kg (3.04 lbs)

Models with PC-ABS (top) and PC-ABS (bottom)
Starting at 1.41 kg (3.11 lbs)

[6]The system weight is approximate and may vary depending on configurations

Color
Eclipse black

Case material
Aluminium (top), PC-CF (bottom)
Aluminium (top), PC-ABS (bottom)
PC-ABS (top), PC-ABS (bottom)

Connectivity

Ethernet
Gigabit onboard Ethernet

WLAN + Bluetooth* [7] [8]
Qualcomm NFA-725A Wi-Fi 6E, 802.11ax, Bluetooth 5.3

[7]Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

[8]Bluetooth may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

WWAN*
4G LTE CAT6 with embedded eSIM
4G LTE CAT16 with embedded eSIM

NFC
Near Field Communication*

Ports
1x USB-A (Hi-Speed USB / USB 2.0)
2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On
1x USB-C (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 & DP 1.4
1x USB-C (USB4 40Gbps), with USB PD 3.0 & DP 1.4
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Ethernet (RJ45)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking
Docking support via USB-C

Security & Privacy

Security
Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Smart card reader*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*

Manageability

System Management*
DASH

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2024 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.