



Nokia E71 Data Sheet

Planned Market Introduction

- Q3 2008
- Category**
- Achieve

Key Features

- Optimized mobile email and messaging experience with full QWERTY keyboard and pocket-size for one-handed typing
- Two customizable Home Screen views with active stand-by plug-ins and application shortcuts – fast and easy switching between e.g. business and personal modes
- Quick access to applications with One-touch keys (Home, Calendar, Contacts, Email)
- Intelligent input with auto-completion, auto-correction and learning capability ensuring fast and error-free typing
- Nokia Calendar and Contacts for Eseries applications with improved features
- Built-in A-GPS and Nokia Maps
- HSDPA data connection up to 3.6 Mbps for fast web browsing and downloading

Additional features

- 3.2 megapixel camera with auto-focus and flash, front camera for video calls
- Music player, Media player, Visual Radio
- Nokia MiniMap browser
- Online sharing: Share on Ovi
- Built-in mobile VPN for convenient intranet access
- Data encryption for both phone memory and microSD
- Nokia PC Internet access (via Phone as modem functionality)

Email solutions

- Nokia Intellisync Wireless Email
- Mail for Exchange and other corporate server mail formats
- POP/IMAP
- 3rd party email solutions

Technical Profile

- System:** WCDMA 850/2100, WCDMA 900/2100 and WCDMA 850/1900, HSDPA, GSM/EGSM 850/900/1800/1900
- User Interface:** S60 platform
- Dimensions:** 114 mm x 57 mm x 10 mm (L x W x H)
- Volume:** 66 cc
- Weight:** 126 g
- Standby time:** Up to 17 days (GSM), 20 days (WCDMA)
- Talk time:** Up to 10.5 hours (GSM), 4.5 hours (WCDMA)
- Main display:** 2.36" QVGA (320x240), up to 16 million colors
- Battery:** BP-4L, 1500 mAh, Li-Po
- Memory:** Up to 110 MB internal memory, support for up to 8 GB microSD memory card

Main Camera

- Image capture:** Up to 3.2 megapixels (2048x1536 pixels)
- Video capture:** Video recording in QVGA quality

Data Services & Connectivity

- WCDMA max download 384 kbps; upload 384 kbps
- HSDPA up to 3.6 Mbps
- WLAN (IEEE 802.11g)
- GPRS multislot class 32, max download 296 kbps; upload 177.6 kbps
- GPS and support for assisted GPS (A-GPS)
- FS-USB, Infrared
- Bluetooth wireless technology 2.0 with A2DP stereo audio, enhanced data rates (EDR)
- 2.5 mm AV connector

Nokia Original Accessories

- Car:** Mobile Holder CR-106
Advanced Car Kit CK-300
Holder Easy Mount HH-12
- Headsets:** Bluetooth Headset BH-602
- Audio:** Bluetooth Speakers MD-5W
- Data:** 8 GB Card MU-43
- Power:** Mobile Charger DC-4

- Inbox Colors** Grey steel, White steel