

Ready for Home & School.

Fully-featured, Wireless 4-in-1 for the Home Office.



- Convenience and flexibility with built-in 802.11b/g wireless technology. Compatible with 802.11n.(1)
- Full feature fax with 25 page automatic document feeder
- Lab-quality photos with direct photo printing from Memory Cards, USB drive or with PictBridge™
- Print fast! Up to 25 ppm black and 18 ppm colour (3)
- Fast and easy install




Home & Student X6650 Wireless 4-in-1

Print. Copy. Scan. Fax.

LEXMARK
TM

Fully-featured, wireless 4-in-1 for the home office.



Product Functionality

Wireless

- Built-in 802.11b/g wireless printing. Compatible with 802.11n.
- High-quality printing from virtually anywhere in your home over a secure wireless network (1)
- Share the Lexmark X6650 wirelessly among multiple computers
- Easy, guided setup with Lexmark installation software
- Connect with 802.11b/g wireless network and wireless computer or with USB cable

Print

- Up to 25 ppm black and 18 ppm colour printing (3)
- Superior quality printing up to 4800x1200 dpi print resolution

Copy

- 1-touch, PC-free copying (colour or black)
- Reduction / enlargement capacity from 25% - 400%
- 1-99 copies
- Borderless copying in popular photo sizes

Scan

- Flatbed scanner easily handles thick books, reports and more
- 36-bit colour scanner depth; 12-bit grayscale
- Optical Character Recognition (OCR) software allows you to easily scan hard copy text documents into a soft copy format
- Preserve important documents with direct to PDF scanning

Fax

- Up to 25 page capacity automatic document feeder(ADF) for multiple page faxing and copying
- Standalone black and colour faxing with 33.6 Kbps modem speed
- 99 speed dials, automatic redial, junk fax block and supports caller ID

Photo Printing

- Print directly from digital memory cards slots, PictBridge™ compatible digital cameras or USB flash drive
- Select photos to print via scan back proof-sheet for PC-free printing
- Brilliant, 6-colour printing with optional photo cartridge
- Print borderless photos in popular sizes
- Apply photo effects: sepia, antique gray, antique brown, black & white

Software Suite

- Lexmark Service Center simplifies printer troubleshooting
- Lexmark Productivity Studio Software makes it easy to scan, crop, rotate and resize photos, plus 1-touch colour fix and red eye reduction
- Lexmark Toolbar, with Picnik™ photo editing and Scheduled Print, makes Internet printing easy!
- Lexmark Productivity Studio makes creative and school projects easy

Cartridge Compatibility

- Get 2X more pages with available XL, high yield cartridges!
- Black: 36(2), 36A, 36XL(2), 36XLA
- Color: 37(2), 37A, 37XL(2), 37XLA
- Photo: 31

Paper Compatibility

- Lexmark Photo Paper, Lexmark Premium Paper
- Use Lexmark genuine supplies for best results!



- Reduce e-waste using this wireless all-in-one which reduces the need for multiple devices in your home and office. Plus, this reliable printer is built to last and backed by a 1 year warranty.
- Operate efficiently. With this Energy Star Qualified All-In-One save up to 61% of operating power in automatic power saving mode.
- Remember, Lexmark recycles returned Lexmark printers and cartridges for free.

Technical Specifications

Operating Systems Supported

- Microsoft Windows XP, XP Professional x64, Vista, 2000 5.00.2195 or later, Vista x64
- Apple Mac OS X (10.4.4-10.5.x Intel, PowerPC), OS X (10.3.9 Power PC)

Digital Media Memory Card Compatibility

- CompactFlash I & II • Sony Memory Stick- Memory Stick PRO • Secure Digital (SD) Card • MultiMediaCard (MMC) • Microdrive • Sony Memory Stick Duo (with adapter) • Mini Secure Digital (Mini SD) Card (with adapter) • Sony Memory Stick PRO Duo (with adapter) • SanDisk TransFlash Memory Module (with adapter) • RS-MMC (with adapter) • xD Card Type M- Type H • MultiMediaCard (MMC) Mobile (with adapter) • Micro Secure Digital (Micro SD) Card (with adapter) • Secure Digital High Capacity (SDHC) Card (with adapter)

Print Noise Level, Operating

- 48 dBA

Duty Cycle, Maximum

- 3000 Pages per month

Product Warranty

- One Year Replacement

Connectivity

- Standard Ports : USB 2.0 Specification Hi-Speed Certified, USB Direct interface on Operator Panel, USB pass-through via PictBridge port, 802.11g/b Wireless

Print (ASF) Paper Input Capacity (Maximum)

- 100 pages 20 lb or 75 gsm bond

Print (ASF) Paper Output Capacity (Maximum)

- 25 pages 20 lb or 75 gsm bond

Media Sizes Supported

- 10 Envelope, 7 3/4 Envelope, 9 Envelope, A4, A5, B5 Envelope, C5 Envelope, DL Envelope, 6 3/4 Envelope, A2 Baronial, A6 Card, B5, C6 Envelope, Custom, Hagaki Card, Index Card, Executive, Legal, Letter, 4 x 6", Statement, L, 2L, Chokei 3, Chokei 4, Chokei 40, Kakugata 3, Kakugata 4, Kakugata 5, Kakugata 6, 5 x 7", 13 x 18 cm, 10 x 15 cm

Borderless Printing Media Sizes

- 4" x 6", A4, Letter, A6, Hagaki Card, L, 2L, A5, 5" x 7", Legal, 3.5" x 5" or 89 mm x 127 mm, 10 x 15 cm, 13 x 18 cm, B5, 10 x 20 cm, 4" x 8"

Dimensions

- Size (H x W x D) : 8.1 x 18.3 x 11.6"
- Size, Trays Extended (H x W x D) : 13.1 x 18.3 x 19.7"
- Weight : 16.55 lbs.
- Packaged Size (H x W x D) : 16.575 x 21.457 x 12.44"
- Packaged Weight : 20.03 lbs.
- Pallet Size (H x W x D) : 37.65 x 48 x 40"
- Pallet Weight : 280.4 lbs.
- Pallet Quantity : 12

Standard Box Contents

- Lexmark X6650 Printer
- One color cartridge
- One black cartridge
- Setup sheet
- User's Guide on CD
- Windows/Mac Installation CD
- Power supply and line cord
- Fax Guide
- Network Guide
- Phone Guide
- Statement of Limited Warranty
- (1) 2 meter cable for wireless setup/ USB connection

*Licensed Return Program Cartridge



(1) Printer designed to utilize your network's security (WEP, WPA and WPA2) and broadcast range. Access to electricity is required.
 (2) Non-refillable cartridge licensed for single use only. Return empty cartridge only to Lexmark for remanufacturing, refilling or recycling. A variable amount of ink remains when this cartridge must be replaced. Replacement cartridges (36A, 37A, 36XLA, 37XLA) sold without those terms are available through www.lexmark.com. All prices, features, specifications and claims are subject to change without notice.
 (3) Printing in draft mode and excludes time to first page print.

Lexmark and Lexmark with the diamond design are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. All other trademarks are the property of their respective owners. The USB-IF logos are trademarks of Universal Serial Bus Implementers Forum, Inc. Mac and Macintosh are trademarks of Apple Computer, Inc., registered in the United States and other countries. ENERGY STAR® is a U.S. registered mark. Microsoft, Windows, the Windows logo, Windows Vista, and the Windows Vista logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. PrecisionSense is a trademark of Lexmark International, Inc. registered in the United States and/or other countries.

All other trademarks are the property of their respective owners. Information in this document is subject to change without notice. © 2008 Lexmark International, Inc. 740 West New Circle Road, Lexington, KY 40550. As of 06/08.