

Lexmark C782n



LEXMARK

Lexmark C782n

The versatile Lexmark C782n supports a wide variety of media and can be upgraded to an MFP solution.



Lexmark C782n, C782dn, C782dtn

In the Box

Lexmark C782n

- Lexmark C782n Printer
- 10,000-page Cyan, Magenta, Yellow and Black Return Program Print Cartridges¹
- Power Cord
- Software and Documentation CD

Lexmark C782dn

- Lexmark C782n + Automatic two-sided printing

Lexmark C782dtn

- Lexmark C782dn + 500-sheet Drawer

Product Specifications

| | |
|---|--|
| Part Number | C782n: 10Z0103, C782dn: 10Z0104, C782dtn: 10Z0105. |
| Product Class | Medium/large workgroup colour laser printer; Calibrated for PANTONE™ solid colour simulation |
| Speed | Black: Up to 40 ppm; Colour: Up to 35 ppm |
| Time to First Page | Black: As fast as 11 seconds; Colour: As fast as 13 seconds |
| Print Resolution | 1200 x 1200 dpi; 4800 Colour Quality |
| Processor | 800 MHz |
| Memory (std./max.) | 256MB/768MB |
| Connectivity Standard Optional Network Mgmt Utility | Ethernet, USB, USB Direct Interface, 1 internal solutions port Serial, Parallel, Wireless, Gigabit Ethernet, Fiber Optic MarkVision Professional |
| Printer Languages | PostScript 3 and PCL 6 emulations, PPDS Migration Tool |
| Direct Print Formats | PDF v1.5, GIF, PNG, BMP, PCX, DCX, JPEG, TIFF, HTML 4.0 |
| Fonts | PCL: 89 scalable, 2 bitmapped; PostScript: 158 scalable; PPDS: 39 scalable, 5 bitmapped |
| Operating Systems | Windows, Linux, UNIX, Mac, NetWare and OS/400 |
| Acoustics | Printing: 53 dBA; Idle: 30 dBA |
| Size (WxDxH) | C782n: 604.5 mm x 469.9 mm x 528.3 mm (23.8in. x 18.5in x 20.8 in.); C782dn: 604.5 mm x 469.9 mm x 617.2 mm (23.8in. x 18.5in. x 24.3 in.); C782dtn: 604.5 mm x 469.9 mm x 734.1 mm (23.8in. x 18.5in. x 28.9in.) |
| Weight | C782n: 47.7 kg. (105 lb); C782dn: 53.8 kg. (118.5 lb); C782dtn: 60 kg. (132 lb) |
| Duty Cycle² | Maximum monthly duty cycle: Up to 150,000 pages per month |
| Recommended Monthly Page Volume³ | 2, 500 - 17,000 pages per month |

Media Specifications


| | |
|---|--|
| Paper Capacity (sheets) Standard Maximum | C782n, C782dn: Input: 600; Output: 250 C782dtn: Input: 1,100; Output: 250 Input: 3,100; Output: 900 |
| Paper Sources Standard Maximum | C782n, C782dn: Input: 2; Output: 1 C782dtn: Input: 3; Output: 1 Input: 5; Output: 6 |
| Media Information Types Size Weight | Plain paper, recycled paper, card stock, transparencies, envelopes, vinyl labels, paper labels, polyester labels, dual-web labels, integrated labels, outdoor media Letter, A4, A5, JIS B5, statement, folio, legal, executive, universal (3 x 5 in. to 9.01 x 14 in.), envelopes (7 ³ / ₄ , 9, 10, DL, C5, B5), banner (8.5 x 48 in.) Plain paper: 16 to 47 lb. (60 to 176 g/m ²); Card stock: up to 110 lb. (199 g/m ²); Labels: 48-92 lb. (180-300 g/m ²) |

Shipping Dimensions

| | |
|------------------------|---|
| Lexmark C782n | 795 mm x 650 mm x 810 mm. 68 kg. (31.3 in. x 25.6 in. x 31.9 in. 150 lb). |
| Lexmark C782dn | 1100 mm x 725 mm x 945 mm. 91 kg. (43.3 in. x 28.5 in. x 37.2 in. 201 lb). |
| Lexmark C782dtn | 1320 mm x 725 mm x 945 mm. 100.7 kg. (52 in. x 28.5 in. x 37.2 in. 222 lb). |

Part Numbers

| | | |
|--|--|----------|
| Supplies | 15,000-page Black Extra High Yield Return Program Print Cartridge ¹ | C782X1KG |
| | 15,000-page Cyan Extra High Yield Return Program Print Cartridge ¹ | C782X1CG |
| | 15,000-page Magenta Extra High Yield Return Program Print Cartridge ¹ | C782X1MG |
| | 15,000-page Yellow Extra High Yield Return Program Print Cartridge ¹ | C782X1YG |
| | 15,000-page Black Extra High Yield Print Cartridge ¹ | C782X2KG |
| | 15,000-page Cyan Extra High Yield Print Cartridge ¹ | C782X2CG |
| | 15,000-page Magenta Extra High Yield Print Cartridge ¹ | C782X2MG |
| | 15,000-page Yellow Extra High Yield Print Cartridge ¹ | C782X2YG |
| | 10,000-page Black High Yield Return Program Print Cartridge ¹ | C780H1KG |
| | 10,000-page Cyan High Yield Return Program Print Cartridge ¹ | C780H1CG |
| | 10,000-page Magenta High Yield Return Program Print Cartridge ¹ | C780H1MG |
| | 10,000-page Yellow High Yield Return Program Print Cartridge ¹ | C780H1YG |
| | 10,000-page Black High Yield Print Cartridge ¹ | C780H2KG |
| | 10,000-page Cyan High Yield Print Cartridge ¹ | C780H2CG |
| | 10,000-page Magenta High Yield Print Cartridge ¹ | C780H2MG |
| | 10,000-page Yellow High Yield Print Cartridge ¹ | C780H2YG |
| | 6,000-page Black Return Program Print Cartridge ¹ | C780A1KG |
| | 6,000-page Cyan Return Program Print Cartridge ¹ | C780A1CG |
| | 6,000-page Magenta Return Program Print Cartridge ¹ | C780A1MG |
| | 6,000-page Yellow Return Program Print Cartridge ¹ | C780A1YG |
| | 6,000-page Black Print Cartridge ¹ | C780A2KG |
| | 6,000-page Cyan Print Cartridge ¹ | C780A2CG |
| | 6,000-page Magenta Print Cartridge ¹ | C780A2MG |
| | 6,000-page Yellow Print Cartridge ¹ | C780A2YG |
| | Toner Waste Container | 10B3100 |
| | Staple Cartridges | 11K3188 |
| | Routine Maintenance Items: | |
| ITU Maintenance Kit with Transfer Roll | 40X1826 | |
| Fuser Maintenance Kit | 40X1831 | |
| Memory/Flash Options | 128MB SDRAM | 13N1523 |
| | 256MB SDRAM | 13N1524 |
| | 512MB SDRAM | 13N1526 |
| | 32MB Flash Card | 1021208 |
| | 64MB Flash Card | 1021209 |
| | 40+GB Hard Disk | 13N1530 |
| Warranty | 1-year Onsite Repair | Base |
| | 1-year Onsite Repair extended warranty | 2349404 |
| | 2-year Onsite Repair extended warranty | 2349405 |
| | 3-year Onsite Repair extended warranty | 2349406 |



- 100-sheet Multipurpose Feeder (standard)
- 500-sheet Drawer (standard)
- Duplex Unit (standard on dn & dtn, 20B2400)
- 500-Sheet Drawer (standard on dtn, 20B2300)
- 2000-sheet Drawer (20B2700)



StapleSmart™ Finisher
(20B3060)



5-bin Mailbox
(20B3000)

Options Not Pictured

| | |
|----------------------------|---------|
| 500-sheet Tray | 20B2373 |
| Banner Media Tray | 20B5000 |
| Envelope Drawer | 10Z3100 |
| Outdoor Media Drawer | 20B3340 |
| Printer Stand | 16N1708 |
| Output Expander | 20B3050 |
| Scanner Stand with Cabinet | 16C0700 |
| Scanner Shelf | 21J0055 |
| 4600 MFP Option | 21J0401 |

¹ Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798.

² Duty Cycle is defined as the maximum number of pages a device could deliver in a month. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs.

³ Recommended Monthly Page Volume is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage

Additional Part Numbers

| | | |
|--------------------------------|--|---------|
| Solutions | Traditional Chinese Font Card | 1021242 |
| | Simplified Chinese Font Card | 1021241 |
| | Japanese Font Card | 1021243 |
| | Korean Font Card | 1021240 |
| | Forms Card | 10Z0402 |
| | Card for PRESCRIBE | 10Z0404 |
| | PrintCryption™ Card | 10Z0403 |
| | Card for IPDS and SCS/Tne | 10Z0401 |
| | Bar Code Card | 10Z0400 |
| Connectivity | Internal Print Servers ¹ | |
| | MarkNet™ N8020 Gigabit Ethernet | 14S0200 |
| | MarkNet N8030 Fiber Ethernet | 14S0220 |
| | MarkNet N8050 802.11g Wireless | 14S0165 |
| | External Print Servers ² | |
| | MarkNet N7020e GigaBit Ethernet | 14T0220 |
| | N4050e 802.11g Wireless | 14T0145 |
| | Local Connections | |
| | RS-232C Serial Interface Card | 1021092 |
| Parallel 1284-B Interface Card | 1021091 | |
| Media | Glossy Paper (letter, 200 sheets) | 12A5950 |
| | Professional Colour Laser Transparencies (letter, 50 sheets) | 12A8240 |
| | Banner Paper (8.27 x 36 in.) | 12A8940 |
| | Outdoor Media (letter) | 12A8600 |

Terms & Conditions

Lexmark, MarkNet and Lexmark with diamond design are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. StapleSmart and PrintCryption are trademarks of Lexmark International, Inc. PCL is a registered trademark of Hewlett Packard Company. All other trademarks are the property of their respective owners. © 2007 Lexmark International, Inc. All rights reserved.

¹ Use of Internal Print Server disables network card resident in printer.
² Requires USB Connection