DOWNLOAD SPECS

imagePROGRAF TM-305

Main Unit Specs

Printer Type	5-Colour 36-inch Printer
Number of Nozzles	Total: 15,360 | MBK: 5,120 nozzles | C, M, Y, BK: 2,560 nozzles each
Nozzle Pitch	1,200 dpi | Non-firing nozzle detection and compensation
OS Compatibility	Windows® 7, 8.1, 10 (32/64bit) | Windows® Server 2008 R2, 2012, 2012 R2, 2016 (64bit) | Macintosh OS X v10.10.5-v10.12x
Standard Interfaces	USB 2.0 High-Speed | 10/100/1000 Base-T/TX | Wireless LAN (IEEE 802.11 b/g/n) | Direct USB Thumb Drive Printing
Ink Droplet Size	5 picoliter
Ink Capacity	130 ml or 300ml per colour

Ink Type	Pigment Ink
Colour Set	Pigment: Matte Black, Black, Cyan, Magenta, Yellow
Buffer Ram	128 GB (2 GB Physical)
Media Width	Cut Sheet - 8- 36 | Roll Feed - 8 - 36
Media Thickness	0.07-0.8mm
Maximum Roll Print Length	Roll Feed - 59′ (18 meters)
Maximum Media Roll Diameter	5.9 (150mm)
Borderless Printing Width	8”, 10, 12”, 14, 16” 17, 20”, 24, 36 B4 (10.12/257 mm), A3 (11.69/297 mm), A3+ (12.95/329 mm), A (16.54/420 mm), B2 (20.28/515 mm), A1 (23.39/594 mm), B1 (28.66/ 728 mm), A0 (33.11/841 mm)
Paper Feed Method	Roll Feed: One Roll, Top-loading, Front Output | Cut Sheet: Top Loading, Front Output
Languages	SGRaster, HPGL/2, HP-RTL, JPEG, PDF
Noise Level Approx.	Operation: 44 dB (A) or less | Standby: 35 dB (A) or less | Acoustic Power: 6.0 Bels or less
Physical Dimensions	42 x 51 x 35
Weight	Approx. 134 lbs (roll holder included, no inks, no print heads)
Power Source	AC100-240V (50-60Hz)
Power Consumption	Maximum: 69W or less | Standby 3.6W or less | Power Off: 0.3W or less (Compliant with Executive Order)
Operating Environment	Temperature: 59°-86° F (15°-30° C) Relative Humidity: 10-80% (No Condensation)

User-Replaceable Items	Print Head (PF-06) | Maintenance Cartridge (MC-31) | Ink Tanks (PFI-120/PFI-320) | Cutter E (CT-08)
Software Included	TM Unified Printer Driver, Accounting Manager, Apple AirPrint, Canon Print Service, Device Management Console, Direct Print & Share, Free Layout Tool, Free Layout Plus, imagePROG