



## 2230Fh

<b>Cabinet Color</b>	Piano Black Finish
<b>Panel</b>	TFT Active Matrix LCD 22" Widescreen, Diagonal 558.7mm Viewable Image Size Bright Glossy Panel
<b>Pixel Pitch</b>	0.282mm x 0.282mm
<b>Display Area</b>	474mm x 296mm
<b>Brightness</b>	300 cd/m2 (typ)
<b>Contrast Ratio</b>	20,000:1 (dynamic)
<b>Response Time</b>	2ms (typ)
<b>Viewing Angle</b>	Horizontal: 170 Degrees (CR>10) Vertical: 160 Degrees (CR>10)
<b>Compatibility</b>	PC/Windows, Mac® Equipped With Analog VGA Dsub or DVI Port
<b>Scanning Frequency</b>	Horizontal: 30K~83KHz Vertical: 56~75 Hz
<b>Pixel Frequency</b>	165MHz
<b>Maximum Resolution</b>	1680x1050x60Hz
<b>Recommended Resolution</b>	1680x1050@60Hz
<b>Supported Resolutions</b>	640x480@56/60/67/72/75Hz, 720x400@70Hz, 832x624@75Hz 800x600@56/60/72/75Hz, 1024x768@60/70/75Hz 1152x864@75Hz, 1440x900@60Hz, 1280x960@60Hz 1680x1050@60Hz
<b>Color</b>	16.7M
<b>Signal Input</b>	Analog: 0.7Vp-p(standard), 75 OHM, Positive
<b>Digital Input</b>	DVI-D & HDMI with HDCP*
<b>Connectors</b>	Analog RGB Signal: 15-pin D-sub Male Digital Signal: 24-pin DVI-D Power: (3-Pin Plug CEE22)
<b>Power Source</b>	Universal 100~240VAC, 50/60Hz
<b>Power Consumption</b>	49Watts ( Max. )
<b>Plug &amp; Play</b>	DDC/2B, DDC/CI
<b>EPA ENERGY STAR®</b>	Yes
<b>User Control</b>	Navigation Key (Auto, Eco/Up, Down, Menu), Power
<b>OSD Languages</b>	8 Languages including English, French and Spanish
<b>Regulations</b>	cULus, FCC, CE, Certified for Windows Vista Logo, ROHS
<b>Built-in Speakers</b>	2W x 2
<b>Other Features</b>	720p/1080i HD Compatible, Aluminum Navigation Key, User Friendly Graphical OSD Menu, VESA 100mm Wall Mount Compliant**, Kensington Security Slot, includes AOC proprietary i-Menu software OSD
<b>Dimensions (WxHxD mm)</b>	Monitor: 510x417x220, Carton: 562x454x132
<b>Dimensions (WxHxD inches)</b>	Monitor: 20.1x16.4x8.7, Carton: 22.1x17.9x5.2
<b>Weight</b>	11.4 lbs (5.2 kgs) Net 14.7 lbs (6.7 kgs) Gross
<b>Loading Qty w/pallet</b>	20' = 800 pcs.; 40' Std = 1680 pcs.
<b>UPC Code</b>	685417021185

Note: Specifications are subject to change without notice. \*High-bandwidth Digital Content Protection: Enables viewing of High-Definition contents. \*\*Wall mount arm & bracket not included. Windows Vista and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries.