Raider GE67Hx 12UGS-070

Manufacturer Part #	RaiderGE6712070
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business.)
CPU	Core i7-12800HX 8+8Core
CPU Speed	1.5-4.8 GHz
Color	Dark Grey
Screen Size	15.6" OLED QHD, Wide View Angle 240Hz Thin Bezel, 100% DCI-P3
Resolution	2560x1440 (16:9)
GPU	NVIDIA® GeForce RTX™ 3070 TI Laptop GPU Up to 1535MHz Boost Clock, 150W Maximum Graphics Power with Dynamic Boost. Max. 205W CPU-GPU Power with MSI OverBoost Technology. *May vary by scenario.
Video Memory	8G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (84 Key)
Speaker	Sound by Dynaudio, 2x1W Speaker, 2x2W Duo Wave Woofer
Memory	16GB (8GB*2) DDR5 4800MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2)
Bluetooth	BT 5.2
Card Reader	SD7.0
Webcam	1080p FHD Webcam
USB	1x USB3.2 Gen 2; 2x USB3.2 Gen 1
Type-C Port	1x Thunderbolt™ 4; 1x USB 3.2 Gen 2/DP
Video Port	1x HDMI (8K @ 60Hz / 4K @ 120Hz)
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	330W
Battery Pack	4 cell (99.9Whr)
Dimension	14.09"x 10.51"x 0.92"
Weight	5.24 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)