

Tripp Lite

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

SmartRack Roof-Mounted Fan Panel - 6 208/240V high-performance fans; 420 CFM; C14 inlet

MODEL NUMBER: SRXFANROOF



Description

Tripp Lite's SmartRack SRXFANROOF is ideal for increasing the ventilation in all rack enclosure server cabinets. The unit features (6) 208-240V high performance fans mounted in a roof panel, and includes toolless mounting hardware. Built-in cable access holes for routing of cables through fan roof panel. Supports 208-240V 50/60 Hz AC input.

COMPATIBLE SMARTRACK ENCLOSURES - SR25UB, SR25UBKD, SR25UBSP1, SR25UBTAA, SR42UB, SR42UBCL, SR42UBEXP, SR42UBG, SR42UBKD, SR42UBSP1, SR42UBTAA, SR48UB, SR48UBCL, SR48UBEXP, SR48UBSP1, SR42UBTAA, and other Tripp Lite SmartRack enclosures that specify the use of this accessory.

Features

- Ideal for increasing the ventilation in all rack enclosure server cabinets
- Features (6) 208-240V high performance fans mounted in a roof panel
- Includes toolless mounting hardware
- Built-in cable access holes for routing of cables through fan roof panel
- Supports 208-240V 50/60 Hz AC input
- Compatible SmartRack Enclosures: SR25UB, SR25UBKD, SR25UBSP1, SR25UBTAA, SR42UB, SR42UBCL, SR42UBEXP, SR42UBG, SR42UBKD, SR42UBSP1, SR42UBTAA, SR48UB, SR48UBCL, SR48UBEXP, SR48UBSP1, SR42UBTAA, and other Tripp Lite SmartRack enclosures that specify the use of this accessory

Specifications

OVERVIEW

Highlights

- Roof Mount Fan Panel 208-240V
- Ideal for increasing the ventilation of SmartRacks
- Features (6) 208-240V fans mounted in a roof panel
- Tooless mounting hardware included
- · Cold rolled steel with black finish

Package Includes

- SRXFANROOF 208-240V 50/60Hz fan roof
- Tooless mounting hardware
- 6 inch C14 inlet dongle (usersupplied input cord required)





UPC Code	037332144553
INPUT	
Nominal Input Voltage(s) Supported	208V AC; 230V AC; 240V AC
Nominal Input Voltage Description	208-240V AC 50/60 Hz
Input Connection Type	IEC C14 inlet dongle (user-supplied input cord required)
Voltage Compatibility (VAC)	208; 230; 240
COOLING	
Cooling Type	Passive
PHYSICAL	
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	58.17 x 8.89 x 90.93
Shipping Dimensions (hwd / in.)	22.90 x 3.50 x 35.80
Shipping Weight (kg)	11.20
Shipping Weight (lbs.)	24.70
Unit Dimensions (hwd / cm)	5,33 x 55,63 x 90,17
Unit Dimensions (hwd / in.)	2.1 x 21.9 x 35.5
Unit Weight (kg)	9.98
Unit Weight (lbs.)	22
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies