DESKTOP

Aegis RS 14th

AEGIS RS 14NUF7-639US

Specification

Manufacturer Part #	AeRS14NUF639
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business)
CPU	Intel® Core™ i7-14700KF
Chipset	Intel Z790
Motherboard	PRO Z790 WIFI
CPU Cooler	240mm Liquid Cooler
VGA	NVIDIA® GeForce RTX™ 4070 TI
Memory (GB)	32GB DDR5 (2 x 16GB)
LAN	1x RJ45 (2.5Gbps)
Wireless Communication	Intel® Wi-Fi 7
Audio	1x Mic-in 1x Headphone-out
Video Port	1xHDMI-out(2.1) 3xDP-out(1.4a)
Expansion Slots	4x PCI-E x16 slot 2x PCI-E x1 slot 2x M.2 (1 free) 4x SATA 6G (6 free)
USB	Front: 2x USB 3.2 Gen 1 Type-A 1x USB 3.2 Gen2 Type-C Rear: 4x USB 3.2 Gen 1 5Gbps (Type-A) 1x USB 3.2 Gen 2x2 20Gbps (Type-C) 2x USB 2.0
HDD/SSD	2TB M.2 NVMe Gen4
Peripherals	MSI Gaming Keyboand and Mouse
Power Supply	750W
Power Efficiency Level	80+ Gold
Dimensions	8.46" x 16.93" x 17.72"
Weight	29.98 lbs
Warranty	1 Year

"2023-11-04 - Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."