HP Z4 Rack G5 Workstation (A02LHUA)

Overview

Compactly Rackable. Uniquely Powerful

Empower a flexible workforce with Z by HP pro-level performance in a high-density 1U footprint. Specifically designed to pack more units in a single rack, this slim powerhouse delivers the performance your team needs. All with the ability to upgrade and expand as compute demands evolve.

Workhorse Power. Compact 1U size

This 1U workstation packs impressive power for advanced VFX, 3D modeling, and rendering. Get an Intel® Xeon® W-series CPU, [1] support for entry or high-end graphics, and large memory configurations, all with room to upgrade and expand.

Comprehensive security. Reliability you can trust.

Get peace of mind with a workstation that's built to endure. The Z4 Rack undergoes 360K hours of rigorous testing and is certified for pro apps. And with HP Wolf Security for Business, it's protected below, in, and above the OS.[2]

Upgrade and expand with ease

Invest in the technology you need now and expand as the compute demands of your workforce evolve. With an easily accessible, tool-less design, get access to add or swap components—like graphics, memory, and storage.

Part of the world's most sustainable PC portfolio[3]

At HP, we care about the impact our products have on our people, communities, and the planet. Z products are designed with sustainability at the forefront. So, you can take pride in choosing Z, knowing that you are helping protect our shared future.

Features

Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

Intel® Xeon® W processor

Get optimized performance whether your professional application utilizes high core count or high frequency with the Intel® Xeon® W processor.[1]

Ultra Fast Memory Configurations

Accelerate your workflow and power through memory-intensive workloads with fast visualization, advanced visual effects, and rendering.

Expansion Slots

Support the highest performance workflows, today and beyond.

Power Supply

With dual power supply, you have power to stay up and running. Choose an aggregated option—combining two 675W power supplies—or a redundant option for critical workflows.

---

[1] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[2] HP Wolf Security for Business requires Windows 10 Pro or higher, includes various HP security features and is available on HP Pro, Elite and Workstation products. See product details for included security features and OS requirement.

[3] Applies to HP PCs, Workstations and Displays manufactured after January 2019. Based on most Gold and Silver EPEAT® registrations by meeting all required criteria and achieving 50-74% of the optional points for EPEAT® Silver and 75-100% of the optional points for EPEAT® Gold according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.

Specifications

Form factor	1U rackable workstation
Operating system	Windows 11 Pro[1]
Processor family	Intel® Xeon® W processor
Processor	Intel® Xeon® W3-2423 (up to 4.0 GHz with Intel® Turbo Boost Technology, 15 MB L3 cache, 6 cores, 12 threads)[6,7]
Chipset	Intel® W790
Memory	16 GB DDR5-4800 MHz RAM (1 x 16 GB)
Memory Slots	4 DIMM
Internal Storage	512 GB HP Z Turbo Drive Dual Pro TLC SSD
Hard drive (2nd)	512 GB HP Z Turbo Drive PCIe® Gen4 TLC M.2 SSD
Internal drive bays	Two 2.5" M.2 or one 3.5" SATA
External drive bays	Two 2.5" M.2
Audio	Realtek ALC3205-CG
Minimum dimensions (W x D x H)	4.3 x 43.8 x 65.6 cm (without rack mounting ears)
Minimum dimensions (W x D x H)	1.69 x 17.25 x 25.8 in (without rack mounting ears)
Weight	Starting at 9.5 kg (without rack rails); Starting at 12.5 kg (with rack rails) *(Exact weight depends on configuration.)*
Weight	Starting at 21.6 lb (without rack rails); Starting at 27.6 lb (with rack rails) *(Exact weight depends on configuration.)*
Keyboard	HP USB 320K Keyboard
Pointing device	HP Wired 320M Mouse
Ports	4 USB Type-A 5Gbps signaling rate (1 charging); 1 headset connector
Expansion slots	2 M.2 PCIe 4 x4; 1 PCIe 5 x16 mechanical (x8 electrical); 1 PCIe 5 x8 mechanical (x8 electrical); 1 PCIe 5 x16 mechanical (x8 or x16 electrical) *(PCIe slots 2 and 3 only come standard if the configuration demands them. Otherwise, they are an optional add-on feature via the Dual Slot Riser, which can be configured CTO or aftermarket.)*
Ports	2 USB Type-A 5Gbps signaling rate; 1 RJ-45
Management features	HP Anyware Remote System Controller; HP Client Management Script Library (download); HP Cloud Recovery; HP Driver Packs; HP Image Assistant Gen5 (download)[8,28,29,31]
Security management	Full volume encryption; HP Secure Erase; Kensington lock slot; Secure authentication; TPM 2.0 certified; HP BIOSphere; HP Sure Run; HP Sure Click; HP Sure Sense; HP Sure Admin; HP Platform Certificate; HP Sure Start; HP Sure Recover; Self-Encrypted Drives[13,14,15,16,17,18,19,20]

Software included	HP PC Hardware Diagnostics UEFI; HP Performance Advisor; HP Support Assistant; HP PC Hardware Diagnostics Windows; HP Privacy Settings; HP Desktop Support Utilities; HP Manageability Integration Kit; HP Notifications; HP Anyware; HP Data Science Stack; HP Services Scan; HP Data Science Stack Manager; myHP[8,10,11,12,26,27,30,32]
UPC number	198122566228

Additional specifications

Available software	HP Smart Support
ECC memory	non-ECC
Graphic card footnote number	[23]
Graphics	Discrete
Graphics (discrete)	NVIDIA® Quadro® T400 (4 GB GDDR6 dedicated)
Graphics card brand	NVIDIA®
Graphics card family	Quadro®
Graphics card memory size	4
Graphics card memory size uom	GB
Graphics card memory type	GDDR6
I/O Port location	Rear
I/O Port location	Front
Legal tagline	HP recommends Windows 11 Pro for business
Memory and storage	16 GB memory; 1 TB SSD storage
Memory layout (slots & size)	1 x 16 GB
Memory module type	DIMM
Memory size	16
Memory size uom	GB
Memory speed	4800
Memory speed uom	MHz
Memory type	DDR5
Model Number	T400
Number of memory slots	1
Playbook TS icon OS	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03905482.png
Playbook TS icon battery life	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03905264.png
Playbook TS icon connectivity	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201987.png
Playbook TS icon dimensions tower	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201997.png
Playbook TS icon graphics	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08169202.png
Playbook TS icon memory	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08267700.png
Playbook TS icon processor	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201972.png
Playbook TS icon storage	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192819.png
Playbook TS icon weight imperial	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c05790117.png

Playbook TS icon weight metric	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08267650.png
Processor Brand	Intel®
Processor cache	15 MB L3
Processor core	6
Processor family	Xeon® W
Processor frequency technology	Intel® Turbo Boost Technology
Processor maximum frequency	4.0
Processor maximum frequency uom	GHz
Processor model	2423
Processor threads	12
Product long name specifications	HP Z4 Rack G5 Workstation, Windows 11 Pro, Intel® Xeon® W, 16GB RAM, 512GB SSD, NVIDIA® Quadro® T400
Product short name specifications	HP Z4 Rack G5 Workstation, Intel® Xeon® W, 16GB RAM, 512GB SSD
Standard memory note	Transfer rates up to 4800 MT/s.
Storage brand 01	HP Z Turbo Drive
Storage capacity	512
Storage capacity uom 01	GB
Storage form factor 01	M.2
Storage interface 01	PCIe® Gen 4
Storage memory technology 01	TLC
Storage type	SSD
Storage type 01	SSD
UNSPSC code	43211515

---

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See http://www.windows.com.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See http://www.intel.com/technology/turboboost/ for more information.

[8] Optional or add-on feature.

[10] HP Performance Advisor Software - HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one-and every day after. Learn more or download at: https://www8.hp.com/us/en/workstations/performance-advisor.html .

[11] HP Support Assistant requires Windows and Internet access.

[12] HP Manageability Integration Kit can be downloaded from http://www8.hp.com/us/en/ads/clientmanagement/overview.html .

[13] HP Sure Click requires Windows 10 or 11 Pro or higher. See https://bit.ly/2PrLT6A_SureClick for complete details.

[14] HP Sure Start requires Windows 10 or 11 or higher.

[15] HP Sure Recover Gen4 is available on select HP PCs and requires an open network connection. You must back up important files, data, photos, videos, etc. before using HP Sure Recover to avoid loss of data.

[16] HP Sure Sense requires Windows 10 or 11 Pro or Enterprise and higher.

[17] HP Sure Run Gen5 requires Windows 1o or 11 Pro or higher.

[18] HP Sure Admin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from http://www.hp.com/go/clientmanagement and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.

[19] HP Secure Erase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88 "Clear"" sanitation method. HP Secure Erase does not support platforms with Intel® Optane™.

[20] HP BIOSphere Gen6 features may vary depending on the platform and configurations.

[26] Network access required. HP Anyware software and licensing are available through a 1- or 3-year subscription. Renewal is required after the subscription term. HP Anyware subscriptions are based on the number of concurrent PCoIP connections used (pay for the number of host connections, not the software) with a minimum order quantity of 5. For a limited time, an HP Anyware Professional subscription also includes access and support for ZCentral Remote Boost and ZCentral Connect and is available for purchase through an HP reseller or contact sales at hp.com/Anyware. ZCentral Remote Boost Sender requires Windows 10 and 11, RHEL/CentOS (7 or 8), or UBUNTU 18.04 or 20.04 LTS operating systems. macOS (10.14 or newer) operating system and ThinPro 7.2 are only supported on the receiver side. ZCentral Connect requires Windows (10 or 11) or Windows Server (2016 or 2019) operating system, Microsoft Active Directory and Intel Active Management Technology for select features. For system requirements and to install HP Anyware and Anyware Manager, refer to the Admin Guides at: https://docs.teradici.com/find/product/hp-anyware.

[27] Z by HP Data Science Stack Manager requires Windows 10 version 21H2 (Build 19044) and higher or 64-bit Ubuntu 20.04 and is available on select Z workstations.

[28] HP Anyware Remote System Controller is an optional feature.

[29] Internet access required. Automation of tasks and viewing system information only available with select Z desktop workstations, see datasheet for details. Fleet management and viewing of consolidated reports from all devices requires HP Anyware Remote System Management. HP Anyware Integrated Remote System Controller not compatible with Z2 Mini platforms and not recommended for non-Z devices. HP service and support not available for non-Z devices. Full suite of hardware alerts available with select Z desktop workstations. See datasheet for details.

[30] myHP requires Windows OS.

[31] HP Cloud Recovery is available for Z by HP, HP Elite and Pro desktops and laptops PCs with Intel® or AMD processors and requires an open, wired network connection. Note: You must back up important files, data, photos, videos, etc. before use to avoid loss of data. For details, please refer to: https://support.hp.com/us-en/document/c05115630 .

[32] HP Services Scan is provided with Windows Update on select products and will check entitlement on each hardware device to determine if an HP TechPulse-enabled service has been purchased, and will download applicable software automatically. HP TechPulse is a telemetry and analytics platform that provides critical data around devices and applications. For full system requirements or to disable this feature, please visit http://www.hpdaas.com/requirements . Not applicable in China.

Monitors

Business Monitors

★ : Recommended

P-Series

HP P24v G5 FHD Monitor	64W18A6	
HP P24v G5 FHD Monitor	64W18A7	
HP P24v G5 FHD Monitor	64W18AA	
HP P24v G5 FHD Monitor	64W18AS	
HP P24v G5 FHD Monitor	64W18AT	
HP P22 G4 22 FHD Monitor	1A7E4AA	obsolete
HP P22 G4 22 FHD Monitor	1A7E4AS	obsolete
HP P22 G4 22 FHD Monitor	1A7E4AT	obsolete
HP P22 G5 FHD Monitor	64X86A7	
HP P22 G5 FHD Monitor	64X86AA	
HP P22 G5 FHD Monitor	64X86AS	
HP P22 G5 FHD Monitor	64X86AT	
HP P22a G4 FHD Monitor	3Y0Q1A6	obsolete
HP P22a G4 FHD Monitor	3Y0Q1AA	obsolete
HP P22a G5 FHD Monitor - P22a	8D5J1AA	
HP P22b G5 FHD Monitor - P22b	8D5K4AA	
HP P22h G5 FHD Monitor	64W30A7	
HP P22h G5 FHD Monitor	64W30AA	
HP P22h G5 FHD Monitor	64W30AS	
HP P22h G5 FHD Monitor	64W30AT	
HP P22v G5 FHD Monitor	64V81A6	
HP P22v G5 FHD Monitor	64V81A7	
HP P22v G5 FHD Monitor	64V81AA	
HP P22v G5 FHD Monitor	64V81AS	
HP P22v G5 FHD Monitor	64V81AT	
HP P22v G5 FHD Value Monitor	7N909AT	
HP P24 G5 FHD Monitor	64X66A7	
HP P24 G5 FHD Monitor	64X66AA	
HP P24 G5 FHD Monitor	64X66AF	
HP P24 G5 FHD Monitor	64X66AS	

HP P24 G5 FHD Monitor	64X66AT	
HP P24a G4 FHD Monitor	3Y0Q4A6	obsolete
HP P24a G4 FHD Monitor	3Y0Q4AA	obsolete
HP P24a G5 FHD Monitor - P24a	8D5J5AA	
HP P24h G4 FHD Monitor	7VH44AA	
HP P24h G4 FHD Monitor	7VH44AS	obsolete
HP P24h G4 FHD Monitor	7VH44AT	obsolete
HP P24h G4 FHD Monitor	9UJ13A8	
HP P24h G4 FHD Monitor	9UJ13AA	
HP P24h G5 FHD Monitor	64W34A7	
HP P24h G5 FHD Monitor	64W34AA	
HP P24h G5 FHD Monitor	64W34AS	
HP P24h G5 FHD Monitor	64W34AT	
HP P24v G4 Monitor	9TT78AA	
HP P24v G5 FHD Value Monitor	7N914AT	
HP P27 G5 FHD Monitor	64X69A7	
HP P27 G5 FHD Monitor	64X69AA	
HP P27 G5 FHD Monitor	64X69AS	
HP P27 G5 FHD Monitor	64X69AT	
HP P27h G5 FHD Monitor	64W41A7	
HP P27h G5 FHD Monitor	64W41AA	
HP P27h G5 FHD Monitor	64W41AS	
HP P27h G5 FHD Monitor	64W41AT	
HP P32u G5 QHD USB-C Monitor	64W51A7	
HP P32u G5 QHD USB-C Monitor	64W51AA	
HP P32u G5 QHD USB-C Monitor	64W51AS	
HP P32u G5 QHD USB-C Monitor	64W51AT	
HP P34hc G4 WQHD USB-C Curved Monitor	21Y56A7	
HP P34hc G4 WQHD USB-C Curved Monitor	21Y56AA	
HP P34hc G4 WQHD USB-C Curved Monitor	21Y56AS	
HP P34hc G4 WQHD USB-C Curved Monitor	21Y56AT	

E-Series

HP E22 G5 FHD Monitor	6N4E8AA	
HP E22 G5 FHD Monitor	6N4E8AS	
HP E22 G5 FHD Monitor	6N4E8AT	

HP E22 G5 FHD Monitor	6N4E8E9	
HP E23 G4 FHD Monitor	9VF96AA	obsolete
HP E24 G4 FHD Monitor	9VF99A7	
HP E24 G4 FHD Monitor	9VF99AA	
HP E24 G4 FHD Monitor	9VF99AS	
HP E24 G4 FHD Monitor	9VF99AT	
HP E24 G5 FHD Monitor	6N6E9AA	
HP E24 G5 FHD Monitor	6N6E9AS	
HP E24 G5 FHD Monitor	6N6E9AT	
HP E24 G5 FHD Monitor	6N6E9E9	
HP E24 G5 FHD No Stand Monitor	6N6E9A9	
HP E24 G5 FHD PVC Free Monitor	6N6E9A5	
HP E24d G4 FHD USB-C Docking Monitor	6PA50A4	
HP E24d G4 FHD USB-C Docking Monitor	6PA50AS	
HP E24d G4 FHD USB-C Docking Monitor	6PA50AT	
HP E24d G4 FHD USB-C Docking Monitor	6PA50E9	
HP E24i G4 WUXGA Monitor	9VJ40A7	
HP E24i G4 WUXGA Monitor	9VJ40AA	
HP E24i G4 WUXGA Monitor	9VJ40AS	
HP E24i G4 WUXGA Monitor	9VJ40AT	
HP E24i G4 WUXGA No Stand Monitor	9VJ40A9	obsolete
HP E24i G4 Without Video Cable WUXGA Monitor	9VJ40A3	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32A7	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32AA	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32AS	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32AT	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32E9	
HP E24mv G4 FHD Conferencing Monitor	169L0AA	
HP E24mv G4 FHD Conferencing Monitor	169L0AS	
HP E24mv G4 FHD Conferencing Monitor	169L0AT	
HP E24mv G4 FHD Conferencing Monitor	169L0E9	
HP E24q G5 QHD Monitor	6N4F1AA	
HP E24q G5 QHD Monitor	6N4F1AS	
HP E24q G5 QHD Monitor	6N4F1AT	
HP E24q G5 QHD Monitor	6N4F1E9	
HP E24q G5 QHD PVC Free Monitor	6N4F1A5	

HP E24t G5 FHD Touch Monitor	6N6E6AA
HP E24t G5 FHD Touch Monitor	6N6E6AS
HP E24t G5 FHD Touch Monitor	6N6E6AT
HP E24t G5 FHD Touch Monitor	6N6E6E9
HP E24u G4 FHD USB-C Monitor	189T0AA
HP E24u G5 FHD USB-C Monitor	6N4D0AA
HP E24u G5 FHD USB-C Monitor	6N4D0AS
HP E24u G5 FHD USB-C Monitor	6N4D0AT
HP E24u G5 FHD USB-C Monitor	6N4D0E9
HP E24u G5 FHD USB-C PVC Free Monitor	6N4D0A5
HP E27 G5 FHD Monitor	6N4E2AA
HP E27 G5 FHD Monitor	6N4E2AS
HP E27 G5 FHD Monitor	6N4E2AT
HP E27 G5 FHD Monitor	6N4E2E9
HP E27 G5 FHD PVC Free Monitor	6N4E2A5
HP E27k G5 4K USB-C Monitor	6N4C4AA
HP E27k G5 4K USB-C Monitor	6N4C4AS
HP E27k G5 4K USB-C Monitor	6N4C4AT
HP E27k G5 4K USB-C Monitor	6N4C4E9
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29A7
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29AA
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29AS
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29AT
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29E9
HP E27q G4 QHD Monitor	9VG82A7
HP E27q G4 QHD Monitor	9VG82AA
HP E27q G4 QHD Monitor	9VG82AT
HP E27q G5 QHD Monitor	6N6F2AA
HP E27q G5 QHD Monitor	6N6F2AS
HP E27q G5 QHD Monitor	6N6F2AT
HP E27q G5 QHD Monitor	6N6F2E9
HP E27q G5 QHD No Stand Monitor	6N6F2A9
HP E27q G5 QHD PVC Free Monitor	6N6F2A5
HP E27u G4 QHD USB-C Monitor	189T3AA
HP E27u G5 QHD USB-C Monitor	6N4D3AA
HP E27u G5 QHD USB-C Monitor	6N4D3AS

HP E27u G5 QHD USB-C Monitor	6N4D3AT	
HP E27u G5 QHD USB-C Monitor	6N4D3E9	
HP E27u G5 QHD USB-C PVC Free Monitor	6N4D3A5	
HP E32k G5 4K USB-C Monitor	6N4D6AA	
HP E32k G5 4K USB-C Monitor	6N4D6AS	
HP E32k G5 4K USB-C Monitor	6N4D6AT	
HP E32k G5 4K USB-C Monitor	6N4D6E9	
HP E32k G5 4K USB-C PVC Free Monitor	6N4D6A5	
HP E34m G4 WQHD Curved USB-C Conferencing Monitor	40Z26A7	
HP E34m G4 WQHD Curved USB-C Conferencing Monitor	40Z26AA	
HP E34m G4 WQHD Curved USB-C Conferencing Monitor	40Z26AS	
HP E34m G4 WQHD Curved USB-C Conferencing Monitor	40Z26AT	
HP E34m G4 WQHD Curved USB-C Conferencing Monitor	40Z26E9	
HP E45c G5 DQHD Curved Monitor	6N4C1AA	
HP E45c G5 DQHD Curved Monitor	6N4C1AS	
HP E45c G5 DQHD Curved Monitor	6N4C1AT	
HP E45c G5 DQHD Curved Monitor	6N4C1E9	

Value Displays

HP M24m Conferencing Monitor	678U5AA	
HP M24m Conferencing Monitor	678U5AS	
HP M24m Conferencing Monitor	7N4J6AT	
HP M27m Conferencing Monitor	678U8AA	
HP M27m Conferencing Monitor	678U8AS	

Business LCD Monitors

HP P204v 19.5-inch Monitor	5RD66A7	
HP P204v 19.5-inch Monitor	5RD66AA	
HP P204v 19.5-inch Monitor	5RD66AS	obsolete
HP P204v 19.5-inch Monitor	5RD66AT	obsolete

Series 7 Pro

HP Series 7 Pro 23.8 inch FHD Monitor - 724pf	8X530AA	
HP Series 7 Pro 23.8 inch FHD Monitor - 724pf	8X530AT	
HP Series 7 Pro 23.8 inch FHD Monitor - 724pf	8X530E9	
HP Series 7 Pro 23.8 inch FHD Monitor - 724pf PVC Free	8X530A5	

HP Series 7 Pro 24 inch WUXGA Monitor - 724pn	8X534AA
HP Series 7 Pro 24 inch WUXGA Monitor - 724pn	8X534AT
HP Series 7 Pro 24 inch WUXGA Monitor - 724pn	8X534E9
HP Series 7 Pro 24 inch WUXGA USB-C Monitor - 724pu	8Y2F7AA
HP Series 7 Pro 24 inch WUXGA USB-C Monitor - 724pu	8Y2F7AT
HP Series 7 Pro 24 inch WUXGA USB-C Monitor - 724pu	8Y2F7E9
HP Series 7 Pro 27 inch 4K Thunderbolt 4 Monitor - 727pk	8J9G2AA
HP Series 7 Pro 27 inch 4K Thunderbolt 4 Monitor - 727pk	8J9G2AT
HP Series 7 Pro 27 inch 4K Thunderbolt 4 Monitor - 727pk	8J9G2E9
HP Series 7 Pro 27 inch QHD Monitor - 727pq	8J4D8AT
HP Series 7 Pro 27 inch QHD Monitor - 727pq	8J4D8E9
HP Series 7 Pro 27 inch QHD Thunderbolt 4 Monitor - 727pu	8J9E6AT
HP Series 7 Pro 27 inch QHD Thunderbolt 4 Monitor - 727pu	8J9E6E9
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk	8Y2K9AA
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk	8Y2K9AT
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk	8Y2K9E9
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk PVC Free	8Y2K9A5
HP Series 7 Pro 39.7 inch 5K2K Conferencing Monitor - 740pm PVC Free	8Y2R2A5
HP Series 7 Pro 39.7 inch 5K2K Conferencing Monitor-740pm	8Y2R2AA
HP Series 7 Pro 39.7 inch 5K2K Conferencing Monitor-740pm	8Y2R2AT
HP Series 7 Pro 39.7 inch 5K2K Conferencing Monitor-740pm	8Y2R2E9

Z Displays

HP Z24f G3 FHD Display	3G828A7
HP Z24f G3 FHD Display	3G828AA
HP Z24f G3 FHD Display	3G828AT
HP Z24m G3 QHD Conferencing Display	4Q8N9A7
HP Z24m G3 QHD Conferencing Display	4Q8N9AA
HP Z24m G3 QHD Conferencing Display	4Q8N9AT
HP Z24m G3 QHD Conferencing Display	4Q8N9E9
HP Z24n G3 WUXGA Display	1C4Z5A7
HP Z24n G3 WUXGA Display	1C4Z5AA
HP Z24n G3 WUXGA Display	1C4Z5AT
HP Z24q G3 QHD Display	4Q8N4A7
HP Z24q G3 QHD Display	4Q8N4AA
HP Z24q G3 QHD Display	4Q8N4AT

HP Z24q G3 QHD Display	4Q8N4E9
HP Z24u G3 WUXGA USB-C Display	1C4Z6A7
HP Z24u G3 WUXGA USB-C Display	1C4Z6AA
HP Z24u G3 WUXGA USB-C Display	1C4Z6AT
HP Z24u G3 WUXGA USB-C Display	1C4Z6E9
HP Z25xs G3 QHD USB-C DreamColor Display	1A9C9A7
HP Z25xs G3 QHD USB-C DreamColor Display	1A9C9AA
HP Z25xs G3 QHD USB-C DreamColor Display	1A9C9AT
HP Z27k G3 4K USB-C Display	1B9T0A7
HP Z27k G3 4K USB-C Display	1B9T0AA
HP Z27k G3 4K USB-C Display	1B9T0AT
HP Z27q G3 QHD Display	1C4Z7A7
HP Z27q G3 QHD Display	1C4Z7A9
HP Z27q G3 QHD Display	1C4Z7AA
HP Z27q G3 QHD Display	1C4Z7AT
HP Z27u G3 QHD Display	1B9X2AA
HP Z27u G3 QHD Display	1B9X2AT
HP Z32k G3 4K USB-C Display	50U19A7
HP Z32k G3 4K USB-C Display	50U19AA
HP Z32k G3 4K USB-C Display	50U19AT
HP Z32k G3 4K USB-C Display	50U19E9
HP Z34c G3 WQHD Curved Display	30A19A7
HP Z34c G3 WQHD Curved Display	30A19AA
HP Z34c G3 WQHD Curved Display	30A19AT
HP Z34c G3 WQHD Curved Display	30A19E9
HP Z38c 37.5-inch Curved Display	Z4W65A4
HP Z38c 37.5-inch Curved Display	Z4W65A8
HP Z38c 37.5-inch Curved Display	Z4W65AT
HP Z40c G3 WUHD Curved Display	3A6F7AA
HP Z40c G3 WUHD Curved Display	3A6F7AT
HP Z40c G3 WUHD Curved Display	3A6F7E9

HP Home Monitors

HP Value Displays

HP 24mh 23.8-inch Display	1D0J9AA

HP 24mh 23.8-inch Display	1D0J9AS	
HP 24mh 23.8-inch Display	1D0J9E9	
HP 24mh 23.8-inch Display	7XM23AA	
HP 27mq 27-inch Display	1F2J9AA	
HP 27mq 27-inch Display	7XM25AA	
HP M22f FHD Monitor	2D9J9AA	
HP M22f FHD Monitor	2D9J9AS	
HP M22f FHD Monitor	2D9J9E9	
HP M22f FHD Monitor	2E2Y3A6	
HP M22f FHD Monitor	2E2Y3AA	
HP M24 Webcam Monitor	459J4AA	obsolete
HP M24f FHD Monitor	2D9K0AA	
HP M24f FHD Monitor	2D9K0AS	
HP M24f FHD Monitor	2D9K0E9	
HP M24f FHD Monitor	2E2Y4A6	
HP M24f FHD Monitor	2E2Y4AA	
HP M24fe FHD Monitor	43G27AA	
HP M24fe FHD Monitor	43G27AS	
HP M24fe FHD Monitor	43G27E9	
HP M24fe FHD Monitor	43G28AA	
HP M24fw FHD Monitor	2D9K1AA	
HP M24fw FHD Monitor	2D9K1AS	
HP M24fw FHD Monitor	2D9K1E9	
HP M24fw FHD Monitor	2E2Y5AA	
HP M24fw FHD Monitor	43B20AA	
HP M24fwa FHD Monitor	34Y22AA	
HP M24fwa FHD Monitor	34Y22AS	
HP M24fwa FHD Monitor	34Y22E9	
HP M24fwa FHD Monitor	34Y23AA	
HP M32f FHD Monitor	2H5M7AA	
HP M32f FHD Monitor	2H5M7AS	
HP M32f FHD Monitor	2H5M7E9	
HP M32f FHD Monitor	2H5N0AA	
HP M32fw FHD Monitor	6R6E6AA	
HP M34d WQHD Curved Monitor	3B1W4AA	obsolete
HP M34d WQHD Curved Monitor	3B1W4AS	obsolete

HP M34d WQHD Curved Monitor	3B1W4E9	
HP M34d WQHD Curved Monitor	3B1W5AA	obsolete
HP V28 4K Monitor	8WH59AA	

HP Home Monitors

HP M27 Webcam Monitor	459K0AA	obsolete
HP M27f FHD Monitor	2G3D3AA	
HP M27f FHD Monitor	2G3D3AS	
HP M27f FHD Monitor	2G3D3E9	
HP M27f FHD Monitor	2H0N1AA	
HP M27fe FHD Monitor	43G45AA	
HP M27fe FHD Monitor	43G45AS	
HP M27fe FHD Monitor	43G45E9	
HP M27fe FHD Monitor	43G46AA	
HP M27fq QHD Monitor	2H4B5AA	
HP M27fq QHD Monitor	2H4B5AS	
HP M27fq QHD Monitor	2H4B5E9	
HP M27fq QHD Monitor	2H4B8AA	
HP M27fw FHD Monitor	2H1A4AA	
HP M27fw FHD Monitor	2H1A4AS	
HP M27fw FHD Monitor	2H1A4E9	
HP M27fw FHD Monitor	2H1B1AA	
HP M27fw FHD Monitor	43B24AA	
HP M27fwa FHD Monitor	356D5AA	
HP M27fwa FHD Monitor	356D5AS	
HP M27fwa FHD Monitor	356D5E9	
HP M27fwa FHD Monitor	356D6AA	
HP M27ha FHD Monitor	22H94AA	
HP M27ha FHD Monitor	22H94AS	
HP M27ha FHD Monitor	22H94E9	
HP M27ha FHD Monitor	35M57AA	
HP U28 4K HDR Monitor	1Z978AA	
HP U28 4K HDR Monitor	1Z979AA	
HP U28 4K HDR Monitor	1Z980AA	
HP U28 4K HDR Monitor	1Z980AS	
HP U32 4K HDR Monitor	368Y5AA	

HP U32 4K HDR Monitor	368Y5AS	
HP U32 4K HDR Monitor	368Y5E9	
HP V20 HD+ Monitor	1H848AA	obsolete
HP V20 HD+ Monitor	1H849A6	
HP V20 HD+ Monitor	1H849AA	
HP V20 HD+ Monitor	1H850AA	obsolete
HP V20 HD+ Monitor	1H850AS	obsolete
HP V22i G5 FHD Monitor	6D8G8AA	
HP V22i G5 FHD Monitor	6D8G8E9	
HP V22i G5 FHD Monitor	6D8G9A6	
HP V22i G5 FHD Monitor	6D8G9AA	
HP V22v G5 FHD Monitor	65P56AA	
HP V22v G5 FHD Monitor	65P56AS	
HP V22v G5 FHD Monitor	65P56E9	
HP V22v G5 FHD Monitor	65P57A6	
HP V22v G5 FHD Monitor	65P57AA	
HP V22ve G5 FHD Monitor	6D8G2AA	
HP V22ve G5 FHD Monitor	6D8G2AS	
HP V22ve G5 FHD Monitor	6D8G2E9	
HP V22ve G5 FHD Monitor	6D8G3AA	
HP V24i G5 FHD Monitor	65P58AA	
HP V24i G5 FHD Monitor	65P58AS	
HP V24i G5 FHD Monitor	65P58E9	
HP V24i G5 FHD Monitor	65P59A6	
HP V24i G5 FHD Monitor	65P59AA	
HP V24ie G5 FHD Monitor	6D8H0AA	
HP V24ie G5 FHD Monitor	6D8H0AS	
HP V24ie G5 FHD Monitor	6D8H0E9	
HP V24ie G5 FHD Monitor	6D8H1AA	
HP V24v G5 FHD Monitor	65P62AA	
HP V24v G5 FHD Monitor	65P62AS	
HP V24v G5 FHD Monitor	65P62E9	
HP V24v G5 FHD Monitor	65P63AA	
HP V27c G5 FHD Curved Monitor	65P60AA	
HP V27c G5 FHD Curved Monitor	65P60E9	
HP V27c G5 FHD Curved Monitor	65P61AA	

HP V27i G5 FHD Monitor	65P64AA	
HP V27i G5 FHD Monitor	65P64AS	
HP V27i G5 FHD Monitor	65P64E9	
HP V27i G5 FHD Monitor	65P65AA	
HP V27ie G5 FHD Monitor	6D8H2AA	
HP V27ie G5 FHD Monitor	6D8H2AS	
HP V27ie G5 FHD Monitor	6D8H2E9	
HP V27ie G5 FHD Monitor	6D8H3AA	

Pavilion Displays

HP Pavilion 22cwa 21.5-inch IPS LED Backlit Monitor	T4Q59AA	obsolete

Series 5

HP Series 5 23.8 inch FHD Height Adjust Monitor - 524sh	94C19AA	
HP Series 5 23.8 inch FHD Height Adjust Monitor - 524sh	94C19AS	
HP Series 5 23.8 inch FHD Height Adjust Monitor - 524sh	94C19E9	
HP Series 5 23.8 inch FHD Height Adjust Monitor - 524sh	94C20AA	
HP Series 5 23.8 inch FHD Monitor - 524sf	94C17AA	
HP Series 5 23.8 inch FHD Monitor - 524sf	94C17AS	
HP Series 5 23.8 inch FHD Monitor - 524sf	94C17E9	
HP Series 5 23.8 inch FHD Monitor - 524sf	94C18AA	
HP Series 5 23.8 inch FHD Monitor with Speakers - 524sa	94C36AA	
HP Series 5 23.8 inch FHD Monitor with Speakers - 524sa	94C36AS	
HP Series 5 23.8 inch FHD Monitor with Speakers - 524sa	94C36E9	
HP Series 5 23.8 inch FHD Monitor with Speakers - 524sa	94C37AA	
HP Series 5 23.8 inch FHD White Monitor - 524sw	94C21AA	
HP Series 5 23.8 inch FHD White Monitor - 524sw	94C21AS	
HP Series 5 23.8 inch FHD White Monitor - 524sw	94C21E9	
HP Series 5 23.8 inch FHD White Monitor - 524sw	94C22AA	
HP Series 5 27 inch FHD Height Adjust Monitor - 527sh	94C50AA	
HP Series 5 27 inch FHD Height Adjust Monitor - 527sh	94C50AS	
HP Series 5 27 inch FHD Height Adjust Monitor - 527sh	94C50E9	
HP Series 5 27 inch FHD Height Adjust Monitor - 527sh	94C51AA	
HP Series 5 27 inch FHD Monitor - 527sf	94F44AA	
HP Series 5 27 inch FHD Monitor - 527sf	94F44AS	
HP Series 5 27 inch FHD Monitor - 527sf	94F44E9	

HP Series 5 27 inch FHD Monitor - 527sf	94F45AA
HP Series 5 27 inch FHD Monitor with Speakers - 527sa	94F48AA
HP Series 5 27 inch FHD Monitor with Speakers - 527sa	94F48AS
HP Series 5 27 inch FHD Monitor with Speakers - 527sa	94F48E9
HP Series 5 27 inch FHD Monitor with Speakers - 527sa	94F49AA
HP Series 5 27 inch FHD White Monitor - 527sw	94F46AA
HP Series 5 27 inch FHD White Monitor - 527sw	94F46AS
HP Series 5 27 inch FHD White Monitor - 527sw	94F46E9
HP Series 5 27 inch FHD White Monitor - 527sw	94F47AA
HP Series 5 31.5 inch FHD Monitor - 532sf	94F50AA
HP Series 5 31.5 inch FHD Monitor - 532sf	94F50AS
HP Series 5 31.5 inch FHD Monitor - 532sf	94F50E9
HP Series 5 31.5 inch FHD Monitor - 532sf	94F51AA

OMEN by HP Displays

OMEN 27u 4K Gaming Monitor	3G6W0AA
OMEN 27u 4K Gaming Monitor	3G6W0AS
OMEN 27u 4K Gaming Monitor	3G6W0E9
OMEN 27u 4K Gaming Monitor	3G6W1AA
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780D9AA
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780D9AS
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780D9E9
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780F0AA
OMEN by HP 27 inch FHD 165Hz Gaming Monitor - OMEN 27	780F9AA
OMEN by HP 27 inch FHD 165Hz Gaming Monitor - OMEN 27	780F9AS
OMEN by HP 27 inch FHD 165Hz Gaming Monitor - OMEN 27	780F9E9
OMEN by HP 27 inch FHD 165Hz Gaming Monitor - OMEN 27	780G0AA
OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G5AA
OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G5AS
OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G5E9
OMEN by HP 27 inch FHD 240Hz Gaming Monitor - OMEN 27s	780G6AA
OMEN by HP 27 inch QHD 165Hz Gaming Monitor - OMEN 27q	780H4AA
OMEN by HP 27 inch QHD 165Hz Gaming Monitor - OMEN 27q	780H4AS
OMEN by HP 27 inch QHD 165Hz Gaming Monitor - OMEN 27q	780H4E9
OMEN by HP 27 inch QHD 165Hz Gaming Monitor - OMEN 27q	780H5AA
OMEN by HP 27 inch QHD 240Hz Gaming Monitor - OMEN 27qs	780J4AA

OMEN by HP 27 inch QHD 240Hz Gaming Monitor - OMEN 27qs	780J4AS
OMEN by HP 27 inch QHD 240Hz Gaming Monitor - OMEN 27qs	780J4E9
OMEN by HP 27 inch QHD 240Hz Gaming Monitor - OMEN 27qs	780J5AA
OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G8AA
OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G8AS
OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G8E9
OMEN by HP 27 inch UHD 144Hz Gaming Monitor - OMEN 27k	780G9AA
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K6AA
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K6AS
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K6E9
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K7AA
OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K0AA
OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K0AS
OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K0E9
OMEN by HP 31.5 inch QHD 165Hz Gaming Monitor - OMEN 32q	780K1AA
OMEN by HP 34 inch WQHD 165Hz Curved Gaming Monitor - OMEN 34c	780K8AA
OMEN by HP 34 inch WQHD 165Hz Curved Gaming Monitor - OMEN 34c	780K8AS
OMEN by HP 34 inch WQHD 165Hz Curved Gaming Monitor - OMEN 34c	780K8E9
OMEN by HP 34 inch WQHD 165Hz Curved Gaming Monitor - OMEN 34c	780K9AA

Accessories

Memory

★ : Recommended

DDR5 Memory

16GB DDR5 (1x16GB) 4800 DIMM ECC REG China Memory	90L17AA
16GB DDR5 4800 ECC Memory	340K1AA
32GB DDR5 (1x32GB) 4800 DIMM ECC REG China Memory	90L18AA
32GB DDR5 4800 ECC Memory	340K2AA
64GB DDR5 (1x64GB) 4800 DIMM ECC REG China Memory	905S6AA
64GB DDR5 4800 ECC Memory	340K3AA

Batteries/Chargers/Adapters

Power Supplies

675W Z4 Rack EPA90 External Power Supply	8Y2L8AA

Power Cords

C13-C14 2.0m 10A 200-240V Countries Straight Desktop Power Cord	8R882AA
C13-C14 2.0m 15A 100-127V Countries Straight Desktop Power Cord	8R881AA
HP C13 1.83m AC Power Cord	6Z1T9AA

Graphics Cards

Graphics Cards

AMD Radeon Pro W6800 32GB GDDR6 6mDP Graphics	340K7AA
AMD Radeon Pro W7500 8 GB 4DP Graphics	8D6C2AA
AMD Radeon Pro W7600 8 GB 4DP Graphics	8D6B9AA
NVIDIA RTX 4000 Ada 20 GB 4DP Graphics	8D6B7AA
NVIDIA RTX 4500 Ada 24 GB 4DP Graphics	8D6C1AA
NVIDIA RTX 6000 Ada 48 GB 4DP Graphics	79C23AA
NVIDIA RTX 6000 Ada 48 GB 4DP w/NVIDIA Omniverse Enterprise Graphics	9X3E1AA
NVIDIA RTX A2000 12 GB 4mDP Graphics	5Z7D9AA
NVIDIA RTX A2000 12 GB 4mDP Graphics	5Z7D9AT
NVIDIA RTX A4000 16 GB 4DP Graphics	20X24AA
NVIDIA RTX A4000 16 GB 4DP Graphics	20X24AT
NVIDIA RTX A5000 24 GB 4DP Graphics	20X23AA

NVIDIA RTX A5000 24 GB 4DP Graphics	20X23AT
NVIDIA T1000 8 GB 4mDP Graphics	5Z7D8AA
NVIDIA T1000 8 GB 4mDP Graphics	5Z7D8AT
NVIDIA T400 4 GB 3mDP Graphics	5Z7E0AA
NVIDIA T400 4 GB 3mDP Graphics	5Z7E0AT

PC Controller/Controller Options

PC Processor Cards

Allied Telesis AT-2911T/2-901 Dual Port 1GbE NIC	6E3Y9AA
Intel Ethernet I350-T4 4-Port 1Gb NIC	W8X25AA
Intel I225V Single Port 2.5GbE PCIe NIC	406L9AA
NVIDIA Mellanox ConnectX-6 LX Dual Port 25GbE SFP28 NIC	436M8AA

PC Expansion Boards

HP Z4 Rack Dual PCIe Gen5 x16 + PCIe Gen5 x16(x8) slot Riser Kit	7K6C7AA

PC Networking Adapters

PC Fast Ethernet Adapters

Allied Telesis AT-2914SX/LC-901 1GB LC Fiber NIC	1C7Q2AA

Expansion Solution and Controller Cards

Port Adapters

HP 10GBase-T Flex IO	56Q71AA
HP 2.5GbE LAN Flex Port Z2 Mini	169K0AA
HP 2.5GbE LAN Flex Port Z2 Mini	169K0AT
HP Flex 1GbE Fiber LC Single Port	20J15AA
HP Serial Port Flex IO v3	5B895AA
HP Type-C SuperSpeed USB 20Gbps Front Premium Module	38T92AA
HP Z2 G5 Internal Serial and PS/2 Port	141K9AA

Remote Interfaces

HP Integrated Remote System Controller	7K6D9AA
HP Remote System Controller	7K6D7AA
HP Remote System Controller Main Board Adapter	7K6D8AA
HP Remote System Controller for Universal KVM	7K7N2AA

MultiBay Drive Adapters

HP Z4 Rack G5 2.5 in Dual Drive Cage Adapter	7K6C5AA	
HP Z4 Rack G5 3.5 in Drive Cage Adapter	7K6C6AA	

Cables/Cable Kits/Cable Adapters

Data Transfer Cables

HP 10GbE SFP+ SR/SW LC Fiber Optic Transceiver	860T8AA	
HP 25GbE SFP28 LC Fiber Optic Transceiver	860T9AA	

Audio and Video Cables

HP DisplayPort To VGA Adapter	AS615AA	
HP DisplayPort To VGA Adapter	AS615AT	obsolete
HP DisplayPort To VGA Adapter	F7W97AA	
HP DisplayPort to DVI-D Adapter	FH973AA	
HP DisplayPort to DVI-D Adapter	FH973AT	obsolete
HP DisplayPort to HDMI True 4K Adapter	2JA63AA	

Port Cables and Cable Adapters

HP Internal USB Port Kit	EM165AA	

Cable Adapters

HP Single miniDP-to-DP Adapter Cable	2MY05AA	
HP miniDP-to-DP Adapter Cables (Bulk 12)	2KW87A6	

Rack Brackets/Bezels/ Panels/Rails/ Trays/Mounting

Rack Kits

HP Rack Cable Management Arm	35Z34AA	

Mounting Kits

HP Z4 Rack Remote System Controller Arm Bracket	8D0Q8AA	

Rail Kits

HP ZCentral 4R Rail Rack kit	16G60AA	

Keyboards/Mice and Input Devices

Keyboards

HP Wired Desktop 320K Keyboard	9SR37AA
HP Wired Desktop 320K Keyboard	9SR37ET
HP Wired Desktop 320K Keyboard	9SR37UT

Mice

HP Wired Desktop 320M Mouse	9VA80AA
HP Wired Desktop 320M Mouse	9VA80ET
HP Wired Desktop 320M Mouse	9VA80UT

Keyboard and Mouse Kits

HP Wired Desktop 320MK Mouse and Keyboard	9SR36AA
HP Wired Desktop 320MK Mouse and Keyboard	9SR36ET
HP Wired Desktop 320MK Mouse and Keyboard	9SR36UT

PC Drives and Storage

Removable Hard Drive Enclosure

HP Z Turbo Drive Dual Pro PCIe-4x4 NVMe Carrier	56Q86AA
HP Z4 Rack 2.5 in Drive Carrier	7K6C3AA

PC Solid State Drives

Z Turbo 1TB 2280 PCIe-4x4 SED OPAL2 TLC M.2 SSD Module	38T76AA
Z Turbo 1TB PCIe-4x4 SED OPAL2 TLC Z4 Rack Kit SSD	7K6A7AA
Z Turbo 1TB PCIe-4x4 TLC China SSD Module	906H6AA
Z Turbo 1TB PCIe-4x4 TLC SSD Module	38T77AA
Z Turbo 2TB 2280 PCIe-4x4 SED OPAL2 TLC M.2 SSD Module	38T79AA
Z Turbo 2TB PCIe-4x4 SED OPAL2 TLC Z4 Rack Kit SSD	7K6B0AA
Z Turbo 2TB PCIe-4x4 TLC China SSD Module	906J0AA
Z Turbo 2TB PCIe-4x4 TLC SSD Module	38T75AA
Z Turbo 512GB 2280 PCIe-4x4 SED OPAL2 TLC M.2 SSD Module	38T81AA
Z Turbo 512GB 2280 PCIe-4x4 TLC China SSD Module	906H1AA
Z Turbo 512GB PCIe-4x4 SED OPAL2 TLC Z4 Rack Kit SSD	7K6A6AA
Z Turbo 512GB PCIe-4x4 TLC SSD Module	38T80AA

PC Rack Options

PC Bezels/Fascia Kits

HP ZCentral 4R Front Bezel Security	16G58AA

Network Adapters

Adapter Cards

Intel X550 10GBASE-T Dual Port NIC	1QL46AA

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly BT700 USB-A Bluetooth Adapter	786C4AA
Poly BT700 USB-C Bluetooth Adapter	786C5AA
Poly DA75 USB to QD Adapter	786C6AA
Poly DA85 USB to QD Adapter	786C7AA
Poly DA85-M USB to QD Adapter	786C8AA
Poly Savi 7210 Monaural DECT 1920-1930 MHz Top	783Q5AA
Poly Savi 7220 Stereo DECT 1920-1930 MHz Top	783Q6AA
Poly Savi 7310 Monaural DECT 1920-1930 MHz Top	783N0AA
Poly Savi 7310 Monaural Microsoft Teams Certified DECT 1920-1930 MHz Top	783N2AA
Poly Savi 7320 Stereo DECT 1920-1930 MHz Top	783N1AA
Poly Savi 7320 Stereo Microsoft Teams Certified DECT 1920-1930 MHz Top	783N3AA
Poly Savi 8210/8220 Universal Power Supply -9V 500mA	783M9AA
Poly Voyager Microsoft Teams Certified Office Base	786D0AA
Poly Voyager Office Base	786C9AA

Wired Headset

Poly Blackwire 3210 Monaural USB-A Headset	80S01AA
Poly Blackwire 3210 Monaural USB-A Headset (Bulk)	80S01A6
Poly Blackwire 3210 Monaural USB-C Black Headset +USB-C/A Adapter (Bulk)	8X2J8A6
Poly Blackwire 3210 Monaural USB-C Headset +USB-C/A Adapter	8X214AA
Poly Blackwire 3210 Monaural USB-C Headset +USB-C/A Adapter (Bulk)	8X214A6
Poly Blackwire 3215 Monaural USB-A Headset	80S06AA
Poly Blackwire 3215 Monaural USB-A Headset (Bulk)	80S06A6
Poly Blackwire 3215 Monaural USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X227AA
Poly Blackwire 3215 Monaural USB-C Headset +3.5mm Plug +USB-C/A Adapter (Bulk)	8X227A6
Poly Blackwire 3220 Stereo USB-A Headset	80S02AA
Poly Blackwire 3220 Stereo USB-A Headset (Bulk)	80S02A6
Poly Blackwire 3220 Stereo USB-C Black Headset +USB-C/A Adapter (Bulk)	8X2J9A6
Poly Blackwire 3220 Stereo USB-C Headset +USB-C/A Adapter	8X228AA
Poly Blackwire 3220 Stereo USB-C Headset +USB-C/A Adapter	93S87AA

Poly Blackwire 3220 Stereo USB-C Headset +USB-C/A Adapter (Bulk)	8X228A6
Poly Blackwire 3225 Stereo USB-A Headset	80S11AA
Poly Blackwire 3225 Stereo USB-A Headset (Bulk)	80S11A6
Poly Blackwire 3225 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X229AA
Poly Blackwire 3225 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter (Bulk)	8X229A6
Poly Blackwire 3310 Microsoft Teams Certified Headset +USB-C/A Adapter TAA	760Q7AA
Poly Blackwire 3310 Microsoft Teams Certified USB-A Headset	767F6AA
Poly Blackwire 3310 Monaural Microsoft Teams Certified USB-C Headset +USB-C/A Adapter	8X216AA
Poly Blackwire 3310 Monaural USB-C Headset +USB-C/A Adapter	8X215AA
Poly Blackwire 3310 USB-A Headset	767F7AA
Poly Blackwire 3315 Microsoft Teams Certified USB-A Headset	76J13AA
Poly Blackwire 3315 Monaural Microsoft Teams Certified USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X218AA
Poly Blackwire 3315 Monaural USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X217AA
Poly Blackwire 3315 USB-A Headset	76J12AA
Poly Blackwire 3320 Stereo Microsoft Teams Certified USB-C Headset +USB-C/A Adapter	8X220AA
Poly Blackwire 3320 Stereo USB-C Headset +USB-C/A Adapter	8X219AA
Poly Blackwire 3325 Microsoft Teams Certified USB-A Headset	76J21AA
Poly Blackwire 3325 Stereo Microsoft Teams Certified USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X222AA
Poly Blackwire 3325 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X221AA
Poly Blackwire 3325 USB-A Headset	76J20AA
Poly Blackwire 5210 Monaural USB-A Headset	80R98AA
Poly Blackwire 5210 Monaural USB-A Headset (Bulk)	80R98A6
Poly Blackwire 5210 Monaural USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X230AA
Poly Blackwire 5210 Monaural USB-C Headset +3.5mm Plug +USB-C/A Adapter (Bulk)	8X230A6
Poly Blackwire 5220 Stereo USB-A Headset	80R97AA
Poly Blackwire 5220 Stereo USB-A Headset (Bulk)	80R97A6
Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA
Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	93S88AA
Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter (Bulk)	8X231A6
Poly Blackwire 8225 Stereo Microsoft Teams Certified USB-C Headset +USB-C/A Adapter	8X225AA
Poly Blackwire 8225 Stereo USB-C Headset +USB-C/A Adapter	8X223AA

Poly Blackwire C3210 USB-A Black Headset (Bulk)	77R24A6
Poly Blackwire C3220 UC USB-A Headset	7S4L0AA
Poly Blackwire C3220 USB-A Black Headset (Bulk)	77R32A6
Poly Blackwire C3225 Top	7S4M7AA
Poly Blackwire C5220 USB-A Headset	7S4L8AA
Poly Blackwire C725-M Microsoft Teams Certified USB-A Headset	8A9S2AA
Poly EncorePro 310 Monaural USB-A Headset TAA	767G1AA
Poly EncorePro 310 Monoaural with Quick Disconnect Headset TAA	77T43AA
Poly EncorePro 310 USB-C Monoaural Headset TAA	760Q8AA
Poly EncorePro 320 Stereo USB-A Headset TAA	767G0AA
Poly EncorePro 320 Stereo USB-C Headset TAA	767F9AA
Poly EncorePro 320 with Quick Disconnect Binaural Headset TAA	77T26AA
Poly EncorePro 510 Monaural Headset +Quick Disconnect	783Q2AA
Poly EncorePro 510 with Quick Disconnect Monoaural Headset TAA	783Q1AA
Poly EncorePro 510D with Quick Disconnect Monoaural Digital Headset TAA	783Q0AA
Poly EncorePro 510V Monaural Headset VoiceTube +Quick Disconnect	783Q4AA
Poly EncorePro 510V Voice Tube Microphone with Quick Disconnect Monoaural Headset TAA	783Q3AA
Poly EncorePro 515 Microsoft Teams Certified Monoaural with USB-A Headset	783R1AA
Poly EncorePro 515 Monoaural with USB-A Headset	783R0AA
Poly EncorePro 520 Binaural Headset +Quick Disconnect	783P7AA
Poly EncorePro 520 with Quick Disconnect Binaural Headset TAA	783P6AA
Poly EncorePro 520D with Quick Disconnect Binaural Digital Headset TAA	783P5AA
Poly EncorePro 520V Binaural Headset VoiceTube +Quick Disconnect	783P9AA
Poly EncorePro 520V Voice Tube Microphone with Quick Disconnect Binaural Headset TAA	783P8AA
Poly EncorePro 525 Microsoft Teams Certified Stereo with USB-A Headset	783R2AA
Poly EncorePro 525 USB-A Stereo Headset	783R3AA
Poly EncorePro 530 Headset +Quick Disconnect	783P3AA
Poly EncorePro 530 with Quick Disconnect Discreet Headset TAA	783P2AA
Poly EncorePro 530D with Quick Disconnect Discreet Digital Headset TAA	783P4AA
Poly EncorePro 540 Convertible Headset +Quick Disconnect	783P1AA
Poly EncorePro 540 with Quick Disconnect Convertible Headset TAA	783P0AA
Poly EncorePro 540D with Quick Disconnect Convertible Digital Headset TAA	783N7AA
Poly EncorePro 545 USB-A Convertible Headset	783R4AA
Poly EncorePro 710D with Quick Disconnect Monoaural Digital Headset TAA	783N6AA

Poly EncorePro 715 USB-A Monoaural Headset TAA	783N5AA
Poly EncorePro 720D with Quick Disconnect Binaural Digital Headset TAA	783N4AA
Poly EncorePro 725 USB-A Stereo Headset TAA	783M6AA
Poly EncorePro HW710 Single Ear Headset +Carry Case +Quick Disconnect TAA	805H7AA
Poly EncorePro HW710 Single Ear Headset +HIS Kit +Carry Case TAA (Bulk)	805H7A6
Poly EncorePro HW720 Binaural Headset +Carry Case TAA	805H6AA
Poly H251 Supraplus Speakerphone +Pouch TAA	7S442AA
Poly H251N Supraplus Monaural Headset +Pouch TAA	7S443AA
Poly H261N Supraplus Binaural Headset +Pouch TAA	7S444AA
Poly HW261N Supraplus Binaural Dual Headset +Pouch TAA	7W074AA

Wireless Headset

Poly CS510 XD Extra Density Headset TAA	7E2J8AA
Poly CS520 XD Extra Density Headset TAA	7E2J9AA
Poly CS540 XD Extra Density Convertible Headset TAA	7E2J7AA
Poly CS540A Convertible Headset +AP11 Kit	7K2E5AA
Poly CS545 XD Extra Density Headset TAA	7E2K0AA
Poly Savi 7210 Office DECT 1920-1930 MHz Single Ear Headset	7W6D4AA
Poly Savi 7220 Office Binaural DECT 1920-1930 MHz Headset	7W6D5AA
Poly Savi 7310 Office Monaural DECT 1920-1930 MHz Headset	7S430AA
Poly Savi 7310-M Office DECT 1920-1930 MHz Single Ear Headset	7S439AA
Poly Savi 7320 Office Stereo DECT 1920-1930 MHz Headset	7S429AA
Poly Savi 7320-M Office Stereo DECT 1920-1930 MHz Headset	7S435AA
Poly Savi 8210 Office DECT 1920-1930 MHz Single Ear Headset	7S445AA
Poly Savi 8210 UC DECT 1920-1930 MHz USB-A Headset	77T29AA
Poly Savi 8210 UC Microsoft Teams Certified DECT 1920-1930 MHz USB-A Headset	77T31AA
Poly Savi 8210-M Office DECT 1920-1930 MHz Single Ear Headset TAA	7S447AA
Poly Savi 8220 Office Stereo DECT 1920-1930 MHz Headset	7S4B5AA
Poly Savi 8220 UC DECT 1920-1930 MHz USB-A Headset	77T33AA
Poly Savi 8220 UC Microsoft Teams Certified DECT 1920-1930 MHz USB-A Headset	77Y82AA
Poly Savi 8220-M Office Stereo DECT 1920-1930 MHz Headset TAA	7S4B6AA
Poly Savi 8245 DECT 1920-1930 MHz Headset +USB-A to USB-C Cable +D400 TAA	7W6B6AA
Poly Savi 8245-M Microsoft Teams Certified DECT 1920-1930 MHz USB-A Headset +D200 TAA	77T36AA

Poly Voyager 4245 USB-A Headset	7D7K0AA	
Poly Voyager 4245-M Office Headset +USB-A to Micro USB Cable	7S3Y5AA	
Poly Voyager 4310 Microsoft Teams Certified USB-A Headset +BT700 dongle	77Y91AA	
Poly Voyager 4310 Microsoft Teams Certified USB-C Headset +BT700 dongle	77Y95AA	
Poly Voyager 4310 USB-A Headset +BT700 dongle	76U48AA	
Poly Voyager 4310 USB-C Headset +BT700 dongle	77Y94AA	
Poly Voyager 4310 USB-C Headset +BT700 dongle +Charging Stand	77Y96AA	
Poly Voyager 4310-M Microsoft Teams Certified USB-C Headset +BT700 dongle +Charging Stand	77Y97AA	
Poly Voyager 4310-M UC Headset +USB-A to USB-C Cable +BT700 dongle	7Y210AA	
Poly Voyager 4320 Microsoft Teams Certified USB-A Headset +BT700 dongle	77Y98AA	
Poly Voyager 4320 Microsoft Teams Certified USB-C Headset +BT700 dongle	77Z30AA	
Poly Voyager 4320 USB-A Headset +BT700 dongle	76U49AA	
Poly Voyager 4320 USB-C Headset +BT700 dongle	76U50AA	
Poly Voyager 4320 USB-C Headset +BT700 dongle +Charging Stand	77Z31AA	
Poly Voyager 4320-M +USB-A to USB-C Cable +BT700 dongle	7Y211AA	
Poly Voyager 4320-M Microsoft Teams Certified Headset +BT700 dongle +Charging Stand	77Z32AA	
Poly Voyager 5200 Headset +USB-A to Micro USB Cable	7S431AA	
Poly Voyager 5200 Headset +USB-A to Micro USB Cable Nano Coating Technology	80S12AA	
Poly Voyager 5200 Office Headset +USB-A to Micro USB Cable TAA	7W6D2AA	
Poly Voyager 5200 Office Headset +USB-C to Micro USB Cable TAA	7S3Y1AA	
Poly Voyager 5200 UC Headset +USB-A to Micro USB Cable +BT700 dongle	7Y209AA	
Poly Voyager 5200 UC USB-A Headset +BT600 Dongle TAA	7K2E1AA	
Poly Voyager 5200 USB-A Bluetooth Headset +BT700 dongle	7K2F3AA	
Poly Voyager 5200 USB-A Headset HK	7S3X7AA	
Poly Voyager 5200 USB-A Office Headset TAA	7D793AA	
Poly Voyager 5200 USB-A Office Headset TAA	7W6D3AA	
Poly Voyager 5200-M Office Headset +USB-C to Micro USB Cable TAA	7S3Y4AA	
Poly Voyager 5240 Headset +USB-A to Micro USB Cable Nano Coating Technology	7S433AA	
Poly Voyager 6200 Black Headset	7D7G5AA	obsolete
Poly Voyager 6200 USB-C Black Headset	7D792AA	obsolete
Poly Voyager Focus 2 Microsoft Teams Certified USB-A Headset	77Y85AA	
Poly Voyager Focus 2 Microsoft Teams Certified USB-C Headset	77Y88AA	
Poly Voyager Focus 2 UC Headset +USB-A to USB-C Cable +Charging Stand	7S4L6AA	

Poly Voyager Focus 2 USB-A Headset	76U46AA
Poly Voyager Focus 2 USB-C Headset	76U47AA
Poly Voyager Focus 2 USB-C with charge stand Headset	77Y89AA
Poly Voyager Focus 2-M Microsoft Teams Certified with charge stand Headset	77Y90AA
Poly Voyager Focus B825 Headset +USB-A to Micro USB Cable	7S4M3AA
Poly Voyager Focus B825 UC +USB-A to Micro USB Cable +BT700 dongle	7S4K7AA
Poly Voyager Focus B825 UC Headset	7F0J1AA
Poly Voyager Focus B825 UC USB-C Headset +Charging Stand	7F0J3AA
Poly Voyager Focus B825 USB-A Headset +Charging Stand	7E2M4AA
Poly Voyager Focus B825 USB-A Headset +Charging Stand	7E2M4AT
Poly Voyager Focus B825 USB-C Headset TAA	7F0J4AA
Poly Voyager Focus B825-M UC Microsoft Teams Certified Headset	7F0J2AA
Poly Voyager Focus B825-M UC Microsoft Teams Certified Headset +Charging Stand	7F0J0AA
Poly Voyager Focus B825-M UC Microsoft Teams Certified Headset +Charging Stand	7F0J0AT
Poly Voyager Focus B825-M UC Microsoft Teams Certified Headset for Vending Machines	7K2E3AA
Poly Voyager Focus B825-M XS Extra Security UC Microsoft Teams Certified Headset +Charging Stand TAA	7K2E2AA
Poly Voyager Legend +Integrated Charge Cable	7W6C7AA
Poly Voyager Legend Headset +Integrated Charge Cable +Pin Adapter	7W6B8AA
Poly Voyager Legend Headset +USB-A to Micro USB Cable +Charging Stand with no Wall Plug	7W6B7AA
Poly Voyager Surround 80 UC Microsoft Teams Certified USB-C Headset +USB-C/A Adapter	8G7U0AA
Poly Voyager Surround 80 UC Microsoft Teams Certified USB-C Headset +USB-C/A Adapter	8H2G3AA
Poly Voyager Surround 80 UC USB-C Headset +USB-C/A Adapter	8G7T9AA
Poly Voyager Surround 85 UC Microsoft Teams Certified USB-C Headset +USB-C/A Adapter +Charging Stand	8G7T8AA
Poly Voyager Surround 85 UC USB-C Headset +USB-C/A Adapter +Charging Stand	8G7T7AA

Speakerphones

Poly Sync 10 Speakerphone +USB-A to USB-C Cable	7S4M6AA
Poly Sync 20 USB-C Speakerphone	7F0J7AA
Poly Sync 20+ Microsoft Teams Certified USB-A Speakerphone	772C9AA
Poly Sync 20+ Microsoft Teams Certified USB-C Speakerphone	772D1AA

Poly Sync 20+ USB-A Speakerphone	772C6AA
Poly Sync 20+ USB-C Speakerphone	772D0AA
Poly Sync 20+M Speakerphone +USB-A to USB-C Cable +BT700 dongle +Pouch	7Y215AA
Poly Sync 20-M Microsoft Teams Certified USB-C Speakerphone	7F0J8AA
Poly Sync 20-M Speakerphone +USB-A to USB-C Cable	7S4M1AA
Poly Sync 40+ Microsoft Teams Certified USB-A USB-C Speakerphone +BT700 USB-A Adapter	77P36AA
Poly Sync 40+ USB-A USB-C Speakerphone +BT700 USB-A Adapter	772C5AA
Poly Sync 60 Microsoft Teams Certified Speakerphone	77P41AA
Poly Sync 60 Speakerphone	772C2AA

Video

Video Accessories

Poly G7500 IP Table Microphone	874R3AA
Poly IP Ceiling Microphone Array	875S1AA
Poly Studio X50/X52/X70/USB Table Microphone	875M6AA

Voice

Conference Phone Accessories

Poly Trio 8300/8800 Expansion Microphones	85X00AA
Poly Trio C60 Expansion Microphones	85X02AA

Disclaimer — Copyright

Intel, the Intel logo, vPro, and Core Inside are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark of its proprietor, used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Adobe PDF is a trademark of Adobe Systems Incorporated. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. NVIDIA, the NVIDIA logo are trademarks and/or registered trademarks of NVIDIA Corporation in the US. and other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. All other trademarks are the property of their respective owners.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.