

# Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), Yellow, 20 ft. (6.09 m)

MODEL NUMBER: N201-020-YW



#### **Features**

- Length: 20-ft. (6.09 m)/Color: Yellow/Connectors: RJ45 male
- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation

## **Specifications**

OVERVIEW		
UPC Code	037332146212	
Technology	Cat6	
PHYSICAL		
Color	Yellow	
Cable Shielding	UTP	
Cable Jacket Material	PVC	
Cable Jacket Rating	СМ	
Number of Conductors	4 Pair	

### **Highlights**

- Premium cabling for Category 6,
  Category 5e and Category 5
  applications—rated for 550
  MHz/1 Gbps communications
- Designed to meet Category 6 specifications; reduces crosstalk and return loss
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

## Package Includes

20-ft. (6.09 m) Cat6 Yellow Gigabit Patch Cord Snagless Molded



Conductor Material	Strandad Cappar	
	Stranded Copper	
Conductor Gauge	24 AWG	
Cable Length (ft.)	20	
Cable Length (m)	6.1	
Cable Length (in.)	240	
Cable Length (cm)	609.6	
Shipping Dimensions (hwd / cm)	27.94 x 17.78 x 1.27	
Shipping Dimensions (hwd / in.)	11.00 x 7.00 x 0.50	
Shipping Weight (kg)	0.25	
Shipping Weight (lbs.)	0.56	
COMMUNICATIONS		
Bandwidth per TIA Standard	250 MHz	
Maximum Bandwidth as Tested	500 MHz	
Maximum Data Rate	1Gbps	
Network Speed	1Gbps	
CONNECTIONS		
Side A - Connector 1	RJ45 (MALE)	
Side B - Connector 1	RJ45 (MALE)	
Connector Type	Molded; Snagless	
Wiring Configuration	EIA/TIA 568B	
FEATURES & SPECIFICATIONS		
Cable Style	Unshielded; Molded; Snagless	
SPECIAL FEATURES		
IP68 Rated	No	
Snagless Connector	Yes	
Antibacterial	No	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>