BUSINESS PRODUCTIVITY MONITORS

PRO MP225 E12VL

SLIM, SLEEK, SMOOTH

SPECIFICATIONS

PANEL SIZE	21.45"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	120Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GtG)
PANEL TYPE	VA
BRIGHTNESS (NITS)	300 cd/m²
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CURVATURE	Flat
CONTRAST RATIO	4000:1
DCR	100000000:1
Signal Frequency	52.8~132 KHz(H) / 48~120Hz(V)
sRGB	100% (CIE 1976)
ACTIVE DISPLAY AREA (MM)	478.656(H) x 260.28(V)
PIXEL PITCH (H X V)	0.2493(H) x 0.241(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M, 8 bits
HDR SUPPORT	N/A
VIDEO PORTS	1x HDMI™ 1.4b (FHD@120Hz) 1x D-Sub (VGA)
USB Ports	N/A
Audio Interface	Line-in Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	N/A
Webcam	N/A
VESA MOUNTING	100 x 100 mm
POWER TYPE	Internal Power Board
POWER INPUT	100~240V, 50/60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
ADJUSTMENT (TILT)	-5° ~ 20°
ADJUSTMENT (SWIVEL)	N/A
ADJUSTMENT (PIVOT)	N/A
ADJUSTMENT (HEIGHT)	N/A
Dimension with Stand (W x D x H)	492.8 x 182.4 x 378.0 mm (19.40 x 7.18 x 14.88 inch)

FEATURES

21.45" Screen Size

View your applications, spreadsheets, and more with a perfect 21.45 inches screen

EyesErgo

An eye care solution designed with ergonomics in mind. Includes Eye care & Ergonomic features.

Anti-Flicker Technology & Less Blue Light

With MSI Anti-Flicker technology & Less Blue Light, a stable output current for the monitor & effectively reduce blue light is provided to protect your eyes.

Less Blue Light

Effectively reduce blue light which could cause serious long-term damage to your eyes.

120Hz High Refresh Rate

Enjoy the high-quality entertainment with a smoother and flicker-free images.

Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.

VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

Accessory Slot Design

Enjoy a clean table with the accessory slot design where you can put MSI Pen or Smartphone, and you will not miss important messages anymore.

© 2026 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.

PRO MP225 E12VL

SLIM, SLEEK, SMOOTH

Dimension without Stand (W x D x H)	492.8 x 49.9 x 283.1 mm (19.40 x 1.96 x 11.15 inch)
CARTON DIMENSION (W X D X H)	567 x 120 x 365 mm (22.32 x 4.72 x 14.37 inch)
ACCESSORIES	1x HDMI Cable (1.4) , 1x Power Cord, 1x Quick Guide
Note	HDMI™: 1920 x 1080 (Up to 120Hz) D-Sub(VGA): 1920 x 1080 (Up to 60Hz) Support - ; Non Support: HDMITM CEC/ MSI Power Link, PIP/PBP, KVM, FW Update

CONNECTIONS

1. 5-Way Navi Key
2. AC-in
3. 1x HDMI™ 1.4b (FHD@120Hz)
4. 1xD-Sub (VGA)
5. Kensington Lock

Generated 2026-02-24, check for the latest version www.msi.com/datasheet. The information provided in this document is intended for informational purposes only and is subject to change without notice.

© 2026 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.