ThinkPad P14s Gen 7 (Intel) 21XJ003DUS





The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core Ultra 7 366H, 16C (4P + 8E + 4LPE) / 16T, Max Turbo up to 4.8GHz, 18MB Intel Smart Cache
- 32GB LPCAMM2 LPDDR5X-7467
- 512GB SSD M.2 2280 PCIe 5.0x4 Performance NVMe Opal 2.0
- Integrated Intel Graphics
- Windows 11 Pro, English (US) / English (UK)
- Case color - Black
- 1Y Premier Support Upgrade from 1Y Courier/Carry-in

Premier Support - A direct 24x7x365 line to our most elite technicians.

- Advanced technical support, 24x7x365, in more than 100 markets
- Comprehensive hardware & OEM software support
- Single point of contact for simplified end-to-end case management
- Technical Account Managers for proactive relationship and escalation management
- Priority on service delivery and repair parts
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories

United States of America



ThinkPad Dual-Mode Wireless ANC Foldable Headset 8550 (Aura Edition) - USB-A,...

4XD1V23301



ThinkPad Bluetooth Presenter Mouse (Aura Edition)

4Y51T62792



ThinkPad 16" Click-Go Backpack (Aura Edition)

4X41V20931

>> View More Accessories

Recommended Services

Best

5Y Premier Support for AIPC upgrade from 1Y Premier Support (5WS1U94201)

Better

3Y Premier Support Plus for AIPC upgrade from 1Y Premier Support (5WS1U94171)

Good

4Y Premier Support for AIPC upgrade from 1Y Premier Support (5WS1U94200)

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

ThinkPad P14s Gen 7 (Intel) 21XJ003DUS

PERFORMANCE

Processor
Intel Core™ Ultra 7 366H, 16C (4P + 8E + 4LPE) / 16T, Max Turbo up to 4.8GHz, 18MB Intel® Smart Cache

AI PC Category
Copilot + PC, AI-Ready Workstations

NPU
Up to 50 TOPS

Graphics
Integrated Intel® Graphics

Chipset
Intel® SoC Platform

Memory[1]
32GB LPCAMM2 LPDDR5X-7467

Memory Slots
One LPCAMM2 connector, dual-channel

Max Memory
Up to 96GB (1x 96GB LPCAMM2), upgradable

Storage
512GB SSD M.2 2280 PCIe® 5.0x4 Performance NVMe® Opal 2.0

Storage Slot
One M.2 2280 PCIe® 5.0 x4 slot

Max Storage Support[2]
Up to one 2TB M.2 2280 Gen 5 Performance SSD

Card Reader
No card reader

Audio Chip
SoundWire®, Realtek® ALC722-CG codec

Speakers
Stereo speakers, 2W x2, Dolby Atmos®

Microphone
2x, Array

Camera
5.0MP + IR with Privacy Shutter, HDR and Computer Vision Human Presence Detection

Battery
75Wh

Power Adapter
100W USB-C® Slim (3-pin)

DESIGN

Display
14.5" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, 60Hz, Eyesafe®, UL Low Blue Light

Touchscreen
None

Screen-to-Body Ratio
88.51%

Color Calibration
AICCP Color Calibration

Pen
Pen Not Supported

Keyboard
Backlit, English

Dimensions (WxDxH)[3]
325.2 x 226.3 x 11.7 / 16.22 (front / rear), 22.2 (maximum) mm 12.80 x 8.91 x 0.46 / 0.64 (front / rear), 0.87 (maximum) inches

Weight[4]
Starting at 1.63 kg (3.59 lbs)

Case Color
Black

Case Material
Aluminium (Top), Aluminium (Bottom)

SOFTWARE

Operating System
Windows® 11 Pro, English (US) / English (UK)

Bundled Software
Intel® Connectivity Performance Suite + Lenovo® AI Now + ThinkShield Pro (SentinelOne, Sepio, Cigent) 1-year

CONNECTIVITY

WLAN + Bluetooth
Intel® Wi-Fi® 7 BE211, 802.11be 2x2 + BT5.4, vPro®

WWAN
WWAN Not Supported

SIM Card
No physical SIM card inbox

Ethernet
100/1000M (RJ-45), vPro®

NFC
No NFC

Standard Ports
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x Thunderbolt™ 4, with USB PD 3.1 and DisplayPort™ 2.1, 140W input / 15W output
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (GbE RJ-45)
- 1x Kensington Nano Security Slot™

Docking
Various docking solutions supported via Thunderbolt™ or USB-C®. For more compatible docking solutions, please visit Docking for ThinkPad® P14s Gen 7 (Intel®)

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0 Enabled

Physical Locks
Kensington Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader
No Smart Card Reader

Fingerprint Reader
Touch Style, Match-on-Chip, Integrated in Power Button

Other Security
- Computer Vision-based Human Presence Detection
- Bottom cover tamper detection
- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management
Intel® vPro® Enterprise

SERVICE

Base Warranty
1-year, Courier or Carry-in

Included Upgrade
1Y Premier Support Upgrade from 1Y Courier/Carry-in

ACCESSORIES

CERTIFICATIONS

ISV Certifications
Please visit ISV certifications for Lenovo® Workstations

Green Certifications
- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test
MIL-STD-810H military test passed

Other Certifications
- Eyesafe® Certified 2.0
- UL Low Blue Light

MODEL

TopSeller	: Yes	**EAN / UPC / JAN**	: 199276369727
Announce Date	: 2026-05-29	**End of Support**	: 2032-12-15

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
  · California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: https://www.calrecycle.ca.gov/Electronics/Consumer
- To view full note details, please visit the web page.