Cubi 5 1M

FEATURES

Small Size

Hand Palm-sized PC but still provides all the elements of a desktop-worthy PC.

Thunderbolt™ 4

Up to 40Gb transmission speed, brings fast speed and versatility, offering a fast and simple level of connection for work.

Matrix Display

Supports the Multi-display mode and the surround view mode

Dual LAN

Dual LAN design provides the second LAN backup and a safer network environment

MSI Power Link

A desktop PC can be powered by an MSI-selected monitor through MSI Power Link technology, enabling the most convenient user experience.

Power Meter

Power Meter enables one-click power saving, carbon emission calculation & electricity cost estimation.

MSI AI Engine

Incorporating AI technology, the MSI AI Engine can switch settings, including lighting, performance, audio and visual based on different applications.

TPM Support

FW TPM design secures your confidential data with encryption keys.

VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

SPECIFICATIONS

Operating System	Windows 11 Home Windows 11 Pro - MSI recommends Windows 11 Pro for business
CPU	Intel® Core™ 7 processor 150U Intel® Core™ 5 processor 120U Intel® Core™ 3 processor 100U
Chipset	Intel® SoC
Graphics	Intel® Graphics (Integrated)
Storage	1x M.2 2280 SSD (NVMe PCIe Gen4 x4, factory pre-installed) 1x 2.5” Drive Bay
System Memory	2x DDR5 5200 SO-DIMMs, up to 64GB
I/O (Front)	1x Thunderbolt 4 (DP 1.4 alt-mode up to 4K@60Hz / PD-out 15W) 2x USB 10Gbps Type A 1x Mic-in / Headphone-out combo
I/O (Rear)	2x USB 10Gbps Type A 2x RJ45 (2.5G & 1G LAN) 1x HDMI out (supports 4K @60Hz as specified in HDMI 2.1) 1x DisplayPort (v1.4)
I/O (SIDE)	1x Kensington Lock 1x External Power Switch Pin Header
Wireless LAN	Intel® WiFi 6E AX211 / AzureWave AW-CB515NF Wi-Fi 5
Bluetooth	5.3 (for AX211) / 5.0 (for AW-CB515NF)
TPM	fTPM
LAN	1x Realtek® RTL8111H (1G), 1x Realtek®RTL8125BG-CG (2.5G)
KEYBOARD / MOUSE	Optional
AC Adapter / PSU	65W
Dimension (WxDxH)	124 X 124 X 53.7 mm (4.88 X 4.88 X 2.11 inch)
WEIGHT (N.W./ G.W.)	0.6 Kg (1.32 lbs)
VESA Mount	75 x 75 mm and 100 x 100 mm
GROSS WEIGHT	1.54 Kg (3.40 lbs)
Certificates	FCC, CB/CE, UL & CUL, VCCI, RCM

CONNECTIONS

1. 1x Mic-in/ Headphone-out combo
2. 2x USB 10Gbps Type A
3. 1x Thunderbolt 4 (USB Type C)
4. 1x Power button
5. 1x Kensington Lock & External Power Switch Pin Header
6. 1x HDMI™ out
7. 1x DP out (1.4)
8. 2x RJ45
9. 2x USB 10Gbps Type A
10. 1x DC Jack

Generated 2026-07-13, check for the latest version www.msi.com/datasheet. The information provided in this document is intended for informational purposes only and is subject to change without notice.

© 2026 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.