Lenovo L27-4r Monitor 68FEKCC1US

The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 27" FHD, 165Hz refresh rate, 99% sRGB, 1,500:1 contrast ratio
- 4ms GtG and 1ms MPRT response time, AMD FreeSync™ support
- HDMI®, VGA and Audio out ports, Built-in 2 x 3W audio speakers
- Hardware low blue light and TÜV-certified flicker-free screen technology
- Tilt stand with phone holder, built-in cable management design and VESA mount 100 x 100
- Lenovo® Artery (Lenovo® Accessories and Display Manager)software
- Case color - Cloud Grey
- 1-year

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories United States of America

NanoSaver Cable Lock from Lenovo

4XE1L51710



Lenovo Cloth Gaming Mouse Pad M

GXH1C97873

>> View More Accessories

Product Illustration

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Lenovo L27-4r Monitor 68FEKCC1US

PERFORMANCE

Display Size
27″

View Area
597.9x336.3 mm

Panel
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920x1080

Pixel Pitch
0.1038x0.3114 mm

Dot / Pixel Per Inch
82 dpi

View Angle (H / V)
178° / 178°

Response Time
1ms (MPRT) / 4ms (Extreme Mode) (G to G) / 6ms (Normal Mode) (G to G)

Color Support
16.7 Million

Refresh Rate
165Hz

Brightness
300 cd/m²

Contrast Ratio
1500:1

Color Gamut
99% sRGB (CIE 1931)

Screen Surface Treatment
Anti-glare

Curvature
None

Camera
None

Microphone
None

Speakers
3Wx2

Power Consumption (Typical / Maximum)
18.5W / 45W

Power Adapter
Integrated

Touchscreen
None

Smart System
None

DESIGN

Stand
Tilt

Case Color
Cloud Grey

Side Bezel Width
2 mm

Mounting
Supports VESA mount 100 x 100 mm

ThinkCentre M Series Support
Tiny Support[1]

Pen
None

Dimensions (WxDxH)[2]
- Monitor with stand | 611.5 x 181.5 x 474.6 mm (24.07 x 7.15 x 18.69 inches)
- Head Only | 611.5 x 41.0 x 355.6 mm (24.07 x 1.61 x 14.00 inches)

Packaging Dimensions (WxDxH)
715.0 x 113.0 x 417.0 mm (28.15 x 4.45 x 16.42 inches)

Weight[3]
- Monitor With Stand | 3.9 kg (8.6 lbs)
- Monitor Head Only | 2.9 kg (6.4 lbs)

Packaging Weight
6.2 kg (13.7 lbs)

CONNECTIVITY

Rear Ports
- 2x HDMI® 2.1 TMDS[4]
- 1x VGA
- 1x audio-out (3.5mm)

SERVICE

Base Warranty
1-year

CERTIFICATIONS

Environmental Certification
ENERGY STAR® Certified, EPEAT™ Gold, EU Energy Efficiency Level (Level-E), Volatile Organic Compound Certification, RoHS

Ergonomic Certification
TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free

Sync Technology
AMD FreeSync™

Special Features
- AMD FreeSync™
- Lenovo® Artery (Lenovo® Accessories and Display Manager)[5]
- Natural Low Blue Light

SOFTWARE

Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

In the Box
- Monitor with stand
- 1x HDMI® 2.0 cable (1.8m)
- 1x Power cable (1.8m)
- 1x Screw
- Quick setup guide
- Warranty booklet

MODEL

Region	: NA
EAN / UPC / JAN	: 0199276546234 / 199276546234 / None
Announce Date	: 2026-07-13

Note:
[1] Sold separately. Need to assemble ThinkCentre Tiny VESA Mount II (PN: 4XF0N03161) to support Tiny PC installation.
[2] The system dimensions may vary depending on configurations.
[3] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
[4] Supports 1920 x 1080@165Hz as specified in HDMI 2.1 TMDS.
[5] Formerly Lenovo Display Control Center. Supports Windows 10 & 11.

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
  · California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: https://www.calrecycle.ca.gov/Electronics/Consumer