

Phaser®
3300MFP
Letter-size
Black-and-white
Multifunction Printer



Xerox Phaser® 3300MFP
Multifunction Laser Printer
Maximize business
productivity

xerox

Phaser® 3300MFP multifunction laser printer

Fast and feature-rich. With high-speed print and copy, and full-featured scan and fax, this powerful multifunction printer delivers document handling that gives busy work teams a competitive edge. Value-priced and network-ready, the Phaser 3300MFP is the robust, reliable choice for your business.

High-end performance

The Phaser 3300MFP is built for speed, with the printing and scanning performance of larger multifunction devices.

30
ppm

- **Copying and printing that moves at the speed of business** (30 ppm with the first page out as fast as 8.5 seconds).
- **Get more printing done** with a 300-sheet capacity, expandable to 550 sheets, and the ability to handle special custom-sized media such as postcards and envelopes.
- **1200 image quality printing** gives your documents a high-quality, professional impact.
- **Print any document with confidence**, thanks to full PCL and PostScript 3 support and automatic tray switching that switches to the next tray when the default tray is empty.
- **Precision engineering** ensures that the Phaser 3300MFP is easy to set up, use and maintain.
- **Digital workflows** let you route electronic and scanned-in paper documents to their correct locations on the network.

Rich feature set at a value price

The Phaser 3300MFP is loaded with features that help you reduce operating costs and optimize resource usage.

- **One device** gives you the right combination of office tools—print, copy, scan and fax—at one great price.
- **Powerful fax/scan tools** bring fax and paper documents easily to the network, for distribution via email, fax or through your network's LDAP address book.
- **Network ready** with built-in Ethernet connectivity, remote management tools and network security.
- **Save money on resources:** Toner-saver and power-saver modes and features like N-up printing and ID Card Copy make it easy to reduce toner, paper and energy costs.
- **Automatic two-sided printing** improves productivity and reduces paper use.
- **Scan to/print from a USB memory drive** from the front control panel in multiple file formats. No computer needed!
- **All the features of top fax machines** including speed dial, Secure Fax, color send and LAN fax.

Phaser® 3300MFP Quick Facts

- Up to 30 ppm print and copy
- 600 x 600 dpi (Up to 1200 x 1200 enhanced image quality)
- 300 MHz processor
- 96 MB (64 MB + 32 MB DIMM) (320 MB maximum)
- 300-sheet capacity, expandable to 550 sheets
- 25,000 pages/month duty cycle



Print, Copy, Scan, Fax

8.5 x 14 in.

30 ppm

WxDxH:
18.3 x 17.1 x 18 in.
466 x 435.4 x 458 mm



Manage paper to digital quickly and easily

Fast, easy scanning

With the power of scanning built-in, the Phaser 3300MFP makes it easy to create, organize and distribute business-critical digital files.

- Scan color documents quickly and accurately at up to 24-bit 4800 x 4800 dpi resolution.
- Send scanned documents directly to the inbox from the front panel using scan to email.
- No-fuss network scanning lets you input and store documents to the network.
- Character recognition software turns hard copies into editable electronic documents.

Powerful faxing

The Phaser 3300MFP easily handles critical fax jobs.

- Forward an incoming fax to another fax number or an email address.
- Powerful 24-bit color faxing.
- Maintain your privacy with Secure Fax receive and a junk fax barrier.
- Store up to 240 fax numbers in speed dial.
- 15 one-touch speed buttons on front panel.
- 200 group-dial locations broadcast fax to up to 249 numbers.



Business-ready design

The Phaser 3300MFP's thoughtful design is tailored for the busiest offices and backed by superb support.

- **Buy with confidence:** The Phaser 3300MFP is backed by 1-year service and our unmatched Xerox Total Satisfaction Guarantee.
- **Support for popular operating system platforms** right out of the box make this multifunction a team player. (Microsoft Windows XP, Windows Vista, Linux/UNIX, and Apple Macintosh)
- **Advanced security features** such as authentication and IP filtering help prevent unauthorized access to the device.
- **Remote management tools** such as CentreWare IS give you quick access to a wealth of information and controls, such as device, toner status, device setup, email and fax address book management, security settings and email alerts. You can also specify which trays are used by specific operations such as fax or copy.
- **Back up device data**, such as address books, using CentreWare IS or a USB memory drive.
- **Designed to save space in the office;** small footprint lets you put it wherever it's needed.
- **Single print cartridge** reduces maintenance and support costs.
- **802.1x support** secures device on network.

- 1 Automatic Document Feeder provides fast scanning, copying and faxing of multi-page jobs.
- 2 Automatic two-sided printing gives you money-saving, professional-looking output.
- 3 50-sheet multipurpose tray handles a variety of paper and custom sizes, including envelopes, labels and post cards.
- 4 250-sheet tray provides plenty of paper capacity for workgroup printing, copying and faxing.
- 5 An additional 250-sheet tray (optional) boosts total capacity to 550 sheets.
- 6 USB memory port lets you save to or print directly from a USB memory drive – no computer needed.
- 7 Toner Saver reduces the amount of toner applied to paper, making toner supplies go further.
- 8 One-touch duplex lets you turn single-sided originals into two-sided copies.
- 9 Find frequently used fax numbers and email addresses in address book. You can also print an address list.



The simple front panel makes walkup functions and features accessible with the touch of a button.

Phaser® 3300MFP

Black-and-White Multifunction Printer



| | | Phaser 3300MFP |
|------------------------------|----------|---|
| Speed | | Up to 30 ppm (Letter) / 28 ppm (A4) |
| Duty Cycle | | Up to 25,000 pages / month |
| Paper Handling | | |
| Paper input | Standard | Automatic Document Feeder: 50 sheets; Custom Sizes: 5.6 x 5.8 in. to 8.5 x 14 in. / 142 x 148 mm to 216 x 356 mm |
| | | Multipurpose Tray: 50 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm |
| | | Main Tray: 250 sheets; Sizes: Letter, Legal, Folio, Oficio, A4, JIS B5, ISO B5, Executive, A5, A6 |
| Optional | | Additional Tray: 250 sheets; Sizes: Letter, Legal, Folio, Oficio, A4, JIS B5, ISO B5, Executive, A5, A6 |
| Paper output | | 150 sheets face down, 1 sheet face up |
| Automatic two-sided printing | | Standard |
| Print | | |
| First-page-out-time | | As fast as 8.5 seconds |
| Print resolution | | 600 x 600 dpi (up to 1200 x 1200 enhanced image quality) |
| Memory (std / max) | | 96 MB (64 MB + 32 MB DIMM) / 320 MB maximum |
| Processor | | 300 MHz |
| Language support | | PCL® 6 / 5e emulations, PostScript® 3™ compatibility |
| Connectivity | | USB 2.0, 10/100Base-TX Ethernet |
| Print features | | Watermarks, Toner save mode, N-up, Saved settings, Fit to page, Collation, Overlay, Reduce/enlarge, Poster, Scaling, Print from USB, Booklet printing |
| Copy | | |
| First-page-out-time | | As fast as 8.5 seconds |
| Copy resolution | | Up to 600 x 600 dpi |
| Copy features | | Reduce/enlarge, Two-sided (1:2 duplex copy), Background suppression, Collation, ID Card Copy, 2-up/4-up, Cloning, Poster |
| Fax | | 33.6 Kbps with MH/MR/MMR/JBIG/JPEG compression |
| Fax features | | Color fax send, Searchable address book, Fax reports, Forward to fax/email, PC and LAN Fax (send only), Secure fax receive, Last number redial, Distinctive ring, Journal, Junk fax barrier, up to 200 group dial locations, Broadcast fax (up to 249 locations), Delayed fax send, Memory receive, Auto file size reduction, 6 MB fax memory |
| Scan | | |
| Scan destinations | | Scan to Email (includes up to 200 local directory entries, 50 group email entries, authentication); Network Scanning (Windows only) via SMB and FTP; Scan to USB Memory Drive (File formats: BMP, JPG, Multipage PDF, Multipage TIFF); Direct Scan to Applications including OCR (software included) |
| Scan features | | Up to 4800 x 4800 dpi (enhanced), File formats: BMP, JPG, Multipage PDF, Multipage TIFF; Scan to PC Desktop® Personal Edition (includes 1 seat of Nuance® PaperPort® SE 11.0, OmniPage® 4.0 SE, Image Retriever), Color Scanning, FTP, SMB, SMTP and HTTP(S), Scan Build Job |
| Security | | 802.1x, SNMPv3, HTTPS, Secure Fax, SSL, IP Filtering, Scan to Email with user authentication |
| Warranty | | One-year warranty, Xerox Total Satisfaction Guarantee |

Device Management

CentreWare® Internet Services, CentreWare Web, CentreWare for HP® OpenView, Rendezvous (Bonjour)

Print Drivers

Windows® 2000/XP/Vista/2003 Server, Mac OS® version 8.6-9.2, 10.3-10.5, Various Linux® OS including SUSE™ 8.2-9.2, Red Hat® 8-9, Fedora™ Core 1-4, Mandrake 9.2-10.1, Xerox Mobile Express Driver, Xerox Global Print Driver

Media Handling

Multipurpose Tray: 16 – 43 lb. bond / 60 – 163 gsm; Media types: Plain paper, envelopes, transparencies, labels, cardstock, postcards, cotton, pre-printed, recycled, bond, archive; Main Tray and Additional Tray (optional): 16 – 24 lb. bond / 60 – 90 gsm; Media types: Plain paper; ADF: Weight: 12.5 to 28 lb / 50 to 120 gsm
Media types: Plain paper

Operating Environment

Operating: 50° to 90° F / 10° to 32° C; Relative humidity: 20 to 80%; Sound pressure levels: Printing: 55 dB(A), Standby: 39 dB(A); Warm-up time (from sleep mode): Less than 20 seconds

Electrical

Power: 110–127 VAC, 50/60 Hz or 220–240 VAC, 50/60 Hz; Power consumption: Standby: 79 W; Printing: 478 W; Power save: 10 W ENERGY STAR® qualified

Dimensions (WxDxH)

18.3 x 17.1 x 18 in. / 466 x 435 x 458 mm; Weight: 41.6 lbs / 18.9 kg; Package Dimensions (WxDxH): 23.2 x 22 x 25.2 in. / 590 x 559 x 640 mm; Optional 250-sheet Tray 2: 18.3 x 17.1 x 3.3 in. / 466 x 434 x 85 mm; Weight: 6.38 lbs / 3.1 kg

Certifications

Listed UL 60950, CE Mark applicable to Directives 2006/95/EC, 2004/108/EC and 99/5/EC, FCC Part 15 Class B, FCC Part 68

What Comes In The Box

- Phaser 3300MFP Multifunction Printer
- Print Cartridge (4,000 print capacity¹)
- Software and Documentation CDs (with Print Drivers, Scanning Software, User Manual, Quick Installation Guide, Warranty Statement and Registration Card)
- Power cord, USB cable, fax cord

Supplies

Standard-Capacity Print Cartridge¹:

4,000 std. pages

106R01411

High-Capacity Print Cartridge¹:

8,000 std. pages

106R01412

¹ Average standard pages. Declared Yield in accordance with ISO/IEC 19752. Yield will vary based on image, area coverage and print mode.

Options

250-sheet Tray

097N01693

256 MB Phaser Memory

097S03761

Supplies Recycling Program

Consumables for the Phaser 3300MFP are part of the Xerox Green World Alliance Supplies Recycling Program. For more information, please visit the Green World Alliance website at www.xerox.com/gwa



Call today. For more information, call **1-877-362-6567** or visit us at www.xerox.com/office