

#### Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

# Cat5e 350 MHz Solid-Core Outdoor-Rated (UTP) PVC Bulk Ethernet Cable - Gray, 1000 ft. (304.8 m)

### MODEL NUMBER: N028-01K-GY



#### Features

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range: -40F to +140F
- 1000-ft. Pull-box, length marked every two feet
- Terminate with Tripp Lite N030-010 Solid wire Cat5e RJ45 plugs

## **Specifications**

OVERVIEW	
UPC Code	037332141491
Technology	Cat5/5e
PHYSICAL	
Color	Gray
Cable Shielding	UTP
Cable Jacket Rating	CMX
Wire Type	Solid
Wire Gauge (AWG)	24
Cable Length (ft.)	1000

#### Highlights

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low

Attenuation Loss

 CMX Outdoor rating; Temp range -40F to +140F

#### Package Includes

1000ft. Box Cat5e Outdoor Rated PVC Bulk Cable



Cable Length (m)	304.8	
Cable Length (in.)	12000	
Cable Length (cm)	30480	
Shipping Dimensions (hwd / cm)	22.86 x 37.08 x 38.10	
Shipping Dimensions (hwd / in.)	9.00 x 14.60 x 15.00	
Shipping Weight (kg)	11.29	
Shipping Weight (lbs.)	24.90	
CONNECTIONS		
Side A - Connector 1	BARE WIRE	
Side B - Connector 1	BARE WIRE	
FEATURES & SPECIFICATIONS		
Cable Style	Outdoor Rated; Bulk; Unshielded	
SPECIAL FEATURES		
Snagless Connector	No	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies